

Quantity	Comment	Designator	Footprint
1	100nF	C1	0805_C
2	10nF	C2, C3	0805_C
2	1nF	Cext1, Cext2	0805_C
1	Header 10X1_M-F	CN5	SIP10 Male-Female
2	Header 8X1_M-F	CN6, CN9	SIP8 Male-Female
2	Header 19X2	CN7, CN10	SIP38 Female
1	Header 6X1_M-F	CN8	SIP6 Male-Female
1	STTH1L06 NM	D1	SMA
1	VBatt	J1	Terminal Block 2 POS
1	Output	J2	Terminal Block 2 POS
1	LED2_green	LED 1	0805_LED
2	LED2_red	LED 2, LED 3	0805_LED
3	2K2	R1, R9, R10	0805_R
5	56K	R2, R3, R5, R6, R7	0805_R
2	36K	R4, R8	0805_R
6	0R	R11, R13, R14, R21, R22, R23	0805_R
7	0R NM	R12, R15, R17, R18, R19, R20, R24	0805_R
1	0R NM	R16	0805_R
2	1k	Rsense1, Rsense2	0805_R
2	---	R_UP1, R_UP2	0805_R
1	GND	TP1	TPoint
1	V_Batt	TP2	TPoint
1	IN0	TP3	TPoint
1	CS1	TP4	TPoint
1	IN1	TP5	TPoint
1	CS2	TP6	TPoint
1	FR_Stby	TP7	TPoint
1	MultiSense1	TP8	TPoint
1	GND_Sense	TP9	TPoint
1	MultiSense2	TP10	TPoint
1	VPS2535H	U1	PSSO24

