



EXT  
JP1  
INT

GND

+5V  
D2

C5  
GND

VIN

VIN

+5V

CN5

R2

R8

CN2

CN1

SENSE-A

R12

OUT1A

R6

R16

C4

R18

R7

R9

VREFA


U1

D1 R13

CN3

OUT2A

HALF SLOW ENABLE CW



C7

FULL FAST SW1 CCW

R10

C6

GND



L6208PD

OUT2B

R4

R5

R20

R17

R11

R21

C9

VREFB

C1

R15

R14



OUT1B

SENSE-B

GND