

Bill of materials

Table 1. X-NUCLEO-NFC10A1 bill of materials

Item	Q.ty	Ref.	Part/Value	Description	Manufacturer	Order code
1	5	C100, C203, C207, C209, C211	2.2 uF	Multilayer Ceramic Capacitors MLCC - SMD/SMT 2.2UF 6.3V 20% 0402	MURATA	GRM155R60J225ME15D
2	2	C200, C215	1.0 uF	Multilayer Ceramic Capacitors MLCC - SMD/SMT 1.0UF 16V 10% 0402	MURATA	GRM155R61C105KA12D
3	6	C201, C202, C206, C208, C210, C213	0.01 uF	Multilayer Ceramic Capacitors MLCC - SMD/SMT 25V 0.01uF X7R 0402 10%	AVX	04023C103KAT2A
4	2	C204, C205	10 pF	Multilayer Ceramic Capacitors MLCC - SMD/SMT 10 pF 50 V C0G 0402	MURATA	GRM1555C1H100GA01D
5	2	C212, C216	0.1 uF	Multilayer Ceramic Capacitors MLCC - SMD/SMT 0.1 uF 10 V X5R 0402	MULTICOMP	MC0402X104K100CT
6	1	C214	4.7 uF	Multilayer Ceramic Capacitors MLCC - SMD/SMT 4.7 uF 10 V X5R 0402	MURATA	GRM155R61A475MEAA
7		C217, C218	5.6 pF	Multilayer Ceramic Capacitors MLCC - SMD/SMT 5.6 pF 50 V C0G 0402, NOT MOUNTED	MURATA	GRM1555C1H5R6BA01D
8	2	C300, C313	200 pF	Multilayer Ceramic Capacitors MLCC - SMD/SMT 200 pF 50 V C0G 0402	MURATA	GRM1885C1H201GA01D
9	2	C301, C311	4.7 pF	Multilayer Ceramic Capacitors MLCC - SMD/SMT 4.7 pF 50 V C0G 0603	MURATA	GRM1885D1H4R7CA01D
10	2	C302, C312	10 pF	CERAMIC CAPACITOR 10PF 50V, C0G, 1%, 0603,	MULTICOMP	MC0603N100F500CT
11	2	C303, C310	39 pF	Multilayer Ceramic Capacitors MLCC - SMD/SMT 39 pF 50V 1% 0603	MURATA	GCM1885C1H390FA16J
12	2	C304, C307	300 pF	Multilayer Ceramic Capacitors MLCC	MURATA	GRM1885C1H381GA01D

Item	Q.ty	Ref.	Part/Value	Description	Manufacturer	Order code
				- SMD/SMT 304 pF 50V C0G 2% 0603		
13	2	C305, C308	9 pF	Multilayer Ceramic Capacitors MLCC - SMD/SMT 9 PF 50V NP0 0,5pF 0603	MURATA	GRM1885C1H9R0DA01D
14	2	C306, C309	130 pF	Multilayer Ceramic Capacitors MLCC - SMD/SMT 130 PF 50V NP0 2% 0603	MURATA	GRM1885C1H131GA01D
15	1	CN5		Header, 10-Pin, Single row,female	SAMTEC	SSQ-110-03-L-S
16	2	CN6, CN9		Header, 8-Pin, Single row,female	SAMTEC	SSQ-108-03-L-S
17	1	CN8		Header, 6-Pin, Single row,female	SAMTEC	SSQ-106-03-L-S
18	2	J300, J304	0 Ohm	Thin Film Resistors 100mW ZEROΩ Jumper	VISHAY	MCS04020Z0000ZE000
19	2	J302, J303		HE14 Male Vertical Single Row 2 pin 2.54MM, NOT MOUNTED	MOLEX	22-28-5020
20	1	L200	120 Ω	Ferrite Beads 120 OHM 25%	MURATA	BLM15PD121SN1D
21	2	L300, L301	270 nH	Fixed Inductors 0603 270nH Unshld 2% 300mΩ AEC-Q200	COILCRAFT	0603LS-271XGLB
22	1	LED100		Standard LEDs - SMD Green Clear 571nm	LITE-ON	LTST-C190KGKT
23	6	LED101, LED102, LED103, LED104, LED105, LED106		Standard LEDs - SMD Blue Clear 470nm	LITE-ON	LTST-C190TBKT
24	2	P200, P201		RF Connectors / Coaxial Connectors U.FL RECEPTACLE SMT GLD M CONT REEL, NOT MOUNTED	HIROSE(HRS)	U.FL-R-SMT(10)
25	1	R100	680Ω	Thick Film Resistors - SMD 680 Ω 62.5mW 0402 5%	YAGEO	RC0402JR-07680RL
26	6	R101, R102, R103, R104, R105, R106	1K Ω	Thick Film Resistors - SMD 0402 1KΩ 5% AEC-Q200	PANASONIC	ERJ2GEJ102X

Item	Q.ty	Ref.	Part/Value	Description	Manufacturer	Order code
27	6	R108, R203, R204, R205, R206, R207	0 Ohm	Thin Film Resistors 100mW ZERO Ω	VISHAY	MCS04020Z0000ZE000
28	1	R208	0.1 Ω	Current Sense Resistors - SMD 0.1 Ω 0603 0.5% 0.20W	OHMITE	KDV06DR100ET
29	1	R209	10k Ω	Thick Film Resistors - SMD 10 k Ω 62.5 mW 0402 1% AEC- Q200	YAGEO	AC0402FR-7W10KL
30	1	R210	330k Ω	Thin Film Resistors - SMD .1W 330K Ω .1% 0402 25ppm	VISHAY	CRCW0402330KFKEDC
31	2	R211, R212	0 Ω	Thin Film Resistors 100mW ZERO ohm, NOT MOUNTED	VISHAY	MCS04020Z0000ZE000
32	2	R300, R301	2.4 Ω	Thick Film Resistors - SMD 2.4 Ω 100 mW 0603 1%	YAGEO	RC0603FR-072R4L
33	1	R304	0 Ω	Thick Film Resistors - SMD 0 Ω 100mW 0603 1% AEC-Q200	YAGEO	AC0603FR-070RL
34	1	S200		Tactile Switches 3.5x2.9mm Right Ang Light Touch Switch	PANASONIC	EVQ-P7C01P
35	11	ST1, ST2, ST3, ST4, ST7, ST8, ST9, ST15, ST16, ST17, ST18		CONN HE14 2PTS MALE VERTICAL	TEST POINT	TEST POINT
36	6	ST5, ST10, ST11, ST12, ST13, ST14		CONN HE14 2PTS MALE VERTICAL, NOT MOUNTED	TEST POINT	TEST POINT
37	1	ST6		CONN HE14 2PTS MALE VERTICAL, NOT MOUNTED	TEST POINT	TEST POINT
38	2	ST19, ST20		CONN HE14 2PTS MALE VERTICAL, NOT MOUNTED	TEST POINT	TEST POINT
39	1	U200		HF READER ST25R200 QFN24, NOT MOUNTED	ST	ST25R200-BMET
40	1	Y200		CRYSTAL 27.1200MHZ 10PF SMD, NOT MOUNTED	NDK AMERICA	NX2016SA-27.12MHZ-EXS00A- CS01188

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2024 STMicroelectronics – All rights reserved