STGB10NC60HDT4, STGP10NC60HD

Datasheet

600 V, 10 A very fast IGBT





Features

- Low on voltage drop ($V_{CE(sat)}$)
- Low C_{res} / C_{ies} ratio (no cross-conduction susceptibility)
- Very soft ultra-fast recovery antiparallel diode

Applications

- High frequency motor controls
- SMPS and PFC in both hard switch and resonant topologies
- Motor drives

Description

These devices are very fast IGBTs developed using advanced PowerMESH technology. This process guarantees an excellent trade-off between switching performance and low on-state behavior.

Product status links
STGB10NC60HDT4
STGP10NC60HD

Product summary	
Order code	**STGB10NC60HDT4**
Marking	GB10NC60HD
Package	D²PAK
Packing	Tape and reel
Order code	**STGP10NC60HD**
Marking	GP10NC60HD
Package	TO-220
Packing	Tube

1 Electrical ratings

Table 1. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{CES}	Collector-emitter voltage (V_{GE} = 0 V)	600	V
I_C(1)	Continuous collector current at T_C = 25 °C	20	A
	Continuous collector current at T_C = 100 °C	10	
I_{CL}(2)	Turn-off latching current	30	A
I_{CP}(3)	Pulsed collector current	30	A
V_{GE}	Gate-emitter voltage	±20	V
I_F	Diode RMS forward current at T_C = 25 °C	10	A
I_{FSM}	Surge non repetitive forward current t_p = 10 ms sinusoidal	20	A
P_{TOT}	Total power dissipation at T_C = 25 °C	65	W
T_{stg}	Storage temperature range	-55 to 150	°C
T_J	Operating junction temperature range		°C

1. *Calculated according to the iterative formula:* $I_C(T_C) = \frac{T_{J(\max)} - T_C}{R_{thJC} \times V_{CE(sat)(\max)}\left(T_{J(\max)}, I_C(T_C)\right)}$
2. *V_{clamp} = 80% V_{CES}, T_J =150 °C, R_G = 10 Ω, V_{GE} = 15 V.*
3. *Pulse width limited by maximum junction temperature.*

Table 2. Thermal data

Symbol	Parameter	Value	Unit
R_{thJC}	Thermal resistance, junction-to-case IGBT	1.9	°C/W
	Thermal resistance, junction-to-case diode	4	
R_{thJA}	Thermal resistance, junction-to-ambient	62.5	°C/W

2 Electrical characteristics

T_C = 25 °C unless otherwise specified

Table 3. Static

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$V_{(BR)CES}$	Collector-emitter breakdown voltage	V_{GE} = 0 V, I_C = 1 mA	600			V
$V_{CE(sat)}$	Collector-emitter saturation voltage	V_{GE} = 15 V, I_C = 5 A		1.9	2.5	V
		V_{GE} = 15 V, I_C = 5 A, T_J = 150 °C		1.7		
$V_{GE(th)}$	Gate threshold voltage	V_{CE} = V_{GE}, I_C = 250 µA	4.5		6.5	V
I_{CES}	Collector cut-off current	V_{GE} = 0 V, V_{CE} = 600 V			0.15	mA
		V_{GE} = 0 V, V_{CE} = 600 V, T_J = 125 °C (1)			1	
I_{GES}	Gate-emitter leakage current	V_{CE} = 0 V, V_{GE} = ±20 V			±100	nA
g_{fs} (2)	Forward transconductance	V_{CE} = 15 V, I_C = 5 A		3.5		S

1. *Specified by design, not tested in production.*
2. *Pulsed: pulse duration = 300 µs, duty cycle 1.5%.*

Table 4. Dynamic

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
C_{ies}	Input capacitance	V_{CE} = 25 V, f = 1 MHz, V_{GE} = 0 V	-	365	-	pF
C_{oes}	Output capacitance		-	43	-	pF
C_{res}	Reverse transfer capacitance		-	8.3	-	pF
Q_g	Total gate charge	V_{CC} = 390 V, I_C = 5 A, V_{GE} = 0 to 15 V (see Figure 18. Gate charge test circuit)	-	19.2	-	nC
Q_{ge}	Gate-emitter charge		-	4.5	-	nC
Q_{gc}	Gate-collector charge		-	7	-	nC

Table 5. Switching on/off (inductive load)

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$t_{d(on)}$	Turn-on delay time	V_{CC} = 390 V, I_C = 5 A,	-	14.2	-	ns
t_r	Current rise time	R_G = 10 Ω, V_{GE} = 15 V	-	5	-	ns
$(di/dt)_{on}$	Turn-on current slope	(see Figure 16. Test circuit for inductive load switching and Figure 19. Switching waveform)	-	1000	-	A/µs
$t_{d(on)}$	Turn-on delay time	V_{CC} = 390 V, I_C = 5 A,	-	14	-	ns
t_r	Current rise time	R_G = 10 Ω, V_{GE} = 15 V, T_J = 125 °C	-	5	-	ns
$(di/dt)_{on}$	Turn-on current slope	(see Figure 16. Test circuit for inductive load switching and Figure 19. Switching waveform)	-	920	-	A/µs
$t_r(V_{off})$	Off voltage rise time	V_{CC} = 390 V, I_C = 5 A,	-	27	-	ns
$t_{d(off)}$	Turn-off delay time	R_G = 10 Ω, V_{GE} = 15 V	-	72	-	ns
t_f	Current fall time	(see Figure 16. Test circuit for inductive load switching and Figure 19. Switching waveform)	-	85	-	ns
$t_r(V_{off})$	Off voltage rise time	V_{CC} = 390 V, I_C = 5 A,	-	50	-	ns
$t_{d(off)}$	Turn-off delay time	R_G = 10 Ω, V_{GE} = 15 V, T_J = 125 °C	-	108	-	ns
t_f	Current fall time	(see Figure 16. Test circuit for inductive load switching and Figure 19. Switching waveform)	-	139	-	ns

Table 6. Switching energy (inductive load)

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
E_{on} (1)	Turn-on switching energy	V_{CE} = 390 V, I_C = 5 A,	-	31.8	-	µJ
E_{off} (2)	Turn-off switching energy	R_G = 10 Ω, V_{GE} = 15 V	-	95	-	µJ
E_{ts}	Total switching energy	(see Figure 16. Test circuit for inductive load switching	-	126.8	-	µJ
E_{on} (1)	Turn-on switching energy	V_{CE} = 390 V, I_C = 5 A,	-	61.8	-	µJ
E_{off} (2)	Turn-off switching energy	R_G = 10 Ω, V_{GE} = 15 V, T_J = 125 °C	-	173	-	µJ
E_{ts}	Total switching energy	(see Figure 16. Test circuit for inductive load switching	-	234.8	-	µJ

1. *Including the reverse recovery of the diode.*
2. *Including the tail of the collector current.*

Table 7. Diode switching characteristics (inductive load)

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
V_F	Forward on-voltage	I_F = 5 A	-	2	2.45	V
		I_F= 5 A, T_J=125 °C	-	1.7		
t_{rr}	Reverse recovery time	I_F = 5 A, V_R = 40 V, di/dt = 100 A/µs (see Figure 17. Diode reverse recovery waveform)	-	22		ns
Q_{rr}	Reverse recovery charge		-	14		nC
I_{rrm}	Reverse recovery current		-	1.3		A
t_{rr}	Reverse recovery time	I_F = 5 A, V_R = 40 V, di/dt = 100 A/µs, T_J = 125 °C (see Figure 17. Diode reverse recovery waveform)	-	33		ns
Qrr	Reverse recovery charge		-	30		nC
I_{rr}	Reverse recovery current		-	1.85		A

2.1 Electrical characteristics (curves)

Figure 1. Typical output characteristics



Figure 2. Typical transfer characteristics



Figure 3. Typical transconductance characteristics



Figure 4. Typical collector-emitter on voltage vs temperature



Figure 5. Typical gate charge characteristics



Figure 6. Typical capacitance characteristics



Figure 7. Normalized gate threshold vs temperature



Figure 8. Typical collector-emitter on voltage vs collector current



Figure 9. Normalized breakdown voltage vs temperature



Figure 10. Typical switching energy vs temperature



Figure 11. Typical switching energy vs gate resistance



Figure 12. Typical switching energy vs collector current



Figure 13. Normalized transient thermal impedance



Figure 14. Safe operating area



Figure 15. Emitter-collector diode characteristics



3 Test circuits

Figure 16. Test circuit for inductive load switching



Figure 17. Diode reverse recovery waveform



Figure 18. Gate charge test circuit



Figure 19. Switching waveform



4 Package information

To meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions, and product status are available at: www.st.com. ECOPACK is an ST trademark.

4.1 D²PAK (TO-263) type B package information

Figure 20. **D²PAK (TO-263) type B package outline**



0079457_26_B

Table 8. **D²PAK (TO-263) type B mechanical data**

Dim.	mm		
	Min.	Typ.	Max.
A	4.36		4.56
A1	0		0.25
b	0.70		0.90
b1	0.51		0.89
b2	1.17		1.37
c	0.38		0.694
c1	0.38		0.534
c2	1.19		1.34
D	8.60		9.00
D1	6.90		7.50
E	10.15		10.55
E1	8.10		8.70
e	2.54 BSC		
H	15.00		15.60
L	1.90		2.50
L1			1.65
L2			1.78
L3		0.25	
L4	4.78		5.28

Figure 21. **D²PAK (TO-263) recommended footprint (dimensions are in mm)**



4.2 TO-220 type A package information

Figure 22. **TO-220 type A package outline**



Table 9. **TO-220 type A package mechanical data**

Dim.	mm		
	Min.	Typ.	Max.
A	4.40		4.60
b	0.61		0.88
b1	1.14		1.55
c	0.48		0.70
D	15.25		15.75
D1		1.27	
E	10.00		10.40
e	2.40		2.70
e1	4.95		5.15
F	1.23		1.32
H1	6.20		6.60
J1	2.40		2.72
L	13.00		14.00
L1	3.50		3.93
L20		16.40	
L30		28.90	
øP	3.75		3.85
Q	2.65		2.95
Slug flatness		0.03	0.10

4.3 D²PAK packing information

Figure 23. **D²PAK tape drawing (dimensions are in mm)**



DM01095771_1

Revision history

Table 10. **Document revision history**

Date	Revision	Changes
30-Jan-2006	1	Initial release
06-Nov-2006	2	Complete version.
08-Feb-2007	3	The document has been reformatted
05-Oct-2007	4	Added TO-220FP, *Table 2* has been updated
16-Dec-2008	5	Added DPAK package
05-May-2025	6	The part numbers STGD10NC60HD and STGF10NC60HD have been removed and the document has been updated accordingly. Updated Section 4: Package information.

Contents

1 **Electrical ratings** 2
2 **Electrical characteristics** 3
2.1 Electrical characteristics (curves) 5
3 **Test circuits** 8
4 **Package information** 9
4.1 D²PAK (TO-263) type B package information 9
4.2 TO-220 type A package information 11
4.3 D²PAK packing information 13
Revision history 14

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2025 STMicroelectronics – All rights reserved