
The BlueNRG-1 device limitations

Silicon identification

This errata sheet applies to the following STMicroelectronics BlueNRG-1 devices:

Order code	Package	Identification information of the device ⁽¹⁾	Device cut
BlueNRG-132	QFN32	0x00000111	1.1
BlueNRG-132	QFN32	0x00000113	1.3
BlueNRG-134	WLCSP34	0x00000111	1.1
BlueNRG-134	WLCSP34	0x00000113	1.3

1. Value as read from register CKGEN_SOC - DIE_ID register (0x4090001C)

Note: For each device limitation the following information is provided:

- *Part number affected: which device and cut is affected by the limitation (the devices and cuts not reported are not affected by it)*
- *Description: limitation description*
- *Impact: limitation impact*
- *Workaround: possible workaround if any*

1 Limitations

1.1 Reduced operating voltage range when brown-out reset (BOR) is enabled

Part number affected: the BlueNRG-132 cut 1.1 and the BlueNRG-134 cut 1.1.

Description: when brown-out reset (BOR) is enabled the operating voltage of the device is reduced to 2.1-3.6 V.

Impact: brown-out reset (BOR) threshold prevents the device from being safely used below 2.1 V.

Workaround: the application using brown-out reset (BOR) must restrict operating range to 2.1 V.

1.2 Brown-out reset (BOR) is not enabled by default

Part numbers affected: the BlueNRG-132 cut 1.1 and the BlueNRG-134 cut 1.1.

Description: the device brown-out reset (BOR) is not enabled by default.

Impact: brown-out reset (BOR) activation requires a software action.

Workaround: brown-out reset (BOR) can be enabled by the software by setting the BOR_CONFIG=BOR_ON preprocessor option in STSW-BLUENRG1-DK (BlueNRG-1, BlueNRG-2 DK SW package).

1.3 Bit pattern could cause SWD interface not to work

Part numbers affected: the BlueNRG-132 cut 1.1 and the BlueNRG-134 cut 1.1.

Description: During debug connection via serial wire debugger (SWD) port, if a specific bit pattern is sent/received to/from the SWDIO pin, the chip could not answer anymore subsequent SWD requests, thus breaking the connection. The bit pattern represented as 32 bit word is 0x39E6xxxx.

Impact: using serial wire debugger (SWD) during development and/or production to program the Flash memory can cause some issues if the Flash memory image contains a particular pattern.

Workaround: none.

1.4 Aux ADC end of calibration interrupt flag cannot be cleared

Part numbers affected: the BlueNRG-132 cut 1.1 and the BlueNRG-134 cut 1.1.

Description: the ADC end of calibration interrupt flag cannot be cleared, so it cannot be used. STATUS register includes end of calibration information in bit 2.

Impact: no specific issue, since the interrupt of end of calibration does not have a practical use in the real application scenario.

Workaround: since the end of calibration bit cannot be used, keep the interrupt mask bit associated disabled. There is no interest in such bit.

1.5 ADC WDOG status flag / interrupt cannot be cleared

Part numbers affected: the BlueNRG-132 cut 1.1 and the BlueNRG-134 cut 1.1.

Description: Aux ADC WDOG status flag / interrupt cannot be cleared.

Impact: Aux ADC WDOG IRQ is not usable.

Workaround: none.

1.6 ADC does not work properly when a 32 MHz system clock is being used

Part numbers affected: the BlueNRG-132 cut 1.1, cut 1.3 and the BlueNRG-134 cut 1.1, 1.3.

Description: ADC IP does not work properly with a system clock at 32 MHz.

Impact: ADC cannot be used with a system clock at 32 MHz.

Workaround: the application, using a 32 MHz quartz and accessing ADC, should configure system clock to 16 MHz.

1.7 ADC SNR degradation

Part numbers affected: the BlueNRG-132 cut 1.1, and the BlueNRG-134 cut 1.1.

Description: ADC SNR may be randomly degraded depending on ADC clock generator start-up.

Impact: SNR degradation is in the range of 6 dB, therefore the effective number of bit of the ADC is reduced by 1 bit.

Workaround: in case of static signal, multiple acquisitions and averaging allow ADC accuracy to be recovered.


1.8 ADC unwanted aliased signal after the decimation filter

Part numbers affected: the BlueNRG-132 cut 1.1, cut 1.3 and the BlueNRG-134 cut 1.1, 1.3.

Description: the bandwidth of the anti-aliasing filter is slightly broader with respect to the signal bandwidth, potentially thus generating unwanted aliased signal after the decimation filter.

Impact: When a pure sine wave, generated in the $[F_s/2; 1.25 \cdot F_s/2]$ range, is being sampled, user can notice an attenuated aliased sine wave in the $[0.75 \cdot F_s/2; F_s/2]$ range.

Figure 1. Interpolation filter frequency response



In case of waveform acquisition, especially when audio speech and music is caught, no further degradation has been identified.

F_s is the sampling frequency on the output of the downsampling filter, described as ADC data rate in the datasheet.

Workaround: by choosing an appropriate oversampling factor (OSR), so that maximum frequency of the sampled signal is lower than $F_s/2$, aliasing may be avoided.

Revision history

Table 1. Document revision history

Date	Version	Changes
29-Jan-2019	1	Initial release.

Contents

1	Limitations	2
1.1	Reduced operating voltage range when brown-out reset (BOR) is enabled	2
1.2	Brown-out reset (BOR) is not enabled by default	2
1.3	Bit pattern could cause SWD interface not to work	2
1.4	Aux ADC end of calibration interrupt flag cannot be cleared	2
1.5	ADC WDOG status flag / interrupt cannot be cleared	2
1.6	ADC does not work properly when a 32 MHz system clock is being used	2
1.7	ADC SNR degradation	2
1.8	ADC unwanted aliased signal after decimation filter	3
	Revision history	4

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2019 STMicroelectronics – All rights reserved