

Document reference:	PCB reference:
<b>STEVAL-IKR002V1D</b>	
Company: <b>STMicroelectronics</b>	

Item	Quantity	Reference	Part / Value	Note	Package	Manufacturer	Manufacturer's ordering code / Orderable Part Number	169 MHz
1	2	C0, C16	C_100n_0402_X7R	Decoupling cap on VREG (pin # 17)	SM/C_0402	Murata	GRM155R71C104KA88D	100nF
2	1	C1	C_TBD_0402_C0G	TX LPF first cap shunt	SM/C_0402	Murata	GRM1555C1H180JZ01	18pF
3	1	C2	C_TBD_0402_C0G	TX LPF second cap shunt	SM/C_0402	Murata	GRM1555C1H270JZ01	27pF
4	1	C3	C_TBD_0402_C0G	TX LPF third cap shunt	SM/C_0402	Murata	GRM1555C1H4R3DZ01	4.3pF
5	1	C4	C_TBD_0402_C0G	RXP Balun shunt cap	SM/C_0402			NE
6	1	C8	C_TBD_0402_C0G	DC block for Antenna	SM/C_0402	Murata	GRM1555C1H391JA01	390pF
7	1	C14	C_TBD_0402_C0G	Additional notch filter cap	SM/C_0402	Murata	GRM1555C1H221JA01	220pF
8	1	C15	C_TBD_0402_C0G	PA load capacitor	SM/C_0402	Murata	GRM1555C1H6R2DZ01	6.2pF
9	1	C5	C_TBD_0402_C0G	RXN Balun series	SM/C_0402	Murata	GRM1555C1H8R0DZ01	8pF
10	1	C6	C_TBD_0402_C0G	DC block for RX	SM/C_0402	Murata	GRM1555C1H221JA01	220pF
11	1	C7	C_TBD_0402_C0G	Matching and filtering	SM/C_0402	Murata	LQG15HN68NJ02	68nH
12	1	C9	C_12P_0402_C0G	XTAL load cap (Xout)	SM/C_0402	Murata	GRM1555C1H120JZ01	12pF
13	1	C10	C_10P_0402_C0G	XTAL load cap (Xin)	SM/C_0402	Murata	GRM1555C1H100JZ01	10pF
14	2	C11, C20	C_1U_0603_X7R	VBAT & SMPS OUT filter cap	SM/C_0603	Murata	GRM188R60J105KA01D	1uF
15	1	C12	C_100n_0402_X7R	SMPS OUT filter cap	SM/C_0402	Murata	GRM155R71C104KA88D	100nF
16	1	C13	C_TBD_0402_X7R	SMPS OUT filter cap	SM/C_0402	Murata	GRM1555C1H561JA01D	560pF
17	1	C19	C_TBD_0402_C0G	VBAT filtering	SM/C_0402	Murata	GRM155R71C103KA01	10nF
18	1	C21	C_100p_0402_C0G	VBAT bypass capacitors	SM/C_0402	Murata	GRM1555C1H101JZ01D	100pF
19	1	C22	C_330p_0402_C0G	Decoupling cap on VREG (pin # 17)	SM/C_0402	Murata	GRM1555C1H331JA01D	330pF
20	1	J1	RF_IN/OUT	SMA Jack Assembly, End Launch	SMA-LAT	Emerson	142-0701-881	
21	2	J6, J7	HEADER 5X2	Male Strip 2X5, 100 mils, BOTTOM MOUNT	WALCON.100/VH/T M20E/W.325/10/M OD			
22	1	D0	L_TBD_0402	TX PA choke	SM/L_0402	Coilcraft	0402HL-471XJR	470nH
23	1	L1	L_TBD_0402	TX LPF first series ind	SM/L_0402	Coilcraft	0402CS-39N	39nH
24	1	L2	L_TBD_0402	TX LPF second series ind	SM/L_0402	Coilcraft	0402CS-56N	56nH
25	1	L3	L_TBD_0402	TX LPF third series ind	SM/L_0402	Murata	GRM1555C1H3R6DZ01	3.6pF
26	1	L4	L_TBD_0402	RXP Balun series ind	SM/L_0402	Murata	LQG15HNR10J02	100nH
27	1	L5	L_TBD_0402	RXN Balun shunt ind	SM/L_0402	Murata	LQG15HN47NJ02	47nH
28	1	L6	L_TBD_0402	RX Balun compensation ind	SM/L_0402			NE
29	1	L8	L_TBD_0402	SMPS out inductor	SM/L_0402	Coilcraft	0402HL-471XJR	470nH

30	1	L9	L_TBD_0402	Additional notch filter ind	SM/L_0402	Coilcraft	0402CS-51N	51nH
31	1	L7	L_10U_0805	SMPS out inductor	SM/L_0805	Murata	LQM21FN100M70L	10uH
32	1	R6	R_ORO_0402	USED TO IDENTIFY BAND: mount only 1 ORO resistor according to assembly options	SM/R_0402	Tyco Electronics	CRG0402ZR	OR0
33	1	R7	R_ORO_0402		SM/R_0402	Tyco Electronics		NE
34	1	R8	R_ORO_0402		SM/R_0402	Tyco Electronics		NE
35	1	R9	R_ORO_0402		SM/R_0402	Tyco Electronics		NE
36	1	R10	R_ORO_0402		SM/R_0402	Tyco Electronics		NE
37	1	R12, R13, R14	R_ORO_0402		SM/R_0402	Tyco Electronics	CRG0402F100K	100k
38	1	U1	SPIRIT1	RF IC	QFN20_REV3	STMicroelectronics		
39	1	U2	HEADER 1X2	Male Strip 1X2, 100 mils	WALCON.100/VH/T M20E/W.325/10/M OD			
40	1	U3	EEPROM	Memory	SO8N	STMicroelectronics	M95640-RMN6P	
41	1	Y1	XTAL	XTAL	XTAL_32_25_REV2	NDK	NX3225GA 25MHz EXS00A-CG03242	25 MHz