

S2-LP RF PCB STEVAL-FKI433V1 (430-470 MHz)							
BOM							
Item	Quantity	Reference	Value	Note	Package	Manufacturer	Part Number
1	1	C9	100nF	Decoupling cap	SM/C_0402	Murata	GRM155R71C104KA88D
2	5	C3, C5, C7, C10, C30	470nF	Decoupling cap	SM/C_0402	Murata	GRM155R61A474KE15
3	1	C12	1uF	SMPS OUT filter cap	SM/C_0603	Murata	GRM188R60J105KA01D
4	1	C1	4.7uF	VBAT filter	SM/C_0603	Murata	GRM188R60J475KE19
5	12	C4, C6, C8, C11, C14, C16, C17, C21, C23, C31, C33, C35	100pF	VBAT bypass capacitors	SM/C_0402	Murata	GRM1555C1H101JZ01D
6	2	C19, C20	12pF	XTAL load cap (Xout)	SM/C_0402	Murata	GRM1555C1H120JZ01
7	2	C13, C18	4.7pF	RXP Balun shunt cap	SM/C_0402	Murata	GRM1555C1H4R7CZ01
8	1	C27	3.3pF	TX LPF third cap shunt	SM/C_0402	Murata	GRM1555C1H3R3CZ01
9	1	C28	8.2pF	TX LPF third cap shunt	SM/C_0402	Murata	GRM1555C1H8R2DZ01
10	1	C24	1.0pF	TX LPF third cap shunt	SM/C_0402	Murata	GRM1555C1H1R0CZ01
11	1	C29	6.8pF	TX LPF third cap shunt	SM/C_0402	Murata	GRM1555C1H6R8BA01
12	1	C25	470pF	VREFVCO filter	SM/C_0402	Murata	GRM1555C1H471JA01
13	2	C15, C26	Not assembled	TX LPF first cap shunt	SM/C_0402		
14	4	C2, C22, C32, C34	150nF	Filter	SM/C_0402	Murata	GRM155R61A154KE19
15	1	J1	RF_IN/OUT	SMA Jack Assembly, End Launch	SMA-LAT	Emerson	142-0701-881
16	1	L4	56nH	TX LPF first series ind	SM/L_0402	Murata	LQG15HS56NJ02
17	1	L2	10uH	SMPS out inductor	SM/L_0805	Murata	LQM21FN100M70L
18	2	L3, L5	27nH	TX LPF third series ind	SM/L_0402	Murata	LQG15HS27NJ02
19	1	L6	0R0 (resistor)	TX LPF first series ind	SM/L_0402	Tyco Electronics	CRG0402ZR
20	1	L1	150nH		SM/L_0402		LQG15HSR15J02
21	1	L7	27nH	TX choke	SM/L_0603	Murata	LQW18AN27NG00
22	1	L8	2.7nH	SMPS out inductor	SM/L_0402	Murata	LQW15AN2N7C00
23	1	L9	30nH	Additional notch filter ind	SM/L_0402	Murata	LQW15AN30NH00
24	1	L10	22nH	SMPS out inductor	SM/L_0805	Murata	LQW15AN22NH00
25	3	R1, R2, R3	100k		SM/R_0402	Tyco Electronics	CRG0402F100K
26	7	R6, R9, R17, R18, R19, R20, R22	Not assembled		SM/R_0402	Tyco Electronics	
27	11	R4, R5, R7, R10, R11, R12, R13, R14, R15, R16, R21	0R0 (resistor)		SM/R_0402	Tyco Electronics	CRG0402ZR
28	1	CN1	Extra-long 10 pins female-male strip	female side mounted to the top	2.54 mm pitch	4UCON	18688
29	2	CN2, CN3	Extra-long 8 pins female-male strip	female side mounted to the top	2.54 mm pitch	4UCON	18688
30	1	CN4	Extra-long 6 pins female-male strip	female side mounted to the top	2.54 mm pitch	4UCON	18688
31	1	JP1	HEADER 1X2	Male Strip 1X2, 100 mils	WALCON.100/VH/TM2OE /W.325/10/MOD		
32	1	Vsmgs_ext	Not	Test point	TP		
33	1	U1	EEPROM	Memory	SO8N	STMicroelectronics	M95640-RMN6
34	1	U2	S2-LP	RF IC	QFN20_REV3	STMicroelectronics	
35	1	Y1	50 MHz	XTAL	NX1612SA	NDK	NX1612SA 50MHz EXS00A-CS08403
36	1		ANT-433MR Right angle	430-470MHz Flexible Whip Antenna		LPRS	
37	1		Nucleo-L152RE			STMicroelectronics	

April 19, 2016