

X-NUCLEO-IHM01A1

<i>Value</i>	<i>Quantity</i>	<i>Description</i>	<i>Part Number</i>	<i>Manufacturer</i>	<i>Part Number</i>
100NF	5	CAP CER 100nF 50V X7R 0603	100NF_50V_X7R_0603		
47UF	1	CAP TANT 47UF 6V3 10% PACK-A	47UF_6V3_TANT_PACK-A		
220NF	1	CAP CER 220nF 35V X7R 0603	220NF_35V_X7R_0603		
3.3NF	1	CAP CER 3.3nF 50V X7R 0603	3.3NF_50V_X7R_0603		
NP	1	CAP NP 0603	C_NP_0603		
10UF	1	CAP TANT 10uF 6V3 10% PACK-A	10UF_6V3_TANT_PACK-A		
10NF	1	CAP CER 10nF 50V X7R 0603	10NF_50V_X7R_0603		
100UF	1	CAP ALU 100uF 63V SMD-PACK-G	EEEFK1J101P	PANASONIC	EEEFK1J101P
MKDS1/6-3.81	1	Screw connector 6 poles MKDS 1/6-3.81	MKDS1/6-3.81	PHOENIX CONTACT	MKDS1/6-3.81
CON-1x2	1	THOUGH-HOLE-1x2-Pin height 14.8 - Body 8.5mn - picth 2.54	SSQ-102-04-F-S	SAMTEC	SSQ-102-04-F-S
CON-1x10	1	THOUGH-HOLE-1x10-Pin height 14.8 - Body 8.5mn - picth 2.54	SSQ-110-04-F-S	SAMTEC	SSQ-110-04-F-S
CON-1x8	2	THOUGH-HOLE-1x8-Pin height 14.8 - Body 8.5mn - picth 2.54	SSQ-108-04-F-S	SAMTEC	SSQ-108-04-F-S
CON-2x19	2	THOUGH-HOLE-2x19-Pin height 14.8 - Body 8.5mn - picth 2.54	SSQ-119-04-L-D	SAMTEC	SSQ-119-04-L-D
CON-1x6	1	THOUGH-HOLE-1x6-Pin height 14.8 - Body 8.5mn - picth 2.54	SSQ-106-04-F-S	SAMTEC	SSQ-106-04-F-S
BAR43	1	Double Diode High Speed Switching Diode	BAR43	ST	BAR43SFILM
RED	1	LED RED - 0805 -2mcd - 621nm	LED_RED	LITE-ON	LTST-C170-EKT
YELLOW	4	LED YELLOW - 0805 -6mcd - 588nm	LED_YELLOW	LITE-ON	LTST-C170-YKT
GREEN	1	LED GREEN - 0805 -6mcd - 569nm	LED_GREEN	LITE-ON	LTST-C170-GKT
OPTICAL_TARGET	3	OPTICAL_TARGET	OPTICAL_TARGET		
OR	6	RES 0 OHM 5% 1/8W 0805	OR_5%_0805		
NP	11	RES NP 0805	R_NP_0805		
10K	2	RES 10K OHM 5% 1/10W 0603 SMD	10K_5%_0603		
2.2K	4	RES 2.2K OHM 5% 1/10W 0805 SMD	2.2K_5%_0805		
330R	2	330R OHM 5% 1/10W	330R_5%_0603		
NP	2	TEST POINT RED	KEYSTONE 5000_NP	KEYSTONE	KEYSTONE 5000
L6474PD	1	easySPIN MICROSTEPPING MOTOR DRIVEN	L6474PD	ST	L6474PD