

**BUL416**

HIGH VOLTAGE FAST-SWITCHING NPN POWER TRANSISTOR

- n STMicroelectronics PREFERRED SALES TYPE
- n NPN TRANSISTOR
- n HIGH VOLTAGE CAPABILITY
- n VERY HIGH SWITCHING SPEED
- n FULLY CHARACTERISEZ AT 125 °C
- n LOW SPREAD OF DYNAMIC PARAMETERS



APPLICATIONS

- n ELECTRONIC BALLAST FOR FLUORESCENT LIGHTING
- n SWITCH MODE POWER SUPPLIES

DESCRIPTION

The device is manufactured using high voltage Multi-Epitaxial Mesa technology for cost-effective high performance. It uses a Hollow Emitter structure to enhance switching speed.

The BUL series is designed for use in lighting applications and low cost switch-mode power supplies.

Figure 1: Package**Figure 2: Internal Schematic Diagram****Table 1: Order Codes**

Part Number	Marking	Package	Packaging
BUL416	BUL416A or (#) BUL416B	TO-220	Tube

See note on page 2

Table 2: Absolute Maximum Ratings

Symbol	Parameter	Value	Unit
V_{CES}	Collector-Emitter Voltage ($V_{BE} = 0$)	1600	V
V_{CEO}	Collector-Emitter Voltage ($I_B = 0$)	800	V
V_{EBO}	Emitter-Base Voltage ($I_C = 0$)	9	V
I_C	Collector Current	6	A
I_{CM}	Collector Peak Current ($t_p < 5ms$)	9	A
I_B	Base Current	5	A
I_{BM}	Base Peak Current ($t_p < 5ms$)	8	A
P_{tot}	Total Dissipation at $T_C = 25\text{ °C}$	110	W
T_{stg}	Storage Temperature	-65 to 150	°C

Symbol	Parameter	Value	Unit
T_J	Max. Operating Junction Temperature	150	°C

Table 3: Thermal Data

$R_{thj-case}$	Thermal Resistance Junction-Case	Max	1.14	°C/W
$R_{thj-amb}$	Thermal Resistance Junction-Ambient	Max	62.5	°C/W

Table 4: Electrical Characteristics ($T_{case} = 25\text{ °C}$ unless otherwise specified)

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
I_{CES}	Collector Cut-off Current ($V_{BE} = 0\text{ V}$)	$V_{CE} = 1600\text{ V}$ $V_{CE} = 1600\text{ V}$ $T_J = 125\text{ °C}$			100 500	μA μA
I_{CEO}	Collector Cut-off Current ($I_B = 0$)	$V_{CE} = 800\text{ V}$			250	μA
$V_{CEO(sus)}^*$	Collector-Emitter Sustaining Voltage ($I_B = 0$)	$I_C = 100\text{ mA}$ $L = 25\text{ mH}$	800			V
V_{EBO}	Emitter-Base Voltage ($I_C = 0$)	$I_E = 10\text{ mA}$	9			V
$V_{CE(sat)}^*$	Collector-Emitter Saturation Voltage	$I_C = 2\text{ A}$ $I_B = 0.4\text{ A}$ $I_C = 4\text{ A}$ $I_B = 1.33\text{ A}$			1.5 3	V V
$V_{BE(sat)}^*$	Base-Emitter Saturation Voltage	$I_C = 2\text{ A}$ $I_B = 0.4\text{ A}$ $I_C = 4\text{ A}$ $I_B = 1.33\text{ A}$			1.2 1.5	V V
h_{FE}^*	DC Current Gain	$I_C = 10\text{ mA}$ $V_{CE} = 5\text{ V}$ $I_C = 0.7\text{ A}$ $V_{CE} = 5\text{ V}$ Group A Group B	10 12 25		27 40	
t_s t_f	INDUCTIVE LOAD Storage Time Fall Time	$I_C = 3\text{ A}$ $I_{B1} = 1\text{ A}$ $V_{BE(off)} = -5\text{ V}$ $R_{BB} = 0\text{ }\Omega$ $V_{clamp} = 200\text{ V}$ $L = 200\text{ }\mu\text{H}$ (see figure 12)		2.3 650		μs ns
t_s t_f	INDUCTIVE LOAD Storage Time Fall Time	$I_C = 3\text{ A}$ $I_{B1} = 1\text{ A}$ $V_{BE(off)} = -5\text{ V}$ $R_{BB} = 0\text{ }\Omega$ $V_{clamp} = 200\text{ V}$ $L = 200\text{ }\mu\text{H}$ $T_J = 100\text{ °C}$ (see figure 12)		3 680		μs ns

* Pulsed: Pulsed duration = 300 μs , duty cycle $\leq 1.5\%$.

Note: Product is pre-selected in DC current gain (Group A and Group B). STMicroelectronics reserves the right to ship either groups according to production availability. Please contact your nearest STMicroelectronics sales office for delivery details.

Figure 3: Safe Operating Area




Figure 4: DC Current Gain




Figure 5: Collector-Emitter Saturation Voltage




Figure 6: Derating Curve




Figure 7: DC Current Gain




Figure 8: Base-Emitter Saturation Voltage




Figure 9: Inductive Load Fall Time




Figure 11: Resistive Load Storage Time




Figure 10: Reverse Biased SOA





Figure 12: Inductive Load Switching Test Circuit



TO-220 MECHANICAL DATA

DIM.	mm.			inch		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A	4.40		4.60	0.173		0.181
b	0.61		0.88	0.024		0.034
b1	1.15		1.70	0.045		0.066
c	0.49		0.70	0.019		0.027
D	15.25		15.75	0.60		0.620
E	10		10.40	0.393		0.409
e	2.40		2.70	0.094		0.106
e1	4.95		5.15	0.194		0.202
F	1.23		1.32	0.048		0.052
H1	6.20		6.60	0.244		0.256
J1	2.40		2.72	0.094		0.107
L	13		14	0.511		0.551
L1	3.50		3.93	0.137		0.154
L20		16.40			0.645	
L30		28.90			1.137	
øP	3.75		3.85	0.147		0.151
Q	2.65		2.95	0.104		0.116




Table 5:

Version	Release Date	Change Designator
14-Jan-2004	1	First Release.
09-Sep-2004	2	Second Release.
26-Jan-2005	3	Third Release.

Obsolete Product(s) - Obsolete Product(s)
Obsolete Product(s) - Obsolete Product(s)

Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences or use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

The ST logo is a registered trademark of STMicroelectronics
All other names are the property of their respective owners

© 2005 STMicroelectronics - All Rights Reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan -
Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America
www.st.com