



High reliability 60 V, 0.5 A NPN transistor



LCC-3

UB

Pin 4 in UB is connected to the metallic lid.



DS10450

Features

V_{ce0}	$I_C(\text{max.})$	H_{FE} at 10 V, 150 mA	$T_j(\text{max.})$
60 V	0.5 A	> 250	200 °C

- Hermetic packages
- ESCC qualified

Description

The 2N2484HR is a bipolar transistor able to operate under severe environment conditions.

Qualified as per ESCC 5201/001 specification and available in LCC-3 and UB hermetic packages, it is specifically recommended for space and harsh environment applications and suitable for low current and high precision circuits such as preamplifiers, oscillators, current mirror configuration.

Product summary

Product status link
2N2484HR

Part-number	Screening options	Agency specification	Package
2N2484UBx	Engineering and flight models	ESCC 5201/001	UB
SOC2484HRx			LCC-3

Note: See [Table 7](#) for ordering information.

1 Electrical ratings

Table 1. Absolute maximum ratings

Symbol	Parameter		Value	Unit
V_{CBO}	Collector-base voltage ($I_E = 0$)		60	V
V_{CEO}	Collector-emitter voltage ($I_B = 0$)		60	V
V_{EBO}	Emitter-base voltage ($I_C = 0$)		6	V
I_C	Collector current		0.5	A
P_{TOT}	Total dissipation at $T_{amb} \leq 25\text{ °C}$	LCC-3 and UB	0.36	W
		LCC-3 and UB ⁽¹⁾	0.73	
T_{OP}	Operating temperature range		-65 to 200	°C
T_J	Max. operating junction temperature		200	°C

1. When mounted on a 15 x 15 x 0.6 mm ceramic substrate.

Table 2. Thermal data

Symbol	Parameter	LCC-3 and UB Value	Unit
RthJA	Thermal resistance junction-ambient (max)	486	°C/W
	Thermal resistance junction-ambient (max)	240 ⁽¹⁾	

1. When mounted on a 15 x 15 x 0.6 mm ceramic substrate.

2 Electrical characteristics

Table 3. Electrical characteristics ($T_{amb} = 25\text{ °C}$ unless otherwise specified)


Symbol	Parameter	Test conditions ⁽¹⁾	Min.	Max.	Unit
I_{CBO}	Collector-base cut-off current ($I_E = 0$)	$V_{CB} = 45\text{ V}$		10	nA
		$V_{CB} = 45\text{ V}$, $T_{amb} = 150\text{ °C}$		10	μA
I_{EBO}	Emitter-base cut-off current ($I_C = 0$)	$V_{EB} = 5\text{ V}$		10	nA
$V_{(BR)CBO}$	Collector-base breakdown voltage ($I_E = 0$)	$I_C = 10\text{ }\mu\text{A}$	60		V
$V_{(BR)CEO}^{(2)}$	Collector-emitter breakdown voltage ($I_B = 0$)	$I_C = 10\text{ mA}$	60		V
$V_{(BR)EBO}$	Emitter-base breakdown voltage ($I_C = 0$)	$I_C = 10\text{ }\mu\text{A}$	6		V
$V_{CE(sat)}^{(2)}$	Collector-emitter saturation voltage	$I_C = 1\text{ mA}$, $I_B = 0.1\text{ mA}$		0.35	V
$h_{FE}^{(2)}$	DC current gain	$I_C = 1\text{ }\mu\text{A}$, $V_{CE} = 5\text{ V}$	30		
		$I_C = 10\text{ }\mu\text{A}$, $V_{CE} = 5\text{ V}$	100	500	
		$I_C = 100\text{ }\mu\text{A}$, $V_{CE} = 5\text{ V}$	175	550	
		$I_C = 1\text{ mA}$, $V_{CE} = 5\text{ V}$	250	650	
		$I_C = 10\text{ mA}$, $V_{CE} = 5\text{ V}$		800	
		$I_C = 10\text{ }\mu\text{A}$, $T_{amb} = -55\text{ °C}$, $V_{CE} = 5\text{ V}$	20		
h_{fe}	High frequency, current gain 1	$I_C = 50\text{ }\mu\text{A}$, $f = 5\text{ MHz}$, $V_{CE} = 5\text{ V}$	3		
	High frequency, current gain 2	$I_C = 500\text{ }\mu\text{A}$, $f = 30\text{ MHz}$, $V_{CE} = 5\text{ V}$	2		
C_{obo}	Output capacitance, ($I_E = 0$)	$V_{CB} = 5\text{ V}$, $I_B = 0.1\text{ mA}$		6	pF
C_{ibo}	Input capacitance	$V_{EB} = 0.5\text{ V}$, $I_C = 0\text{ A}$, $f = 1\text{ MHz}$		6	V
h_{FE}	Small signal current gain	$I_C = 1\text{ mA}$, $V_{CE} = 5\text{ V}$, $f = 1\text{ kHz}$	150		900
h_{ie}	Small signal input impedance	$I_C = 1\text{ mA}$, $V_{CE} = 5\text{ V}$, $f = 1\text{ kHz}$	3.5	24	k Ω
h_{oc}	Small signal output impedance	$I_C = 1\text{ mA}$, $V_{CE} = 5\text{ V}$, $f = 1\text{ kHz}$		40	μmho
h_{re}	Small signal reverse voltage transfer ratio	$I_C = 1\text{ mA}$, $V_{CE} = 5\text{ V}$, $f = 1\text{ kHz}$		800	10^{-6}
N_{FW}	Wide-Band noise	$I_C = 10\text{ }\mu\text{A}$, $V_{CE} = 5\text{ V}$, $R_S = 10\text{ k}\Omega$		3	dB
NF_{N1}	Spot noise figure	$V_{CE} = 5\text{ V}$, $I_C = 10\text{ }\mu\text{A}$ $R_S = 10\text{ k}\Omega$, $f = 100\text{ Hz}$, power BW = 200 Hz		10	dB
NF_{N2}		$V_{CE} = 5\text{ V}$, $I_C = 10\text{ }\mu\text{A}$ $R_S = 10\text{ k}\Omega$, $f = 1\text{ Hz}$, power BW = 20 Hz		3	
NF_{N3}		$V_{CE} = 5\text{ V}$, $I_C = 10\text{ }\mu\text{A}$ $R_S = 10\text{ k}\Omega$, $f = 10\text{ Hz}$, power BW = 2 Hz		2	

1. Measurement performed on a sample basis, LTPD 7 or less.

2. Pulse measurement: Pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 1.0\%$

3 Test circuits

Figure 1. Circuit for electrical measurements



AM07818v1

Table 4. List of components

Component	Description
C1, C2, C5	3.0 - 35 pF
C3 ⁽¹⁾	24 pF
C4	0.4 - 7.0 pF
L1	Straight piece n° 16 bare tin wire, 5/8 inch long
L2	3 turns n° 16 wire, 1/4 inch ID, 5/16 inch long
L3	1 turn n° 18 wire, 1/4 inch ID, 1/4 inch long
L4	Ferrite rf choke, Z = 450 Ω


1. For optimum performance, C3 should be mounted as close as possible to the base lead.

4 Package information

To meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions, and product status are available at: www.st.com. ECOPACK is an ST trademark.

4.1 UB package information

Figure 2. UB package outline



Pad 1: Emitter

Pad 2: Base

Pad 3: Collector

Pad 4: Shielding connected to the lid


8206487

Table 5. UB package mechanical data

Symbols	Dimensions in mm			Dimensions in inches (for reference only)		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	1.17		1.42	0.045		0.056
C	0.46	0.51	0.56	0.018	0.020	0.022
D	0.56	0.76	0.96	0.024	0.030	0.036
E	0.92	1.02	1.12	0.036	0.040	0.044
F	1.95	2.03	2.11	0.077	0.080	0.083
G	2.92	3.05	3.18	0.115	0.120	0.125
I	2.41	2.54	2.67	0.095	0.100	0.105
J	0.42	0.57	0.72	0.0165	0.0225	0.0285
K	1.37	1.52	1.67	0.054	0.060	0.066
L	0.41	0.51	0.61	0.016	0.020	0.024
M	2.46	2.54	2.62	0.097	0.100	0.103
N	1.81	1.91	2.01	0.071	0.075	0.079
N1	0.91	0.96	1.02	0.036	0.038	0.040
r		0.20			0.008	
r1		0.30			0.012	
r2		0.56			0.022	

4.2 LCC-3 package information

Figure 3. LCC-3 package outline



0041211 rev.14

Table 6. LCC-3 package mechanical data

Symbols	Dimensions in mm			Dimensions in inches (for reference only)		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	1.16		1.42	0.046		0.056
C	0.45	0.50	0.56	0.018	0.020	0.022
D	0.56	0.76	0.96	0.022	0.030	0.038
E	0.91	1.01	1.12	0.036	0.040	0.044
F	1.95	2.03	2.11	0.077	0.080	0.083
G	2.92	3.05	3.17	0.115	0.120	0.125
I	2.41	2.54	2.66	0.095	0.100	0.105
J	0.42	0.57	0.72	0.0165	0.0225	0.0285
K	1.37	1.52	1.67	0.054	0.060	0.066
L	0.40	0.50	0.60	0.016	0.020	0.024
M	2.46	2.54	2.62	0.097	0.100	0.103
N	1.80	1.90	2.00	0.071	0.075	0.079
R		0.30			0.012	

5 Ordering information

Table 7. Ordering information

Part number	Agency specification	Screening options	Package	Mass	Lead finish	Marking ⁽¹⁾	Packing
2N2484UB1	-	Engineering model	UB	0.6 g	Gold	2N2484UB1	WafflePack
SOC24841	-		LCC-3			SOC24841	
2N2484UBG	5201/001/06	Flight model	UB			520100106	
2N2484UBT	5201/001/07		Solder Dip		520100107		
SOC2484HRG	5201/001/04	Flight model	LCC-3		Gold	520100104	
SOC2484HRT	5201/001/05				Solder Dip	520100105	

1. Specific marking only. The full marking includes in addition: For the Engineering Models: ST logo, date code; country of origin (FR). For ESCC flight parts: ST logo, date code, country of origin (FR), ESA logo, serial number of the part within the assembly lot.

Contact ST sales office for information about specific conditions for products in die form.



6 Other information

Table 8. Traceability and documentation

Screening type	Date code ⁽¹⁾	Documentation
Engineering model	3yywwN	Certificate of conformance
Flight model	yywwN	Certificate of conformance ESCC qualification maintenance lot reference

1. yy = year, ww = week number, N = lot index in the week.

Revision history

Table 9. Document revision history

Date	Revision	Changes
09-Jul-2010	1	Initial release.
26-Feb-2013	2	Updated: <i>Table 1: Device summary</i> and <i>Table 11: Order codes</i> .
01-Apr-2014	3	Updated: <i>Table 1: Device summary</i> and <i>Table 11: Order codes</i> . Minor text changes.
15-Mar-2021	4	Removed <i>TO-18 package information</i> . Minor text changes in the document title and description on the cover page.
11-Oct-2021	5	Updated Description.
09-Feb-2022	6	Updated <i>Description</i> , <i>product summary</i> , <i>Table 7</i> and <i>Section 5 Ordering information</i> .
03-May-2022	7	Updated <i>Table 7</i> .
24-May-2022	8	Updated <i>Section 4.1 UB package information</i> .
11-Feb-2025	9	Updated Figure 2 .

Contents

1	Electrical ratings	2
2	Electrical characteristics.....	3
3	Test circuits	4
4	Package information.....	5
4.1	UB package information	5
4.2	LCC-3 package information	7
5	Ordering information	9
6	Other information.....	10
	Revision history	11

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2025 STMicroelectronics – All rights reserved