

PLL generation using ST62 auto-reload timer

This note describes how to generate a digital signal locked in phase and frequency (PLL) with a calibrated delay starting from an active edge on the Auto-reload timer input pin.

This timer is an 8 bit timer/counter with prescaler. It includes auto-reload PWM, capture and compare capability with one input and one output pins. It can be controlled by the following registers (8 bit):

- Mode Control Register (MC)
- Status registers (SC0, SC1)
- Load register (LR)
- Incremental counter register (TC)
- Compare register (CP)
- Reload/Capture register (RC)

It can also wake-up the MCU from wait mode and exit from stop mode if an external event is present on the input pin. The prescaler ratio can be programmed to choose the timer input frequency F_{IN} (see Table 1).

The TIMIN input receives a 15 kHz digital signal. We want to generate a phase-locked 15 kHz digital signal with a falling edge delayed 19μs from the input rising edge, and a duty cycle of 75%. The CPU quartz frequency is 8 MHz.

PLL Generation using ARTimer

The Figure 2 shows the TIMOUT signal generated in “load on external edge” mode, given the above TIMIN signal: on TIMIN rising edge, the TC count register is loaded with the value contained in RC register (160 in this example). The timer will resume counting from value 160. When the compare value (210 in this example) is reached, the TIMOUT signal goes down. The timer keeps counting until the overflow (255) is reached. At this point, signal TIMOUT rises again. The timer keeps counting from 0 until next active edge on TIMIN. At this time, TC is loaded again with the RC value (160) and so on...

The delay from TIMIN edge to TIMOUT falling edge is given by $CP - RC$ (multiplied by the TC register clock period T_{in}). The low level duration on TIMOUT is given by $255 - CP$. The remaining of the TIMOUT period is variable, and will adjust to the TIMIN period: small variations of TIMIN period will be absorbed by a variation of T_{VAR} . The following rule must be respected in order to get the proper output signal:

The variable time T_{var} must stay smaller than CP , (otherwise the falling edge on TIMOUT occurs before rising edge on TIMIN) and larger than 0 (otherwise the rising edge on TIMOUT never occurs).

In other words, the period of input TIMIN (TOT in terms of TC clock cycles) must meet the following requirement:

$$255 - RC < TOT < 255 - RC + CP$$

Table 1. Prescaler Programming Ratio

Bit 0 Reg. SC1	PS2	PS1	PS0	PRESCALER Ratio
0	0	0	0	1
0	0	0	1	2
0	0	1	0	4
0	0	1	1	8
0	1	0	0	16
0	1	0	1	32
0	1	1	0	64
0	1	1	1	128
1	0	0	0	3
1	0	0	1	6
1	0	1	0	12
1	0	1	1	24
1	1	0	0	48
1	1	0	1	96
1	1	1	0	192
1	1	1	1	384


Coming back to our example, let's calculate the timer settings:

The input period is $T_{in} = 1/15 \text{ kHz} = 66.7\mu\text{s}$

Calculation of the prescaler ratio:

We want the best possible resolution, e.g. the smaller possible prescaler ratio: we would like the TC counter to count up to the

Figure 2. TIMOUT signal



Note: All numbers are decimal

highest number: 255 (for best resolution). In this case $66.7\mu\text{s} / 255 = 0.26\mu\text{s}$ is the smallest TC clock period that we can use. With a prescaler ratio of 1, the TC clock period is $1/8\text{MHz} = 0.125\mu\text{s}$. So we need a prescaler ratio of 3, giving a TC clock period of $3/8\text{MHz} = 0.375\mu\text{s}$. This is the elementary incrementing time of the TC counter, which gives the resolution of the phase shift and of the low level on TIMOUT (the TC counter is incremented with a clock $F_{\text{IN}} = 1/0.375\mu\text{s} = 2667\text{kHz}$).

The desired delay is $19\mu\text{s}$: $\text{CP} - \text{RC} = 19\mu\text{s} / 0.375\mu\text{s} = 50.67$.

The TIMIN period is:

$\text{TOT} = 66.7\mu\text{s} / 0.375\mu\text{s} = 177.78$.

The duty cycle is: $0.25 = (255 - \text{CP})/\text{TOT}$

Rounding the decimals, this gives:

$\text{RC} = 160$; $\text{CP} = 210$; $\text{TOT} = 178$

The variable time T_{VAR} is: $T_{\text{VAR}} = \text{TOT} - 255 + \text{RC} = 83$

The condition is met: T_{var} is positive and smaller than CP: $(255 - 160) < 178 < (255 - 160 + 210)$

The TIMOUT signal will remain correct and stable as long as this condition is met, even if the input frequency varies:

The input frequency limits for output correctness are:

$(255 - 160) \times 0.375\mu\text{s} < T_{\text{IN}} < (255 - 160 + 210) \times 0.375\mu\text{s}$

The output signal will remain locked in phase and frequency as long as the input signal TIMIN is in the range:

$8.7\text{kHz} < \text{TIMIN frequency} < 28\text{kHz}$

Of course, it is also possible to modify by software the $19\mu\text{s}$ delay and the 75% duty cycle, for example by measuring repetitively an error voltage with the A/D converter and calculating the modified delay or duty cycle.

Program example

```
;***** A-R Timer Register Set *****
RC      .def 0D9h,0FFh,0FFh      ;reload/capture register
CP      .def 0DAh,0FFh,0FFh      ;compare register
MC      .def 0D5h,0FFh,0FFh      ;mode control register
SC0     .def 0D6h,0FFh,0FFh      ;status/control register 0
SC1     .def 0D7h,0FFh,0FFh      ;status/control register 1
LR      .def 0DBh,0FFh,0FFh      ;load register
;=====
        ldi CP, 210               ;compare register = 210d
        ldi RC, 160               ;reload register = 160d
        ldi SC1,00000101b         ;clock source= CPU clock divided by 3
                                   ;rising TIMIN edge active
                                   ;pull-up disabled, prescaler ratio = 1
        ldi MC, 11100011b         ;load on TIMIN mode,interrupts disabled
                                   ;PWMOUT enabled, start timer
```

Table 6. Revision history

Date	Revision	Description of changes
March 1993	1	Initial release
30-June-2008	2	Logo modified

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED ST REPRESENTATIVE, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2008 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com