



Materials Declaration Form


IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D

* : Required Field

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	14-12-2017
Company Unique ID	NL 008751171B01		
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Contact Phone *	Refer to Supplier Comment section	Contact Email *	Refer to Supplier Comment section
Authorized Representative *	MDG MD CHAMPION	Representative Title	MDG MD CHAMPION
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement	
<p>While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.</p>	
Legal Statement	
Supplier Acceptance *	true
Legal Declaration *	Standard
Legal Statement	<p>Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.</p>

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STM32F446ZEJ6 STM32F446ZEJ6TR	P048*421XXXXA	A	9996	14-12-2017
	Amount	UoM	Unit type	ST ECOPACK Grade
	111.20	mg	Each	ECOPACK® 2
	Comment	ECOPACK® 2 is STMicroelectronics trade name for ROHS compliant device without Brominated and Chlorinated compound (900ppm) and without Antimony oxide flame retardant (in each organic material)		

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
3	260	3		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
Not Applicable; if coating is used or other bulk termination	NAC	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
BGA	10,10,0.8	144	No lead	
Comment	Package : A0ZY UFBGA 10X10 144L P 0.8 MM 8526251			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-April 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	TRUE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	FALSE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description

QueryList : REACH-12th January 2017				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				TRUE
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration :						Mfr Item Name	P048*421XXA				7055001.0	33658.0
note : Substance present with less 0.001mg will not be declared in this document												
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die or dies	M-011 Other inorganic materials	0.530	mg	supplier	die	Silicon (Si)	7440-21-3		0.521	mg	983019	4685
				supplier	metallization	Aluminium (Al)	7429-90-5		0.001	mg	1887	9
				supplier	metallization	Titanium (Ti)	7440-32-6		0.001	mg	1887	9
				supplier	Passivation	Silicon Nitride	12033-89-5		0.001	mg	1887	9
				supplier	Passivation	Silicon Oxide	7631-86-9		0.006	mg	11321	54
SILICON DIE	M-011 Other inorganic materials	2.559	mg	supplier	DIE	Silicon (Si)	7440-21-3		2.559	mg	1000000	23016
SUBSTRATE (DS7409HGB)	M-011 Other inorganic materials	33.167	mg	supplier	CORE	Glass Cloth	65997-17-3		5.638	mg	170000	50704
				supplier	CORE	Epoxy resin	61788-97-4		1.327	mg	40000	11930
				supplier	CORE	Flame resistant epoxy resin	223769-10-6		1.327	mg	40000	11930
				supplier	CORE	Heat resistant resin	25722-66-1		1.327	mg	40000	11930
				supplier	CORE	Silica filler	7631-86-9		3.648	mg	110000	32809
				supplier	CORE	Metal Hydroxide	Proprietary		0.663	mg	20000	5965
				supplier	CORE	Copper (Cu)	7440-50-8		13.930	mg	420000	125269
				supplier	SOLDERMASK (AUS320)	Solvent naphtha(petroleum),heavy aromatic	64742-94-5		1.824	mg	55000	16404
				supplier	SOLDERMASK (AUS320)	Napthalene	91-20-3		0.192	mg	5800	1730
				supplier	SOLDERMASK (AUS320)	Phosphinoxide derivative	Proprietary		0.066	mg	2000	597
				supplier	SOLDERMASK (AUS320)	Talc containing no asbestiform fibers	14807-96-6		0.497	mg	15000	4474
				supplier	SOLDERMASK (AUS320)	Barium sulfate	7727-43-7		0.829	mg	25000	7457
				supplier	SOLDERMASK (AUS320)	Dipropylene glycol monomethyl ether	34590-94-8		0.497	mg	15000	4474
				supplier	CU PLATING	Copper (Cu)	7440-50-8		1.194	mg	36000	10737
				supplier	NI PLATING	Nickel (Ni)	7440-02-0		0.166	mg	5000	1492
supplier	AU PLATING	Gold (Au)	7440-57-5		0.040	mg	1200	358				
DIE ATTACH (ATB-130U)	M-011 Other inorganic materials	0.369	mg	supplier	GLUE	Butadiene,acrylonitrile polymer,carboxy-termi	68610-41-3		0.258	mg	700000	2324
				supplier	GLUE	Phenol-formaldehyde polymer	9003-35-4		0.037	mg	100000	332
				supplier	GLUE	Phenol polymer with formaldehyde,glycidyl et	28064-14-4		0.034	mg	92000	306
				supplier	GLUE	Dapsone	80-08-0		0.036	mg	97000	322
				supplier	GLUE	Reaction product bisphenol-A-(epichlorhydrin	25068-38-6		0.004	mg	10000	33
supplier	GLUE	4,4, Isopropylidenediphenol	80-05-7		0.000	mg	1000	3				
BONDING WIRE (MKE 4N)	M-011 Other inorganic materials	2.584	mg	supplier	BONDING WIRE	Gold (Au)	7440-57-5		2.584	mg	1000000	23235
SOLDERBALL (Sn96.5Ag3.5)	M-011 Other inorganic materials	4.471	mg	supplier	SOLDERBALL	Tin (Sn)	7440-31-5		4.315	mg	965000	38803
				supplier	SOLDERBALL	Silver (Ag)	7440-22-4		0.156	mg	35000	1408
ENCAPSULATION (GE-100LFC5)	M-011 Other inorganic materials	67.520	mg	supplier	MOLDING COMPOUND	Silica fused (SiO2)	60676-86-0		60.715	mg	900000	454004
				supplier	MOLDING COMPOUND	Epoxy resin	Proprietary		3.062	mg	45000	27538
				supplier	MOLDING COMPOUND	Phenol resin	Proprietary		2.722	mg	40000	24478
				supplier	MOLDING COMPOUND	Metal Hydroxide	Proprietary		0.680	mg	10000	6120
				supplier	MOLDING COMPOUND	Carbon black	1333-86-4		0.340	mg	5000	3060
				supplier	MOLDING COMPOUND	Phenol resin	Proprietary		2.722	mg	40000	24478
				supplier	MOLDING COMPOUND	Metal Hydroxide	Proprietary		0.680	mg	10000	6120
supplier	MOLDING COMPOUND	Carbon black	1333-86-4		0.340	mg	5000	3060				