

# New op-amps and comparators

Focus on performance



**STMicroelectronics** has introduced a new range of low voltage operational amplifiers delivering high performance in terms of precision and power consumption.

The single, rail-to-rail TS507 features an input offset voltage of 25  $\mu\text{V}$  typ, 100  $\mu\text{V}$  max.

The new TSV911/2/4 and TSV991/2/4 families combine low input offset voltage at 1.5 mV max, with an ultra low input bias current of 1 pA, making them ideal for high impedance sensor signal conditioning. Offering up to 20 MHz bandwidth, these multi-segment products provide an excellent speed/consumption ratio (780  $\mu\text{A}$  typ).

The TS3021/2 rail-to-rail comparators include push-pull outputs and have a response time of 33 ns.

These new series of devices are available in a range of packages and are suited to a wide variety of applications.


## TS507 high-precision, single, rail-to-rail op-amp

### Key features

- Very high precision: 100  $\mu\text{V}$  max
- Low  $V_{\text{IO}}$  drift: 1  $\mu\text{V}/^{\circ}\text{C}$
- High open loop gain: 131 dB
- Rail-to-rail input/output
- Low noise: 12 nV/VHz at 1 kHz
- Supply voltage from 2.7 up to 5.5 V
- ESD tolerance  $\geq 5$  kV (HBM)
- Packages: SOT23-5L, SO8

### Applications

- Sensor signal conditioning
- Medical instrumentation
- Battery-powered systems
- Automotive



Input offset voltage vs. input common mode voltage


# TSV911/2/3 CMOS input, rail-to-rail op-amps

## Key features

- Low input bias current, 1 pA
- Low input offset voltage, 1.5 mV for 'A' version
- Rail-to-rail input/output,  $V_{CC}$  from 2.5 up to 5.5 V
- Excellent speed/power ratio, 780  $\mu$ A, 8 MHz
- High ESD tolerance  $\geq 5$  kV (HBM)
- Packages: SOT23-5L, MiniSO8, SO8, SO14, TSSOP14

## Applications

- Signal conditioning, instrumentation
- Battery-powered systems
- Automotive



Phase margin vs.  $I_{out}$  for the TSV91x


# TSV991/2/4 CMOS input op-amps offer 20 MHz bandwidth

## Key features

- Excellent speed/power ratio, 780  $\mu$ A, 20 MHz ( $G \geq 3$ )
- Low Input bias current, 1 pA
- Rail-to-rail input/output,  $V_{CC}$  from 2.5 up to 5.5 V
- High ESD tolerance  $\geq 5$  kV (HBM)
- Packages: SOT23-5L, MiniSO8, SO8, SO14, TSSOP14

## Applications

- Signal conditioning
- Battery-powered systems
- Instrumentation
- Automotive



Voltage gain and phase vs. frequency at  $V_{CC} = 5$  V and  $V_{icm} = 2.5$  V for the TSV99x


# TS3021/2 rail-to-rail comparators with 33 ns response time

## Key features

- Excellent speed/power ratio, 33 ns, 64  $\mu$ A
- Rail-to-rail inputs/push-pull outputs
- Wide supply voltage: 1.8 to 5 V
- -40 up to 125  $^{\circ}$ C temperature range
- Packages: SOT23-5L, SC70-5

## Applications

- Signal conditioning
- Instrumentation
- Telecom



Response time vs. various overdrives for  $V_{CC} = +2$  V



© STMicroelectronics - November 2007 - Printed in Italy - All rights reserved

The STMicroelectronics corporate logo is a registered trademark of the STMicroelectronics group of companies. All other names are the property of their respective owners.

For selected STMicroelectronics sales offices fax:

China +86 21 52574820; France +33 1 55489569; Germany +49 89 4605454; Italy +39 02 8250449; Japan +81 3 57838216; Singapore +65 6481 5124; Sweden +46 8 58774411; Switzerland +41 22 9292900; United Kingdom and Eire +44 1628 890391; USA +1 781 861 2678

Full product information at [www.st.com](http://www.st.com)