



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D * : Required Field

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2019-01-28
Company Unique ID	NL 008751171801		
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Contact Phone *	Refer to Supplier Comment section	Contact Email *	Refer to Supplier Comment section
Authorized Representative *	Giovanni Giacopello	Representative Title	ADG MD CHAMPION
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement


While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement		
Supplier Acceptance *	true	Legal Declaration *
		Standard

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
SM15T39CA	8HZK*TWB039K	A	ZA41	2019-01-28
	Amount	UoM	Unit type	ST ECOPACK Grade
	250.00	mg	Each	ECOPACK2
Comment	ECOPACK® 2 is STMicroelectronics trade name for ROHS compliant device without Brominated and Chlorinated compound (900ppm) and without Antimony oxide flame retardant (in each organic material)			

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
1	260	3		
Bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
Not Applicable	Tin (Sn), matte	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
SOJ	4.5X2.16X3.68	2	J bend	
Comment	Package: SMC CLIP (SOD 15 NEW)			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-March 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : ELV directive : 2000/53/EC amended 2017/2096 _November 2017	
Query	Response
1 - Product(s) meets EU ELV requirements without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
Exemption Id.	Description
8e	Lead in high melting temperature type solders (i.e. lead-based alloys containing 85 % by weight or more lead)

QueryList : California Prop65 list, dated 26th October 2018			
Query			Response
1 - The product does not contain identified substance from California Prop 65 List, no exposure to consumers is foreseen			FALSE
2 - The product is containing below substance(s) from California Prop 65 List, no exposure to consumers is foreseen			TRUE
Substance	amount in product (mg)	Application	ppm in product
Nickel	0.05	Die	208
Lead	3.90	Soft solder	15596

QueryList : REACH-15th January 2019				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				FALSE
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product
Lead	1000 ppm	3.90	Soft solder	15596
2 - Product(s) does not contain REACH Substances Of Very High Concern in any Embedded article nor Homogeneous Material above the limits per the definition within REACH				FALSE
CategoryLevel_Name	CategoryLevel_Threshold	Amount in Embedded Article / Homogeneous Material (mg)	Application - Article / Homogeneous Material	ppm in Article /Homogeneous Material
Lead	1000 ppm	3.90	Soft solder	925030

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	8HZK*TWB039K					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	M-011 Other inorganic materials	5.063	mg	supplier	die	Silicon (Si)	7440-21-3		4.909	mg	969583	19636
				supplier	metallization	Aluminium (Al)	7429-90-5		0.028	mg	5530	112
				supplier	metallization	Gold (Au)	7440-57-5		0.020	mg	3950	80
				supplier	passivation	Nickel (Ni)	7440-02-0		0.021	mg	4148	84
				supplier	Passivation	Silicon Oxide	7631-86-9		0.028	mg	5530	112
				supplier	back side metallization	Aluminium (Al)	7429-90-5		0.019	mg	3753	76
				supplier	back side metallization	Gold (Au)	7440-57-5		0.007	mg	1383	28
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.031	mg	6123	124
Leadframe & clips	Copper & its alloys	88.531	mg	supplier	alloy	Copper (Cu)	7440-50-8		88.488	mg	999514	353952
				supplier	alloy	Zinc (Zn)	7440-66-6		0.004	mg	45	16
				supplier	alloy	Iron (Fe)	7439-89-6		0.009	mg	102	36
				supplier	alloy	Phosphorus (P)	12185-10-3		0.030	mg	339	120
Soft solder	Solder	4.215	mg	JIG - R	Lead/Lead Compounds	Lead (Pb)	7439-92-1	7a-Lead in high mel	3.899	mg	925030	15596
				supplier	soft solder	Tin (Sn)	7440-31-5		0.211	mg	50059	844
				supplier	soft solder	Silver (Ag)	7440-22-4		0.105	mg	24911	420
Encapsulation	Other inorganic materials	150.083	mg	supplier	mond compound	Amorphous Silica	7631-86-9		92.151	mg	614000	368604
				supplier	mond compound	Quartz	14808-60-7		30.017	mg	200003	120068
				supplier	mond compound	epoxy resin	25068-38-6		18.009	mg	119994	72036
				supplier	mond compound	phenolic resin	29690-82-2		9.005	mg	60000	36020
				supplier	mond compound	Carbon black	1333-86-4		0.901	mg	6003	3604
Connections coating	Solder	2.108	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		2.108	mg	1000000	8432