



## Materials Declaration Form

<b>IPC Form Type *</b>	1752 Distribute	<b>Version</b>	2
<b>Sectionals *</b>	Material Info Manufacturing Info	<b>Subsectionals *</b>	A-D
<i>* : Required Field</i>			

Supplier Information			
<b>Company Name *</b>	STMicroelectronics	<b>Response Date *</b>	2015-07-21
<b>Contact Name *</b>	Refer to "Supplier Comment" section	<b>Contact Title</b>	Refer to "Supplier Comment" section
<b>Contact Phone *</b>	Refer to "Supplier Comment" section	<b>Contact Email *</b>	Refer to "Supplier Comment" section
<b>Authorized Representative *</b>	Emilio Castelli	<b>Representative Title</b>	APG MD CHAMPION
<b>Representative Phone *</b>	Refer to "Supplier Comment" section	<b>Representative Email *</b>	Refer to "Supplier Comment" section
<b>Supplier Comment</b>	Online Technical Support - STMicroelectronics : <a href="http://www.st.com/web/en/support/online_tech_support.html">http://www.st.com/web/en/support/online_tech_support.html</a>		

**Uncertainty Statement**


While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement			
<b>Supplier Acceptance *</b>	true	<b>Legal Declaration *</b>	Standard

**Legal Statement**

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STPA003CD-48X	J848*UAI5ABC	A	SH1A	2015-07-21
	Amount	UoM	Unit type	ST ECOPACK Grade
	7800.00	mg	Each	ECOPACK® 2

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
NAC	NAC	NAC		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
NAC	Tin (Sn), matte, annealed	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
SMD	28.9x15.5x4.5	27	Through-hole	
Comment				

QueryList : ROHS directive 2011/65/EU _ July 2011	
Query	Response
Product(s) meets EU RoHS requirement without any exemptions	false
Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7a' exemption (other selected exemptions may apply)	true
Product(s) meets EU RoHS requirements by application of the selected exemption(s)	false
Product(s) does not meet EU RoHS requirements and is not under exemptions	false
Product(s) is obsolete, no information is available	false
Product(s) is unknown, no information is available	false
Exemption Id.	Description

QueryList : REACH-16th June 2014				
Query				Response
The product does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration						Mfr Item Name	J848*UAI5ABC					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	Other inorganic materials	16.823	mg	supplier	die	Silicon (Si)	7440-21-3		15.639	mg	929620	2005
Die				supplier	metallization	Aluminium (Al)	7429-90-5		0.161	mg	9570	21
Die				supplier	metallization	Tungsten (W)	7440-33-7		0.128	mg	7609	16
Die				supplier	passivation	Silicon Nitride (SiN)	68034-42-4		0.034	mg	2021	4
Die				supplier	passivation	Silicon Oxide(SiO2)	7631-86-9		0.275	mg	16347	35
Die				supplier	back side metallization	Chromium (Cr)	7440-47-3		0.012	mg	713	2
Die				supplier	back side metallization	Gold (Au)	7440-57-5		0.032	mg	1902	4
Die				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.092	mg	5469	12
Die				supplier	back side metallization	Vanadium (V)	7440-62-2		0.007	mg	416	1
Die				supplier	glass coating	Glass: Silicon Dioxide (SiO2)	7631-86-9		0.275	mg	16347	35
Die				supplier	polymer die coating	PIX1 Gamma-butyrolactone	96-48-0		0.168	mg	9986	22
Leadframe	Copper & its alloys	5214.917	mg	supplier	alloy	Copper (Cu)	7440-50-8		5205.117	mg	998121	667323
Leadframe				supplier	alloy	Iron (Fe)	7439-89-6		2.397	mg	460	307
Leadframe				supplier	alloy	Iron Phosphide (FeP)	26508-33-8		4.378	mg	840	561
Leadframe				supplier	metallization	Silver (Ag)	7440-22-4		3.025	mg	580	388
Die attach		10.762	mg	JIG - R	Soft Solder	Lead (Pb)	7439-92-1	7a-Lead in high me	10.493	mg	975005	1345
Die attach				supplier	Soft Solder	Silver (Ag)	7440-22-4		0.161	mg	14960	21
Die attach				supplier	Soft Solder	Tin (Sn)	7440-31-5		0.108	mg	10035	14
Bonding wire				supplier	wire	Copper (Cu)	7440-50-8		4.427	mg	1000000	568
encapsulation		2514.486	mg	supplier	mold compound	Amorphous Silica	7631-86-9		2137.313	mg	850000	274014
encapsulation				supplier	mold compound	Epoxy Cresol Novolak	29690-82-2		150.870	mg	60000	19342
encapsulation				supplier	mold compound	epoxy resin	Proprietary		100.579	mg	40000	12895
encapsulation				supplier	mold compound	Phenol resin	Proprietary		100.579	mg	40000	12895
encapsulation				supplier	mold compound	Carbon black	1333-86-4		17.601	mg	7000	2257
encapsulation				supplier	mold compound	Bismuth (Bi)	7440-69-9		7.544	mg	3000	967
connections coating	Solder	38.585	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		38.585	mg	1000000	4947