



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Sectionals *	A-D <i>* : Required Field</i>

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2017-06-07
Company Unique ID	NL 008751171801		
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Contact Phone *	Refer to Supplier Comment section	Contact Email *	Refer to Supplier Comment section
Authorized Representative *	Laurent Tosi	Representative Title	MMS MD CHAMPION
Representative Phone *	(+33) 442 685 795	Representative Email *	laurent.tosi@st.com
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement

While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement	
Supplier Acceptance *	true
Legal Declaration *	Standard

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STM32F373CBT7	S95B*432XXXB	A	998Z	2017-06-07
Amount	UoM	Unit type	ST ECOPACK Grade	
197,029	mg	Each	ECOPACK® 2	
	Comment	ECOPACK® 2 is STMicroelectronics trade name for ROHS compliant device without Brominated and Chlorinated compound (900ppm) and without Antimony oxide flame retardant (in each organic material)		

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		
3	260	3		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
Not Applicable ; if coating is used or other bulk termination : add in comments	Tin (Sn), matte	Copper Alloy		



Package Designator	Size	Nbr of instances	Shape	
QFP	7x7X1.4	48	L bend	
Comment	Package : 5B LQFP 48 7x7x1.4 1 0110596			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-April 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	TRUE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	FALSE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description

QueryList : REACH-12th January 2017				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	S95B*432XXXB				6000001,0	0,0
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	M-011 Other inorganic materials	15,006	mg	supplier	die	Silicon (Si)	7440-21-3		14,392	mg	959083	73045
				supplier	metallization	Aluminium (Al)	7429-90-5		0,042	mg	2799	213
				supplier	metallization	Copper (Cu)	7440-50-8		0,208	mg	13861	1056
				supplier	metallization	Cobalt (Co)	7440-48-4		0,039	mg	2599	198
				supplier	metallization	Titanium (Ti)	7440-32-6		0,012	mg	800	61
				supplier	metallization	Tungsten (W)	7440-33-7		0,023	mg	1533	117
				supplier	Passivation	Silicon Nitride	12033-89-5		0,027	mg	1799	137
				supplier	Passivation	Silicon Oxide	7631-86-9		0,263	mg	17526	1335
				supplier	Metals	Silver	7440-22-4		1,736	mg	901000	8813
Die Attach Epoxy_ABLEBOND 3230_H	M-011 Other inorganic materials	1,927	mg	#N/A	Plastics/polymers	Highly cross-linked polymer	Proprietary		0,191	mg	99000	968
				supplier	Plastics/polymers	Epoxy Resin A	Proprietary		2,337	mg	21117	11861
				supplier	Plastics/polymers	Epoxy Resin B	Proprietary		2,337	mg	21117	11861
				supplier	Plastics/polymers	Phenol Resin	Proprietary		6,232	mg	56311	31628
				supplier	Glass	Silica(Amorphous)A	60676-86-0		86,234	mg	779231	-562333
Mold Compound_EME-G631SHQ_Sun	M-011 Other inorganic materials	110,665	mg	supplier	Glass	Silica(Amorphous)B	7631-86-9		12,833	mg	115960	65131
				supplier	Non-metals	Carbon Black	1333-86-4		0,693	mg	6265	3519
				supplier	Metals	Silver	7440-22-4		0,264	mg	960000	1342
				supplier	Metals	Others	Proprietary		0,011	mg	40000	56
Wire_AG SI TYPE_MKE	M-011 Other inorganic materials	0,275	mg	supplier	Metals	Tin	7440-31-5		1,078	mg	1000000	5473
Plating anode_Pure Tin_Nuo Nengda	M-011 Other inorganic materials	1,078	mg	supplier	Metals	Iron	7439-89-6		1,489	mg	21865	7555
				supplier	Non-metals	Phosphorus	7723-14-0		0,050	mg	730	252
Leadframe_C9+Ag_HDS	M-011 Other inorganic materials	68,077	mg	supplier	Metals	Zinc	7440-66-6		0,077	mg	1125	389
				supplier	Metals	Copper	7440-50-8		62,170	mg	913235	315539
				supplier	Metals	Silver	7440-22-4		4,289	mg	63000	21768
				JIG-R	Metals	Lead	7439-92-1		0,003	mg	45	16