



Material Composition Declaration

© Copyright 2005. IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.

This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.

Adobe Reader version 7.0.5 is required to complete this declaration.

1752-2 1.1	IPC Web Site for Information on IPC-1752 Standard http://www.ipc.org/IPC-175x	Form Type * Distribute	Declaration Class * Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Informat
------------	--	---------------------------	--

Supplier Information

Company Name * STMicroelectronics	Company Unique ID	Unique ID Authority	Response Date * NA	Response Document ID				
Contact Name *	Title - Contact	Phone - Contact *	Email - Contact *	Duplicate Contact -> Authorized Representative				
Authorized Representative * GIOVANNI GIACOPELLO	Title - Representative AMS/IPD MD CHAMPION	Phone - Representative * NA	Email - Representative * NA	Supplier Comments or URL for Additional Information				
Requester Item Number	Mfr Item Number	Mfr Item Name	Effective Date	Version	Manufacturing Site	Weight *	UOM	Unit Type
	STCS1PHR	1B61*UM64J51	2012-09-03	A	ZY1A	79.52	mg	Each
Alternate Recommendation	Package: HSOP 8L .150" PITCH			Alternate Item Comments	ECOPACK2/ROHS BSA REF: CD00265453			

Manufacturing Process Information

Terminal Plating / Grid Array Material	Terminal Base Alloy	J-STD-020 MSL Rating	Peak Process Body Temperature	Max Time at Peak Temperature	Number of Reflow Cycles
Matte Tin (Sn)	CU Alloy	1	260 C	30 seconds	3

Comments

Disclaimer: While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and

Save the fields in this form to a file

Export Data

Import fields from a file into this form

Import Data

Clear all of the fields on this form

Reset Form

Lock the fields on this form to prevent changes

Lock Supplier Fields

RoHS Material Composition Declaration

Declaration Type *

Simplified

RoHS Directive
2002/95/EC

RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material for Cadmium

Supplier certifies that it gathered the information it provides in this form concerning RoHS restrictive substances using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

RoHS Declaration *

1 - Item(s) does not contain RoHS restricted substances per the definition above

Supplier Acceptance *

Accepted

Exemptions: If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions.

Declaration Signature

Instructions: Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.

Supplier Digital Signature

Homogeneous Material Composition Declaration for Electronic Products

SubItem Instructions: The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

Substance Instructions: [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

Line Functions: +I Inserts a New Item /SubItem +M Inserts a new Material +C Inserts a new Substance Category +S Inserts a new Substance - Deletes the element line

		Item/SubItem Name	Homogeneous Material		Weight	Unit of Measure	Level		Substance Category	Substance		CAS	Exempt	Weight	Unit of Measure	Tolerance		PPM
+I	-I		+M	-M			+C	-C		+S	-S					-	+	
		1B61*UM64J51			1.138	mg			Supplier	Silicon die	Silicon (Si)	7440-21-3		1.125	mg			988,57
									Supplier	Die metallization	Aluminium (Al)	7429-90-5		0.001	mg			879
											Copper (Cu)	7440-50-8		0.001	mg			879
											Titanium (Ti)	7440-32-6		0.001	mg			879
											Chromium (Cr)	7440-47-3		0.001	mg			879
											Gold (Au)	7440-57-5		0.002	mg			1,757
											Nickel (Ni)	7440-02-0		0.007	mg			6,151
									Supplier	Alloy	Copper (Cu)	7440-50-8		29.901	mg			960,49
											Iron (Fe)	7439-89-6		0.737	mg			23,674
											Zinc (Zn)	7440-66-6		0.041	mg			1,317
											Phosphorus (P)	12185-10-3		0.012	mg			385
									Supplier	Coating	Silver (Ag)	7440-22-4		0.44	mg			14,134
									Supplier	Glue	Silver (Ag)	7440-22-4		0.382	mg			802,52
											Epoxy resin 1	9003-36-5		0.038	mg			79,832
											Epoxy resin 2	68475-94-5		0.014	mg			29,412
											2,6-Diglycidyl phenyl al	EC 417-470		0.014	mg			29,412
											Gamma Butyrolactone	96-48-0		0.014	mg			29,412
											Polyoxypropylenediam	9046-10-0		0.014	mg			29,412
									Supplier	Bonding wire	Gold (Au)	7440-57-5		0.16	mg			1,000,0
									Supplier	Moulding Compound	Biphenyl epoxy resin	85954-11-6		3.618	mg			80,000
											Phenol resin Novolak	26834-02-6		1.809	mg			40,000
											Silica, vitreous	60676-86-0		39.301	mg			869,01
											Carbon black	1333-86-4		0.226	mg			4,997

		+S	-S	Bismuth (Bi)		7440-69-9		0.271	mg			5,992											
+M	-M	Finishing			1.39	mg	+C	-C	Supplier	solder			+S	-S	Tin (Sn)			7440-31-5	1.39	mg			1,000,0