



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D

** : Required Field*

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2015-10-12
Contact Name *	Refer to "Supplier Comment" section	Contact Title	Refer to "Supplier Comment" section
Contact Phone *	Refer to "Supplier Comment" section	Contact Email *	Refer to "Supplier Comment" section
Authorized Representative *	LAURENT TOSI	Representative Title	MMS MD CHAMPION
Representative Phone *	33 442 685 795	Representative Email *	laurent.tosi@st.com
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/online_tech_support.html		

Uncertainty Statement

While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.


Legal Statement

Supplier Acceptance *	true	Legal Declaration *	Standard
------------------------------	------	----------------------------	----------

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STM8AF6226TCY	U25V*79JX10A	A	959	2015-10-12
	Amount	UoM	Unit type	ST ECOPACK Grade
	180.00	mg	Each	ECOPACK® 2

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
2	260	3		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
NAC	Nicke/Palladium/Gold (Ni/Pd/Au)	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
QFP	7x7x1.4	32	L bend	
Comment	LQFP 32 7x7x1.4 FOOT PRINT 1.0			

QueryList : ROHS directive 2011/65/EU _ July 2011	
Query	Response
Product(s) meets EU RoHS requirement without any exemptions	true
Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	false
Product(s) meets EU RoHS requirements by application of the selected exemption(s)	false
Product(s) does not meet EU RoHS requirements and is not under exemptions	false
Product(s) is obsolete, no information is available	false
Product(s) is unknown, no information is available	false
Exemption Id.	Description

QueryList : REACH-16th December 2013				
Query				Response
The product does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration						Mfr Item Name	U25V*79JX10A					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
die (s)	Other inorganic materials	2.657	mg	supplier	die	Silicon (Si)	7440-21-3		2.576	mg	969514	14311
die (s)				supplier	metallization	Aluminium (Al)	7429-90-5		0.007	mg	2635	39
die (s)				supplier	metallization	Copper (Cu)	7440-50-8		0.024	mg	9033	133
die (s)				supplier	metallization	Tantalum (Ta)	7440-25-7		0.002	mg	753	11
die (s)				supplier	metallization	Titanium (Ti)	7440-32-6		0.004	mg	1505	22
die (s)				supplier	passivation	Silicon Nitride (SiN)	68034-42-4		0.006	mg	2258	33
die (s)				supplier	passivation	Silicon Oxide(SiO2)	7631-86-9		0.038	mg	14302	211
Lead-frame	Other inorganic materials	69.913	mg	supplier	alloy	Copper (Cu)	7440-50-8		67.256	mg	962000	373644
Lead-frame				supplier	alloy	Iron (Fe)	7439-89-6		2.097	mg	30000	11652
Lead-frame				supplier	alloy	Zinc (Zn)	7440-66-6		0.454	mg	6500	2525
Lead-frame				supplier	alloy	Iron Phosphide (Fe2P)	1310-43-6		0.105	mg	1500	583
Lead-frame Coating	Other inorganic materials	0.403	mg	supplier	coating	Nickel (Ni)	7440-02-0		0.369	mg	914840	2048
Lead-frame Coating				supplier	coating	Palladium (Pd)	7440-05-3		0.012	mg	29660	66
Lead-frame Coating				supplier	coating	Gold (Au)	7440-57-5		0.011	mg	27750	62
Lead-frame Coating				supplier	coating	Silver (Ag)	7440-22-4		0.011	mg	27750	62
Die Attach	Other inorganic materials	1.044	mg	supplier	glue or soft solder	Silver (Ag)	7440-22-4		0.804	mg	770000	4468
Die Attach				supplier	glue or soft solder	Epoxy Cresol Novolak	29690-82-2		0.236	mg	226000	1311
Die Attach				supplier	glue or soft solder	1-isopropyl-2,2-dimethyltrimethylene diisobut	6846-50-0		0.004	mg	4000	23
Wires	Other inorganic materials	0.645	mg	supplier	Bonding wire	Gold (Au)	7440-57-5		0.645	mg	1000000	3581
Encapsulation	Other inorganic materials	105.336	mg	supplier	Moulding Compound	Solid Epoxy Resin	na		7.253	mg	68860	40297
Encapsulation				supplier	Moulding Compound	Phenol Resin	na		5.181	mg	49186	28783
Encapsulation				supplier	Moulding Compound	Silica, vitreous	60676-86-0		92.228	mg	875560	512377
Encapsulation				supplier	Moulding Compound	Carbon-black	1333-86-4		0.518	mg	4919	2878
Encapsulation				supplier	Bismuth/Bismuth Compounds	Bismuth	7440-69-9		0.155	mg	1476	864
Finishing	Other inorganic materials	0.003	mg	supplier	connections coating	Nickel (Ni)	7440-02-0		0.002	mg	914840	13
Finishing				supplier	connections coating	Palladium (Pd)	7440-05-3		0.000	mg	29660	0
Finishing				supplier	connections coating	Gold (Au)	7440-57-5		0.000	mg	27750	0
Finishing				supplier	connections coating	Silver (Ag)	7440-22-4		0.000	mg	27750	0