



Material Composition Declaration

© Copyright 2005. IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.

This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.

Adobe Reader version 7.0.5 is required to complete this declaration.

1752-2 1.1	IPC Web Site for Information on IPC-1752 Standard http://www.ipc.org/IPC-175x	Form Type * Distribute	Declaration Class * Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Informat
------------	--	---------------------------	--

Supplier Information

Company Name * STMicroelectronics	Company Unique ID	Unique ID Authority	Response Date * N/A	Response Document ID				
Contact Name *	Title - Contact	Phone - Contact *	Email - Contact *					
Authorized Representative * GIUSEPPE VITALI PALMA	Title - Representative AMS & IPD MD CHAMPION	Phone - Representative * N/A	Email - Representative * N/A	Supplier Comments or URL for Additional Information				
Requester Item Number	Mfr Item Number	Mfr Item Name	Effective Date	Version	Manufacturing Site	Weight *	UOM	Unit Type
	STTH2R02U	HNZJ*H52F81F	2012-11-09	A	ZA41	110	mg	Each
Alternate Recommendation	PACKAGE: SMB CLIP (SOD 6			Alternate Item Comments	ECOPACK2/ROHS; BSA: CD00252805			

Manufacturing Process Information

Terminal Plating / Grid Array Material Matte Tin (Sn) - annealed	Terminal Base Alloy CU Alloy	J-STD-020 MSL Rating 1	Peak Process Body Temperature 260 C	Max Time at Peak Temperature 30 seconds	Number of Reflow Cycles 3
---	---------------------------------	---------------------------	--	--	------------------------------

Comments

Disclaimer: While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and

Save the fields in this form to a file

Export Data

Import fields from a file into this form

Import Data

Locked

RoHS Material Composition Declaration

Declaration Type *

Simplified

RoHS Directive 2002/95/EC **RoHS Definition:** Quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material for Cadmium

Supplier certifies that it gathered the information it provides in this form concerning RoHS restrictive substances using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

RoHS Declaration * 4 - Item(s) does not contain RoHS restricted substances per the definition above except for selected exemptions

Supplier Acceptance * Accepted

Exemptions: If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions.

Exemption List Version EL-2006/690/EC

7a. Lead in high melting temperature type solders (i.e. lead based solder alloys containing 85% by weight or more lead).

Declaration Signature

Instructions: Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.

Supplier Digital Signature

Homogeneous Material Composition Declaration for Electronic Products

SubItem Instructions: The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

Substance Instructions: [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

Line Functions: +I Inserts a New Item /SubItem +M Inserts a new Material +C Inserts a new Substance Category +S Inserts a new Substance - Deletes the element line

Item/SubItem Name	Homogeneous Material	Weight	Unit of Measure	Level	Substance Category	Substance	CAS	Exempt	Weight	Unit of Measure	Tolerance		PPM		
											-	+			
HNZJ*H52F81F	Silicon Die	1.114	mg	Supplier	Silicon Die	silicon	7440-21-3		1.103	mg			990,12		
					die back side metalliz	Titanium (Ti)	7440-32-6		0.001	mg			898		
						Gold (Au)	7440-57-5		0.002	mg			1,795		
						Nickel (Ni)	7440-02-0		0.008	mg			7,181		
Leadframe + Clip		44.735	mg	Supplier	Alloy	Cu	7440-50-8		44.714	mg			999,53		
						Zn	7440-66-6		0.002	mg			45		
						Fe	7439-89-6		0.004	mg			89		
						Iron Phosphide(FeP)	26508-33-8		0.015	mg			335		
Die Attach		2.301	mg	supplier	Solder	Ag	7440-22-4		0.058	mg			25,206		
						Sn	7440-31-5		0.115	mg			49,979		
Encapsulation		60.92	mg	JIG R	Lead/Lead Compound	Lead	7439-92-1	7a. Lead	2.128	mg			924,81		
						supplier	Molding compound	Silica, vitreous	7631-86-9		44.272	mg			726,72
								Quartz	14808-60-7		5.866	mg			96,290
								Epoxy resin	Proprietary		7.039	mg			115,54
								Phenolic resin	9003-35-4		3.52	mg			57,781
								Carbon black	1333-86-4		0.176	mg			2,889
								Bismuth trioxide	1304-76-3		0.041	mg			673
Finishing		0.93	mg	supplier	connection coating	chlorine	7782-50-5		0.006	mg			98		
						Sn	7440-31-5		0.93	mg			1,000,0		