



# Material Composition Declaration

© Copyright 2005. IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.

This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.

Adobe Reader version 7.0.5 is required to complete this declaration.

1752-2 1.1	IPC Web Site for Information on IPC-1752 Standard <a href="http://www.ipc.org/IPC-175x">http://www.ipc.org/IPC-175x</a>	Form Type * Distribute	Declaration Class * Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Informat
------------	--	---------------------------	--

## Supplier Information

Company Name * STMicroelectronics	Company Unique ID	Unique ID Authority	Response Date * 2011-03-10	Response Document ID PGO7*0C861SA
Contact Name *	Title - Contact	Phone - Contact *	Email - Contact *	<input type="button" value="Duplicate Contact -&gt; Authorized Representative"/>
Authorized Representative * Laurent Tosi	Title - Representative MMS Central Packaging	Phone - Representative * +33 442 685 795	Email - Representative * laurent.tosi@st.com	Supplier Comments or URL for Additional Information

Requester Item Number	Mfr Item Number	Mfr Item Name	Effective Date	Version	Manufacturing Site	Weight *	UOM	Unit Type
		PLASTIC SMALL OUTLINE PA	2011-03-10	A	Shenzhen	80	mg	Each
Alternate Recommendation				Alternate Item Comments				

## Manufacturing Process Information

Terminal Plating / Grid Array Material Nickel/Palladium/Gold (Ni/Pd/Au)	Terminal Base Alloy CU Alloy	J-STD-020 MSL Rating 1	Peak Process Body Temperature 260 C	Max Time at Peak Temperature 30 seconds	Number of Reflow Cycles 3
--	---------------------------------	---------------------------	--	--	------------------------------

Comments  
Ecopack 2 compliant: means Br-Cl & Sb oxide free. DISCLAIMER: While STMicroelectronics has endeavored to provide information which is accurate and up to date, this docum

Save the fields in this form to a file

Export Data

Import fields from a file into this form

Import Data

Clear all of the fields on this form

Reset Form

Lock the fields on this form to prevent changes

Lock Supplier Fields

## RoHS Material Composition Declaration

Declaration Type \*

Simplified

RoHS Directive  
2002/95/EC

**RoHS Definition:** Quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material for Cadmium

Supplier certifies that it gathered the information it provides in this form concerning RoHS restrictive substances using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

RoHS Declaration \*

1 - Item(s) does not contain RoHS restricted substances per the definition above

Supplier Acceptance \*

Accepted

**Exemptions:** If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions.

## Declaration Signature

**Instructions:** Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.

Supplier Digital Signature

## Homogeneous Material Composition Declaration for Electronic Products

**SubItem Instructions:** The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

**Substance Instructions:** [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

**Line Functions:** +I Inserts a New Item /SubItem +M Inserts a new Material +C Inserts a new Substance Category +S Inserts a new Substance - Deletes the element line

		Item/SubItem Name	Homogeneous Material		Weight	Unit of Measure	Level		Substance Category	Substance		CAS	Exempt	Weight	Unit of Measure	Tolerance		PPM
+I	-I		+M	-M			+C	-C		+S	-S					-	+	
		PLASTIC SMALL O			Chip	1.292646	mg		Supplier	silicon die	Silicium (Si)	7440-21-3		1.292322	mg			16,154
									Supplier	die metallization	Aluminium(Al)	7429-90-5		0.000194	mg			2.4300
											Copper (Cu)	7440-50-8		0.000064	mg			0.8100
											Titanium (Ti)	7440-32-6		0.000064	mg			0.8100
					Lead-frame	24.98420	mg		Supplier	alloy	Copper (Cu)	7440-50-8		24.34710	mg			304,33
											Iron (Fe)	7439-89-6		0.586129	mg			7,326.6
											Zinc (Zn)	7440-66-6		0.029981	mg			374.76
											Iron Phosphide (FeP)	26508-33-8		0.020986	mg			262.33
					Lead-frame Coat	0.124344	mg		Supplier	coating	Nickel (Ni)	7440-02-0		0.113999	mg			1,424.9
											Palladium (Pd)	7440-05-3		0.007299	mg			91.238
											Gold (Au)	7440-57-5		0.003046	mg			38.080
					Die Attach	1.027305	mg		Supplier	glue or soft solder	Silver (Ag)	7440-22-4		0.924574	mg			11,557
											acrylate	na		0.061638	mg			770.48
											Methacrylate	na		0.039037	mg			487.97
											acrylate	na		0.002054	mg			25.682
					Wires	0.062108	mg		Supplier	Bonding wire	Gold (Au)	7440-57-5		0.062108	mg			776.35
					Encapsulation	52.508	mg		Supplier	Moulding Compound	Epoxy Resin	na		3.9381	mg			49,226
											Phenol Resin	na		2.6254	mg			32,817
											Silica, vitreous	60676-86-0		45.47192	mg			568,40
											Carbon-black	1333-86-4		0.26254	mg			3,281.7
									B	Bismuth/Bismuth Com	Bismuth	7440-69-9		0.210032	mg			2,625.4
					Finishing	0.001243	mg		Supplier	connections coating	Nickel (Ni)	7440-02-0		0.001139	mg			14.249
											Palladium (Pd)	7440-05-3		0.000072	mg			0.9123

+S	-S	Gold (Au)	7440-57-5		0.00030mg			0.3808
----	----	-----------	-----------	--	-----------	--	--	--------