



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D <i>* : Required Field</i>

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2018-07-17
Company Unique ID	NL 008751171B01		
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Contact Phone *	Refer to Supplier Comment section	Contact Email *	Refer to Supplier Comment section
Authorized Representative *	Giovanni Giacopello	Representative Title	ADG MD CHAMPION
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement


While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement		
Supplier Acceptance *	true	Legal Declaration *
		Standard

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
2031-771009-000	HNRO*Z71Q83Q	A	9941	2018-07-17
	Amount	UoM	Unit type	ST ECOPACK Grade
	15.8	mg	Each	ECOPACK® 2
Comment	ECOPACK® 2 is STMicroelectronics trade name for ROHS compliant device without Brominated and Chlorinated compound (900ppm) and without Antimony oxide flame retardant (in each organic material)			

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
1	260	3		
Bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
Not Applicable	Tin (Sn), matte, annealed	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
DSO	1.9 - 1.9 - 1	2	gull wing	
Comment	Package: DO-216AA; MDF valid also for STPS1L20M			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-March 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : ELV directive : 2000/53/EC amended 2017/2096 _November 2017	
Query	Response
1 - Product(s) meets EU ELV requirements without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
Exemption Id.	Description
8e	Lead in high melting temperature type solders (i.e. lead-based alloys containing 85 % by weight or more lead)

QueryList : California Prop65 list, dated 25th May 2018			
Query			Response
1 - The product does not contain identified substance from California Prop 65 List, no exposure to consumers is foreseen			FALSE
2 - The product is containing below substance(s) from California Prop 65 List, no exposure to consumers is foreseen			TRUE
Substance	amount in product (mg)	Application	ppm in product
Nickel	0.01	Die	633
Lead	0.99	Soft solder	62595

QueryList : REACH-27th June 2018				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				FALSE
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product
Lead	1000 ppm	0.99	Soft solder	62595
2 - Product(s) does not contain REACH Substances Of Very High Concern in any Embedded article nor Homogeneous Material above the limits per the definition within REACH				FALSE
CategoryLevel_Name	CategoryLevel_Threshold	Amount in Embedded Article / Homogeneous Material (mg)	Application - Article / Homogeneous Material	ppm in Article /Homogeneous Material
Lead	1000 ppm	0.99	Soft solder	925164

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	HNRO*Z71Q83Q					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	M-011 Other inorganic materials	0.835	mg	supplier	die	Silicon (Si)	7440-21-3		0.805	mg	964072	50949
				supplier	metallization	Aluminium (Al)	7429-90-5		0.006	mg	7184	380
				supplier	metallization	Gold (Au)	7440-57-5		0.004	mg	4790	253
				supplier	passivation	Nickel (Ni)	7440-02-0		0.004	mg	4790	253
				supplier	metallization	Titanium (Ti)	7440-32-6		0.001	mg	1198	63
				supplier	metallization	Tungsten (W)	7440-33-7		0.001	mg	1198	63
				supplier	Passivation	Silicon Oxide	7631-86-9		0.006	mg	7186	380
				supplier	back side metallization	Titanium (Ti)	7440-32-6		0.001	mg	1198	63
				supplier	back side metallization	Gold (Au)	7440-57-5		0.001	mg	1198	63
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.006	mg	7186	380
Leadframe	M-004 Copper and its alloys	8.445	mg	supplier	alloy	Copper (Cu)	7440-50-8		8.434	mg	998697	533797
				supplier	alloy	Iron (Fe)	7439-89-6		0.004	mg	474	253
				supplier	alloy	Iron Phosphide (FeP)	26508-33-8		0.007	mg	829	443
Soft solder	Solder	1.069	mg	SVHC	solder	Lead (Pb)	7439-92-1	7a-Lead in high me	0.989	mg	925164	62595
				supplier	solder	Silver (Ag)	7440-22-4		0.026	mg	24322	1646
				supplier	solder	Tin (Sn)	7440-31-5		0.054	mg	50514	3418
Clip	M-004 Copper and its alloys	1.562	mg	supplier	clip	Copper (Cu)	7440-50-8		1.562	mg	1000000	98861
Encapsulation	M-011 Other inorganic materials	3.706	mg	supplier	mold compound	Silica, vitreous	60676-86-0		3.191	mg	861036	201962
				supplier	mold compound	epoxy resin	Proprietary		0.278	mg	75014	17595
				supplier	mold compound	resin	Proprietary		0.167	mg	45062	10570
				supplier	mold compound	Silica Cristobalite	4464-46-1		0.037	mg	9984	2342
connections coating	Solder	0.183	mg	supplier	mold compound	Carbon Black	1333-86-4		0.033	mg	8904	2089
				supplier	solder alloy	Tin (Sn)	7440-31-5		0.183	mg	1000000	11582