



## Materials Declaration Form

<b>IPC Form Type *</b>	1752 Distribute	<b>Version</b>	2
<b>Sectionals *</b>	Material Info Manufacturing Info	<b>Subsectionals *</b>	A-D  <i>* : Required Field</i>

Supplier Information			
<b>Company Name *</b>	STMicroelectronics	<b>Response Date *</b>	2015-06-09
<b>Contact Name *</b>	Refer to "Supplier Comment" section	<b>Contact Title</b>	Refer to "Supplier Comment" section
<b>Contact Phone *</b>	Refer to "Supplier Comment" section	<b>Contact Email *</b>	Refer to "Supplier Comment" section
<b>Authorized Representative *</b>	Giovanni Giacobello	<b>Representative Title</b>	IPD Materials Declaration Champion
<b>Representative Phone *</b>	Refer to "Supplier Comment" section	<b>Representative Email *</b>	Refer to "Supplier Comment" section
<b>Supplier Comment</b>	Online Technical Support - STMicroelectronics : <a href="http://www.st.com/internet/com/support/online_tech_support.jsp">http://www.st.com/internet/com/support/online_tech_support.jsp</a>		

**Uncertainty Statement**


While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement			
<b>Supplier Acceptance *</b>	true	<b>Legal Declaration *</b>	Standard

**Legal Statement**

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
	HNSR*Z24S81Q	A	ZA41	2015-06-09
Amount	UoM	Unit type	ST ECOPACK Grade	
70.00	mg	Each	ECOPACK® 2	

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
1	260	3		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
Not Applicable ; if coating is used c	Tin (Sn), matte	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
SOJ	4.3 x 2.77 x 2	2	J bend	
Comment	Package: SMA; MDF valid for STPS130A			

QueryList : ROHS directive 2011/65/EU _ July 2011	
Query	Response
Product(s) meets EU RoHS requirement without any exemptions	false
Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	false
Product(s) meets EU RoHS requirements by application of the selected exemption(s)	true
Product(s) does not meet EU RoHS requirements and is not under exemptions	false
Product(s) is obsolete, no information is available	false
Product(s) is unknown, no information is available	false
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : REACH-17th December 2014				
Query				Response
The product does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration						Mfr Item Name	HNSR*Z24581Q						
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)	
Die or Dies	Other inorganic materials	0.674	mg	supplier	die	Silicon (Si)	7440-21-3		0.641	mg	951039	9157	
Die or Dies				supplier	metallization	Aluminium (Al)	7429-90-5		0.004	mg	5935	57	
Die or Dies				supplier	metallization	Titanium (Ti)	7440-32-6		0.001	mg	1484	14	
Die or Dies				supplier	metallization	Tungsten (W)	7440-33-7		0.001	mg	1484	14	
Die or Dies				supplier	metallization	Nickel (Ni)	7440-02-0		0.003	mg	4451	43	
Die or Dies				supplier	metallization	Gold (Au)	7440-57-5		0.003	mg	4451	43	
Die or Dies				supplier	passivation	Silicon Oxide(SiO2)	7631-86-9		0.004	mg	5935	57	
Die or Dies				supplier	back side metallization	Gold (Au)	7440-57-5		0.001	mg	1484	14	
Die or Dies				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.004	mg	5935	57	
Die or Dies				supplier	polymer die coating	Durimide	proprietary		0.012	mg	17804	171	
Leadframe & Clip	Copper and its alloy	26.927	mg	supplier	alloy	Copper (Cu)	7440-50-8		26.914	mg	999517	384486	
Leadframe & Clip				supplier	alloy	Zinc (Zn)	7440-66-6		0.001	mg	37	14	
Leadframe & Clip				supplier	alloy	Iron (Fe)	7439-89-6		0.003	mg	111	43	
Leadframe & Clip				supplier	alloy	Iron Phosphide (FeP)	26508-33-8		0.009	mg	334	129	
Soft solder	solder	2.852	mg	supplier	solder	Silver (Ag)	7440-22-4		0.071	mg	24895	1014	
Soft solder				supplier	solder	Tin (Sn)	7440-31-5		0.143	mg	50140	2043	
Soft solder				JIG - R	solder	Lead (Pb)	7439-92-1	7a-Lead in high me	2.638	mg	924965	37686	
encapsulation	Other inorganic materials	38.906	mg	supplier	mold compound	Amorphous Silica	7631-86-9		23.974	mg	616203	342486	
encapsulation				supplier	mold compound	Quartz	14808-60-7		7.781	mg	199995	111157	
encapsulation				supplier	mold compound	epoxy resin	Proprietary		4.669	mg	120007	66700	
encapsulation				supplier	mold compound	phenolic resin	9003-35-4		2.334	mg	59991	33343	
encapsulation				supplier	mold compound	Bismuth trioxide	1304-76-3		0.027	mg	694	386	
encapsulation				supplier	mold compound	chlorine residue	7782-50-5		0.004	mg	103	57	
encapsulation				supplier	mold compound	Carbon black	1333-86-4		0.117	mg	3007	1671	
connections coating	Solder	0.641	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		0.641	mg	1000000	9157	