



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D
<i>* : Required Field</i>			

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2013-10-25
Contact Name *	Refer to "Supplier Comment" section	Contact Title	Refer to "Supplier Comment" section
Contact Phone *	Refer to "Supplier Comment" section	Contact Email *	Refer to "Supplier Comment" section
Authorized Representative *	Giuseppe Vitali Palma	Representative Title	AMS/IPD Materials Declaration Champion)
Representative Phone *	Refer to "Supplier Comment" section	Representative Email *	Refer to "Supplier Comment" section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/internet/com/support/online_tech_support.jsp		

Uncertainty Statement

While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.


Legal Statement

Supplier Acceptance *	true	Legal Declaration *	Standard
------------------------------	------	----------------------------	----------

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
	ZP07*LB15FC2	A	SH1A	2013-10-25
Amount	UoM	Unit type	ST ECOPACK Grade	
80.00	mg	Each	ECOPACK® 2	

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles	 life.augmented	
1	260	3		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy		
Not Applicable ; if coating is used okel/Palladium/Silver/Gold (Ni/Pd/Ag/		Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
DSO	4.85X3.9X1.52	3	gull wing	
Comment	Package: SO 08 .15 JEDEC			

QueryList : ROHS directive 2011/65/EU _ July 2011	
Query	Response
Product(s) meets EU RoHS requirement without any exemptions	true
Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	false
Product(s) meets EU RoHS requirements by application of the selected exemption(s)	false
Product(s) does not meet EU RoHS requirements and is not under exemptions	false
Product(s) is obsolete, no information is available	false
Product(s) is unknown, no information is available	false
Exemption Id.	Description

QueryList :REACH-20th June 2013				
Query				Response
The product does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration						Mfr Item Name	ZPO7*LB15FC2					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
die (s)	Other inorganic materials	0.905	mg	supplier	die	Silicon (Si)	7440-21-3		0.883	mg	975691	11038
				supplier	metallization	Aluminium (Al)	7429-90-5		0.007	mg	7735	88
				supplier	passivation	Silicon Nitride (SiN)	68034-42-4		0.003	mg	3315	38
				supplier	passivation	Silicon Oxide(SiO2)	7631-86-9		0.012	mg	13260	150
Leadframe	Copper & its alloys	35.349	mg	supplier	alloy	Copper (Cu)	7440-50-8		35.256	mg	997369	440700
				supplier	alloy	Iron (Fe)	7439-89-6		0.016	mg	453	200
				supplier	alloy	Iron Phosphide (FeP)	26508-33-8		0.03	mg	849	375
				supplier	metallization	Nickel (Ni)	7440-02-0		0.044	mg	1245	550
				supplier	metallization	Palladium (Pd)	7440-05-3		0.001	mg	28	13
				supplier	metallization	Gold (Au)	7440-57-5		0.001	mg	28	13
Die attach	Other Organic Materials	0.381	mg	supplier	metallization	Silver (Ag)	7440-22-4		0.001	mg	28	13
				supplier	glue	Silver (Ag)	7440-22-4		0.347	mg	910761	4338
				supplier	glue	acrylate	Proprietary		0.019	mg	49869	238
Bonding wire	Other Organic Materials	0.02	mg	supplier	glue	Methacrylate	Proprietary		0.015	mg	39370	188
				supplier	wire	Copper (Cu)	7440-50-8		0.02	mg	1000000	250
				supplier	mold compound	Epoxy Resin	Proprietary		3.251	mg	75003	40638
encapsulation	Other Organic Materials	43.345	mg	supplier	mold compound	Phenol Resin	Proprietary		2.167	mg	49994	27088
				supplier	mold compound	Silica, vitreous	60676-86-0		37.537	mg	866005	469213
				supplier	mold compound	Carbon black	1333-86-4		0.217	mg	5006	2713
				supplier	mold compound	Bismuth (Bi)	7440-69-9		0.173	mg	3991	2163