



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D * : Required Field

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2019-02-13
Company Unique ID	NL 008751171801		
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Contact Phone *	Refer to Supplier Comment section	Contact Email *	Refer to Supplier Comment section
Authorized Representative *	Rossana Bonaccorso	Representative Title	ADG MD Champion
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement


While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement		
Supplier Acceptance *	true	Legal Declaration * Standard

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
BDW93CFP	TSFP*BB03562	A	3068	2019-02-13
Amount	UoM	Unit type	ST ECOPACK Grade	
1900.00	mg	Each	ECOPACK2	
	Comment	ECOPACK® 2 is STMicroelectronics trade name for ROHS compliant device without Brominated and Chlorinated compound (900ppm) and without Antimony oxide flame retardant (in each organic material)		

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles	 life.augmented	
NA	NA	NA		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy		
NA	Tin (Sn), matte	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape
SIP	10.2-16.15-4.5	3	Through-hole
Comment	TO 220 ISO FULL PACK IN LINE		

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-March 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : ELV directive : 2000/53/EC amended 2017/2096 _November 2017	
Query	Response
1 - Product(s) meets EU ELV requirements without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
Exemption Id.	Description
8e	Lead in high melting temperature type solders (i.e. lead-based alloys containing 85 % by weight or more lead)

QueryList : California Prop65 list, dated 23rd November 2018			
Query			Response
1 - The product does not contain identified substance from California Prop 65 List, no exposure to consumers is foreseen			FALSE
2 - The product is containing below substance(s) from California Prop 65 List, no exposure to consumers is foreseen			TRUE
Substance	amount in product (mg)	Application	ppm in product
Nickel	0.68	Die - Leadframe	357
Lead	3.37	Soft solder	1775

QueryList : REACH-15th January 2019				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				FALSE
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product
Lead	1000 ppm	3.37	Soft solder	1775
2 - Product(s) does not contain REACH Substances Of Very High Concern in any Embedded article nor Homogeneous Material above the limits per the definition within REACH				FALSE
CategoryLevel_Name	CategoryLevel_Threshold	Amount in Embedded Article / Homogeneous Material (mg)	Application - Article / Homogeneous Material	ppm in Article /Homogeneous Material
Lead	1000 ppm	3.37	Soft solder	954970

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	TSFP*BB03562					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	M-011 Other inorganic materials	3.090	mg	supplier	die	Silicon (Si)	7440-21-3		2.962	mg	958514	1559
				supplier	metallization	Aluminium (Al)	7429-90-5		0.045	mg	14562	24
				supplier	Passivation	Silicon Oxide	7631-86-9		0.051	mg	16504	27
				supplier	back side metallization	Chromium (Cr)	7440-47-3		0.016	mg	5178	8
				supplier	back side metallization	Gold (Au)	7440-57-5		0.011	mg	3560	6
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.005	mg	1618	3
Leadframe	M-004 Copper and its alloys	605.984	mg	supplier	back side metallization	Arsenic (As)	7440-38-2		0.000	mg	64	0
				supplier	alloy	Copper (Cu)	7440-50-8		604.468	mg	997498	318141
				supplier	alloy	Iron (Fe)	7439-89-6		0.605	mg	998	318
				supplier	alloy	Iron Phosphide (FeP)	26508-33-8		0.182	mg	300	96
				supplier	metallization	Nickel (Ni)	7440-02-0		0.674	mg	1112	355
				supplier	metallization	Phosphorus (P)	7723-14-0		0.055	mg	92	29
Soft solder	Solder	3.531	mg	JIG - R	solder	Lead (Pb)	7439-92-1	7a-Lead in high mel	3.372	mg	954970	1775
				supplier	solder	Silver (Ag)	7440-22-4		0.088	mg	24922	46
				supplier	solder	Tin (Sn)	7440-31-5		0.071	mg	20108	38
Bonding wires	M-011 Other inorganic materials	1.810	mg	supplier	wire	Aluminium (Al)	7429-90-5		1.810	mg	1000000	953
Encapsulation	M-011 Other inorganic materials	1279.719	mg	supplier	mold compound	Quartz	14808-60-7		895.803	mg	700000	471475
				supplier	mold compound	Silica, vitreous	60676-86-0		95.979	mg	75000	50515
				supplier	mold compound	Epoxy resin	25068-38-6		179.161	mg	140000	94295
				supplier	mold compound	phenol resin	29690-82-2		89.580	mg	70000	47147
				supplier	mold compound	metal hydroxide	21645-51-2		12.797	mg	10000	6735
				supplier	mold compound	carbon black	1333-86-4		6.399	mg	5000	3368
Connections coating	Solder	5.866	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		5.866	mg	1000000	3087