




Materials Declaration Form

| | | | |
|---------------------------|-------------------------------------|------------------------|-----|
| IPC Form Type * | 1752 Distribute | Version | 2 |
| Sectionals * | Material Info Manufacturing Info | Subsectionals * | A-D |
| <i>* : Required Field</i> | | | |

| Supplier Information | | | |
|------------------------------------|--|-------------------------------|-----------------------------------|
| Company Name * | STMicroelectronics | Response Date * | 26-06-2018 |
| Company Unique ID | NL 008751171B01 | | |
| Contact Name * | Refer to Supplier Comment section | | Refer to Supplier Comment section |
| Contact Phone * | Refer to Supplier Comment section | Contact Email * | Refer to Supplier Comment section |
| Authorized Representative * | MDG MD CHAMPION | Representative Title | MDG MD CHAMPION |
| Representative Phone * | Refer to Supplier Comment section | Representative Email * | Refer to Supplier Comment section |
| Supplier Comment | Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html | | |

| Uncertainty Statement | | | |
|---|--|----------------------------|----------|
| <p>While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.</p> | | | |
| Legal Statement | | | |
| Supplier Acceptance * | true | Legal Declaration * | Standard |
| Legal Statement | <p>Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.</p> | | |

| Product | | | | |
|-----------------|---------------|---|-----------|------------------|
| Mfr Item Number | Mfr Item Name | Version | Mfr Site | Date |
| STM8AL31E88TCX | U35B*79KX11Z | A | 959 | 26-06-2018 |
| | Amount | UoM | Unit type | ST ECOPACK Grade |
| | 180.00 | mg | Each | ECOPACK® 2 |
| | Comment | ECOPACK® 2 is STMicroelectronics trade name for ROHS compliant device without Brominated and Chlorinated compound (900ppm) and without Antimony oxide flame retardant (in each organic material) | | |

| Manufacturing information | | | | |
|---------------------------|---------------------|----------------------|---------|---|
| J-STD-020 MSL Rating | Classification Temp | Nbr of Reflow Cycles | |  life.augmented |
| 3 | 260 | 3 | | |
| bulk Solder Termination | Terminal Plating | Terminal Base Alloy | Comment | |
| NAC | NiPdAu | Copper Alloy | | |

| Package Designator | Size | Nbr of instances | Shape | |
|--------------------|--|------------------|--------|--|
| QFP | 7x7x1.4 | 48 | L Bend | |
| Comment | Package : 58 LQFP 48 7x7x1.4 1 0110596 | | | |

| QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-April 2015 | |
|--|-------------|
| Query | Response |
| 1 - Product(s) meets EU RoHS requirement without any exemptions | TRUE |
| 2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply) | FALSE |
| 3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s) | FALSE |
| 4 - Product(s) does not meet EU RoHS requirements and is not under exemptions | FALSE |
| Exemption Id. | Description |
| | |

| QueryList : REACH-12th January 2017 | | | | |
|--|-------------------------|------------------------|-------------|----------------|
| Query | | | | Response |
| 1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH | | | | TRUE |
| CategoryLevel_Name | CategoryLevel_Threshold | amount in product (mg) | Application | ppm in product |
| | | | | |

| Material Composition Declaration : | | | | | | Mfr Item Name | U35B*79KX112 | | | | 7000002.0 | 999999.0 |
|--|---------------------------------|--------|-----|----------|---------------------------|---|--------------|--------|--------|-----|---|--------------------------------|
| note : Substance present with less 0.001mg will not be declared in this document | | | | | | | | | | | | |
| Homogeneous Material | Material Group | Mass | UoM | Level | Substance Category | Substance | CAS | Exempt | Mass | UoM | Concentration in homogeneous material (ppm) | Concentration in product (ppm) |
| Die or dies | M-011 Other inorganic materials | 6.683 | mg | supplier | die | Silicon (Si) | 7440-21-3 | | 6.501 | mg | 972767 | 36117 |
| | | | | supplier | metallization | Aluminium (Al) | 7429-90-5 | | 0.016 | mg | 2394 | 89 |
| | | | | supplier | metallization | Copper (Cu) | 7440-50-8 | | 0.053 | mg | 7931 | 294 |
| | | | | supplier | metallization | Tantalum (Ta) | 7440-25-7 | | 0.006 | mg | 898 | 33 |
| | | | | supplier | metallization | Titanium (Ti) | 7440-32-6 | | 0.008 | mg | 1197 | 44 |
| | | | | supplier | Passivation | Silicon Nitride | 12033-89-5 | | 0.014 | mg | 2095 | 78 |
| | | | | supplier | Passivation | Silicon Oxide | 7631-86-9 | | 0.085 | mg | 12719 | 472 |
| Lead-frame | M-011 Other inorganic materials | 75.592 | mg | supplier | alloy | Copper (Cu) | 7440-50-8 | | 72.936 | mg | 964855 | 405199 |
| | | | | supplier | alloy | Nickel (Ni) | 7440-02-0 | | 2.097 | mg | 27746 | 11652 |
| | | | | supplier | alloy | Silicium (Si) | 7440-21-3 | | 0.454 | mg | 6012 | 2525 |
| | | | | supplier | alloy | Magnesium (Mg) | 7439-95-4 | | 0.105 | mg | 1387 | 583 |
| Lead-frame Coating | M-011 Other inorganic materials | 0.403 | mg | supplier | coating | Nickel (Ni) | 7440-02-0 | | 0.369 | mg | 914840 | 2048 |
| | | | | supplier | coating | Palladium (Pd) | 7440-05-3 | | 0.012 | mg | 29660 | 66 |
| | | | | supplier | coating | Gold (Au) | 7440-57-5 | | 0.011 | mg | 27750 | 62 |
| | | | | supplier | coating | Silver (Ag) | 7440-22-4 | | 0.011 | mg | 27750 | 62 |
| Die Attach | M-011 Other inorganic materials | 1.954 | mg | supplier | glue or soft solder | Silver (Ag) | 7440-22-4 | | 1.505 | mg | 770000 | 8359 |
| | | | | supplier | glue or soft solder | Epoxy Cresol Novolak | 29690-82-2 | | 0.442 | mg | 226000 | 2454 |
| | | | | supplier | glue or soft solder | 1-isopropyl-2,2-dimethyltrimethylene diisobut | 6846-50-0 | | 0.008 | mg | 4000 | 43 |
| Wires | M-011 Other inorganic materials | 0.913 | mg | supplier | Bonding wire | Gold (Au) | 7440-57-5 | | 0.913 | mg | 1000000 | 5074 |
| Encapsulation | M-011 Other inorganic materials | 94.452 | mg | supplier | Moulding Compound | Solid Epoxy Resin | Proprietary | | 6.786 | mg | 71847 | 37700 |
| | | | | supplier | Moulding Compound | Phenol Resin | Proprietary | | 4.847 | mg | 51319 | 26929 |
| | | | | supplier | Moulding Compound | Silica, vitreous | 60676-86-0 | | 82.043 | mg | 868623 | 455794 |
| | | | | supplier | Moulding Compound | Carbon-black | 1333-86-4 | | 0.485 | mg | 5132 | 2693 |
| | | | | supplier | Moulding Compound | Bismuth (Bi) | 7440-69-9 | | 0.145 | mg | 1540 | 808 |
| Finishing | M-011 Other inorganic materials | 0.002 | mg | supplier | Bismuth/Bismuth Compounds | Bismuth | 7440-69-9 | | 0.145 | mg | 1540 | 808 |
| | | | | supplier | connections coating | Nickel (Ni) | 7440-02-0 | | 0.002 | mg | 1000000 | 13 |