



Material Composition Declaration

© Copyright 2005. IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.

This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.

Adobe Reader version 7.0.5 is required to complete this declaration.

1752-2 1.1	IPC Web Site for Information on IPC-1752 Standard http://www.ipc.org/IPC-175x	Form Type * Distribute	Declaration Class * Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Informat
------------	--	---------------------------	--

Supplier Information

Company Name * STMicroelectronics	Company Unique ID	Unique ID Authority	Response Date *	Response Document ID				
Contact Name *	Title - Contact	Phone - Contact *	Email - Contact *	<input type="button" value="Duplicate Contact -> Authorized Representative"/>				
Authorized Representative * GIOVANNI GIACOPELLO	Title - Representative APM MD CHAMPION	Phone - Representative *	Email - Representative *	Supplier Comments or URL for Additional Information				
Requester Item Number	Mfr Item Number	Mfr Item Name	Effective Date	Version	Manufacturing Site	Weight *	UOM	Unit Type
	SMP50-100	8HST*CWB100M	2009-09-28	A	BO2A	70	mg	Each
Alternate Recommendation	SMA Package			Alternate Item Comments	BSA: CD00243089			

Manufacturing Process Information

Terminal Plating / Grid Array Material Matte Tin (Sn) - annealed	Terminal Base Alloy CU Alloy	J-STD-020 MSL Rating 1	Peak Process Body Temperature 260 C	Max Time at Peak Temperature 30 seconds	Number of Reflow Cycles 3
---	---------------------------------	---------------------------	--	--	------------------------------

Comments

Disclaimer: While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and

Save the fields in this form to a file

Export Data

Import fields from a file into this form

Import Data

Clear all of the fields on this form

Reset Form

Lock the fields on this form to prevent changes

Lock Supplier Fields

RoHS Material Composition Declaration

Declaration Type *

Simplified

RoHS Directive 2002/95/EC **RoHS Definition:** Quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material for Cadmium

Supplier certifies that it gathered the information it provides in this form concerning RoHS restrictive substances using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

RoHS Declaration *

3 - Item(s) does not contain RoHS restricted substances per the definition above except for lead in solders and selected exemptions, if any

Supplier Acceptance *

Accepted

Exemptions: If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions.

Exemption List Version

EL-2006/690/EC

+

-

7a. Lead in high melting temperature type solders (i.e. lead based solder alloys containing 85% by weight or more lead).

Declaration Signature

Instructions: Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.

Supplier Digital Signature

Homogeneous Material Composition Declaration for Electronic Products

SubItem Instructions: The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

Substance Instructions: [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

Line Functions: +I Inserts a New Item /SubItem +M Inserts a new Material +C Inserts a new Substance Category +S Inserts a new Substance - Deletes the element line

		Item/SubItem Name		Homogeneous Material		Weight	Unit of Measure	Level		Substance Category		Substance		CAS	Exempt	Weight	Unit of Measure	Tolerance		PPM		
																		-	+			
+I	-I	8HST*CWB100M		+M	-M	Silicon Die	0.904	mg	+C	-C	Supplier	Silicon die	+S	-S	Silicon	7440-21-3		0.879	mg			972,34
									+C	-C	Supplier	die metallization	+S	-S	Aluminium(Al)	7429-90-5		0.01	mg			11,062
													+S	-S	Nickel (Ni)	7440-02-0		0.011	mg			12,168
													+S	-S	Gold(Au)	7440-57-5		0.004	mg			4,425
		+M	-M	Leadframe		31.553	mg	+C	-C	supplier	alloy		+S	-S	Copper (Cu)	7440-50-8		31.512	mg			998,70
													+S	-S	Iron (Fe)	7439-89-6		0.032	mg			1,014
													+S	-S	Iron Phosphide (FeP)	26508-33-8		0.009	mg			285
		+M	-M	Leadframe coating		0.47	mg	+C	-C	supplier	coating		+S	-S	Nickel (Ni)	7440-02-0		0.466	mg			991,48
													+S	-S	Phosphorus (P)	7723-14-0		0.004	mg			8,511
		+M	-M	Die Attach		0.587	mg	+C	-C	A	Lead/Lead Compound		+S	-S	Lead (Pb)	7439-92-1	7a. Lead	0.549	mg			935,26
									+C	-C	supplier	soft solder	+S	-S	Silver (Ag)	7440-22-4		0.009	mg			15,332
													+S	-S	Tin (Sn)	7440-31-5		0.029	mg			49,404
		+M	-M	Clips		14.211	mg	+C	-C	Supplier	Clips		+S	-S	Copper (Cu)	7440-50-8		14.211	mg			1,000,0
		+M	-M	Encapsulation		21.217	mg	+C	-C	Supplier	Moulding Compound		+S	-S	Silica, vitreous	60676-86-0		17.186	mg			810,01
													+S	-S	Phenol resin	9003-35-4		1.273	mg			59,999
													+S	-S	Carbon black	1333-86-4		0.17	mg			8,012
													+S	-S	Epoxy Cresol Novolak	29690-82-2		2.164	mg			101,99
													+S	-S	Metal hydroxide	Proprietary		0.424	mg			19,984
		+M	-M	Finishing		1.058	mg	+C	-C	supplier	connection coating		+S	-S	Tin (Sn)	7440-31-5		1.058	mg			1,000,0