



## Materials Declaration Form

<b>IPC Form Type *</b>	1752 Distribute	<b>Version</b>	2
<b>Sectionals *</b>	Material Info Manufacturing Info	<b>Subsectionals *</b>	A-D  <i>* : Required Field</i>

Supplier Information			
<b>Company Name *</b>	STMicroelectronics	<b>Response Date *</b>	28-07-2017
<b>Company Unique ID</b>	NL 008751171801		
<b>Contact Name *</b>	Refer to Supplier Comment section		Refer to Supplier Comment section
<b>Contact Phone *</b>	Refer to Supplier Comment section	<b>Contact Email *</b>	Refer to Supplier Comment section
<b>Authorized Representative *</b>	MDG MD CHAMPION	<b>Representative Title</b>	MDG MD CHAMPION
<b>Representative Phone *</b>	Refer to Supplier Comment section	<b>Representative Email *</b>	Refer to Supplier Comment section
<b>Supplier Comment</b>	Online Technical Support - STMicroelectronics : <a href="http://www.st.com/web/en/support/support.html">http://www.st.com/web/en/support/support.html</a>		

**Uncertainty Statement**

While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

**Legal Statement**


<b>Supplier Acceptance *</b>	true	<b>Legal Declaration *</b>	Standard
------------------------------	------	----------------------------	----------

**Legal Statement**

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STM32F334K8T6 STM32F334K8T6TR	S15V*438XXZ	A	998Z	28-07-2017
Amount	UoM	Unit type	ST ECOPACK Grade	
197,06	mg	Each	ECOPACK® 2	
.	Comment	ECOPACK® 2 is STMicroelectronics trade name for ROHS compliant device without Brominated and Chlorinated compound (900ppm) and without Antimony oxide flame retardant ( in each organic material)		

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		
3	260	3		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
Not Applicable; if coating is used or other bulk termination	Tin (Sn), matte	Copper Alloy		


  
 life.augmented

Package Designator	Size	Nbr of instances	Shape	
QFP	7x7X1.4	#REF!	L Bend	
Comment	Package : 5V LQFP 32 7x7x1.4 1 0060661			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-April 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	TRUE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	FALSE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description

QueryList : REACH-12th January 2017				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				TRUE
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	S15V*438XXZ				6000000.0	0.0
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die or dies	M-011 Other inorganic materials	13,621	mg	supplier	die	Silicon (Si)	7440-21-3		13,064	mg	959107	66296
				supplier	metallization	Aluminium (Al)	7429-90-5		0,038	mg	2790	193
				supplier	metallization	Copper (Cu)	7440-50-8		0,189	mg	13876	959
				supplier	metallization	Cobalt (Co)	7440-48-4		0,035	mg	2570	178
				supplier	metallization	Titanium (Ti)	7440-32-6		0,010	mg	734	51
				supplier	metallization	Tungsten (W)	7440-33-7		0,021	mg	1542	107
				supplier	Passivation	Silicon Nitride	12033-89-5		0,025	mg	1835	127
				supplier	Passivation	Silicon Oxide	7631-86-9		0,239	mg	17546	1213
Die Attach Epoxy_ABLEBOND 3230_H	M-011 Other inorganic materials	0,896	mg	Supplier	Metals	Silver	7440-22-4		0,807	mg	901000	4095
				Supplier	Plastics/polymers	Highly cross-linked polymer	Proprietary		0,089	mg	99000	450
Mold Compound_EME-G631SHQ_Sun	M-011 Other inorganic materials	111,537	mg	Supplier	Plastics/polymers	Epoxy Resin A	Proprietary		2,488	mg	21000	12625
				Supplier	Plastics/polymers	Epoxy Resin B	Proprietary		2,488	mg	21000	12625
				Supplier	Plastics/polymers	Phenol Resin	Proprietary		6,634	mg	56000	33667
				Supplier	Glass	Silica(Amorphous)A	60676-86-0		85,527	mg	780450	-565978
				Supplier	Glass	Silica(Amorphous)B	7631-86-9		13,662	mg	115320	69330
Wire_AG SI TYPE_MKE	Bonding Wire	0,253	mg	Supplier	Non-metals	Carbon Black	1333-86-4		0,738	mg	6230	3745
				Supplier	Metals	Silver	7440-22-4		0,243	mg	960000	1233
				Supplier	Metals	Others	Proprietary		0,010	mg	40000	51
Plating anode_Pure Tin_Nuo Nengda	M-011 Other inorganic materials	1,209	mg	Supplier	Metals	Tin	7440-31-5		1,209	mg	1000000	6136
Leadframe_C9+Ag_HDS	Copper & its alloys	69,540	mg	Supplier	Metals	Iron	7439-89-6		1,520	mg	21865	7716
				Supplier	Non-metals	Phosphorus	7723-14-0		0,051	mg	730	258
				Supplier	Metals	Zinc	7440-66-6		0,078	mg	1125	397
				Supplier	Metals	Copper	7440-50-8		63,506	mg	913235	322277
				Supplier	Metals	Silver	7440-22-4		4,381	mg	63000	22232
				JIG-R	Metals	Lead	7439-92-1		0,003	mg	45	16