



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D <i>* : Required Field</i>

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2018-02-06
Company Unique ID	NL 008751171B01		
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Contact Phone *	Refer to Supplier Comment section	Contact Email *	Refer to Supplier Comment section
Authorized Representative *	Giovanni Giacopello	Representative Title	ADG MD Champion
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement


While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement		
Supplier Acceptance *	true	Legal Declaration *
		Standard

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
TN1215-800B-TR	BGDP*P1G128S	A	998G	2018-02-06
	Amount	UoM	Unit type	ST ECOPACK Grade
	320	mg	Each	ECOPACK2

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
1	260	3		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
NA	Tin (Sn), matte	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
SIP	6.5-6.1-2.3	3	GULL WING	
Comment	TO 252 DPAK			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-April 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)
7c-I	Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound

QueryList : California Prop65 list, dated 15th December 2017			
Query			Response
1 - The product does not contain identified substance from California Prop 65 List, no exposure to consumers is foreseen			FALSE
2 - The product is containing below substance(s) from California Prop 65 List, no exposure to consumers is foreseen			TRUE
Substance	amount in product (mg)	Application	ppm in product
Nickel	1.15	Die - Leadframe	3594
Lead	4.10	Soft solder	12809
Lead-Borate Glass	0.58	Die	1825

QueryList : REACH-15th January 2018				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product
2 - Product(s) does not contain REACH Substances Of Very High Concern in any Embedded article nor Homogeneous Material above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	Amount in Embedded Article / Homogeneous Material (mg)	Application - Article / Homogeneous Material	ppm in Article /Homogeneous Material

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	BGDP*P1G1285					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	M-011 Other inorganic materials	4.061	mg	supplier	die	Silicon (Si)	7440-21-3		3.275	mg	806452	10234
				supplier	metallization	Aluminium (Al)	7429-90-5		0.100	mg	24624	313
				supplier	metallization	Gold (Au)	7440-57-5		0.011	mg	2709	34
				supplier	metallization	Nickel (Ni)	7440-02-0		0.017	mg	4186	53
				supplier	Passivation	Silicon Oxide	7631-86-9		0.026	mg	6402	81
				supplier	back side metallization	Aluminium (Al)	7429-90-5		0.016	mg	3940	50
				supplier	back side metallization	Gold (Au)	7440-57-5		0.006	mg	1478	19
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.026	mg	6402	81
Leadframe	M-004 Copper and its alloys	166.051	mg	JIG - R & California 65	glass coating	Lead-Borate Glass	65997-18-4	7c-4-Electrical and e	0.584	mg	143807	1825
				supplier	alloy	Copper (Cu)	7440-50-8		164.729	mg	992039	514778
				supplier	alloy	Iron (Fe)	7439-89-6		0.165	mg	993	516
				supplier	alloy	Iron Phosphide (FeP)	26508-33-8		0.050	mg	301	156
				supplier	metallization	Nickel (Ni)	7440-02-0		1.107	mg	6667	3459
Soft solder	Solder	3.681	mg	JIG - R	solder	Lead (Pb)	7439-92-1	7a-Lead in high mel	3.515	mg	954904	10984
				supplier	solder	Silver (Ag)	7440-22-4		0.092	mg	24993	288
				supplier	solder	Tin (Sn)	7440-31-5		0.074	mg	20103	231
Bonding wires	M-011 Other inorganic materials	0.473	mg	supplier	wire	Aluminium (Al)	7429-90-5		0.473	mg	1000000	1478
Encapsulation	M-011 Other inorganic materials	144.689	mg	supplier	mold compound	Silica, vitreous	60676-86-0		129.858	mg	897497	405806
				supplier	mold compound	Epoxy resin	25068-38-6		10.128	mg	69998	31650
				supplier	mold compound	Phenol resin	29690-82-2		4.341	mg	30002	13566
				supplier	mold compound	carbon black	1333-86-4		0.362	mg	2503	1131
connections coating	Solder	1.045	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		1.045	mg	1000000	3266