



Material Composition Declaration

© Copyright 2005. IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.

This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.

Adobe Reader version 7.0.5 is required to complete this declaration.

1752-2 1.1	IPC Web Site for Information on IPC-1752 Standard http://www.ipc.org/IPC-175x	Form Type * Distribute	Declaration Class * Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Informat
------------	--	---------------------------	--

Supplier Information

Company Name * STMicroelectronics	Company Unique ID	Unique ID Authority	Response Date * 2010-11-19	Response Document ID PT6P*95641KA
Contact Name *	Title - Contact	Phone - Contact *	Email - Contact *	<input type="button" value="Duplicate Contact -> Authorized Representative"/>
Authorized Representative * Laurent Tosi	Title - Representative MMS Central Packaging	Phone - Representative * +33 442 685 795	Email - Representative * laurent.tosi@st.com	Supplier Comments or URL for Additional Information

Requester Item Number	Mfr Item Number	Mfr Item Name	Effective Date	Version	Manufacturing Site	Weight *	UOM	Unit Type
		TSSOP 8 BODY 4.4 PITCH 0.65	2010-11-19	A	Shenzhen	34	mg	Each
Alternate Recommendation				Alternate Item Comments				

Manufacturing Process Information

Terminal Plating / Grid Array Material Nickel/Palladium/Gold (Ni/Pd/Au)	Terminal Base Alloy CU Alloy	J-STD-020 MSL Rating 1	Peak Process Body Temperature 260 C	Max Time at Peak Temperature 30 seconds	Number of Reflow Cycles 3
--	---------------------------------	---------------------------	--	--	------------------------------

Comments
Ecopack 2 compliant: means Br-Cl & Sb oxide free. DISCLAIMER: While STMicroelectronics has endeavored to provide information which is accurate and up to date, this docum

Save the fields in this form to a file

Export Data

Import fields from a file into this form

Import Data

Clear all of the fields on this form

Reset Form

Lock the fields on this form to prevent changes

Lock Supplier Fields

RoHS Material Composition Declaration

Declaration Type *

Simplified

RoHS Directive 2002/95/EC **RoHS Definition:** Quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material for Cadmium

Supplier certifies that it gathered the information it provides in this form concerning RoHS restrictive substances using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

RoHS Declaration * 1 - Item(s) does not contain RoHS restricted substances per the definition above

Supplier Acceptance * Accepted

Exemptions: If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions.

Declaration Signature

Instructions: Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.

Supplier Digital Signature

Homogeneous Material Composition Declaration for Electronic Products

SubItem Instructions: The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

Substance Instructions: [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

Line Functions: +I Inserts a New Item /SubItem +M Inserts a new Material +C Inserts a new Substance Category +S Inserts a new Substance - Deletes the element line

+I	-I	Item/SubItem Name	+M	-M	Homogeneous Material	Weight	Unit of Measure	+C	-C	Level	Substance Category	+S	-S	Substance	CAS	Exempt	Weight	Unit of Measure	Tolerance		PPM
																			-	+	
		TSSOP 8 BODY 4.4			Chip	0.719622	mg			Supplier	silicon die			Silicium (Si)	7440-21-3		0.718522	mg			21,133
										Supplier	die metallization			Aluminium(Al)	7429-90-5		0.000414	mg			12.197
														Copper (Cu)	7440-50-8		0.000455	mg			13.402
														Titanium (Ti)	7440-32-6		0.000230	mg			6.7764
					Lead-frame	14.51685	mg			Supplier	alloy			Copper (Cu)	7440-50-8		14.14667	mg			416,07
														Iron (Fe)	7439-89-6		0.340565	mg			10,016
														Zinc (Zn)	7440-66-6		0.017420	mg			512.35
														Iron Phosphide (FeP)	26508-33-8		0.012194	mg			358.65
					Lead-frame Coat	0.09846	mg			Supplier	coating			Nickel (Ni)	7440-02-0		0.090269	mg			2,654.9
														Palladium (Pd)	7440-05-3		0.005779	mg			169.99
														Gold (Au)	7440-57-5		0.002412	mg			70.950
					Die Attach	0.254642	mg			Supplier	glue or soft solder			Silver (Ag)	7440-22-4		0.203713	mg			5,991.5
														2,6-Diglycidylphenyl all	13561-08-5		0.038196	mg			1,123.4
														1,4-bis (2,3-epoxyprop	2425-79-8		0.005092	mg			149.78
														Polyoxypropylenediam	9046-10-0		0.007639	mg			224.68
					Wires	0.039433	mg			Supplier	Bonding wire			Gold (Au)	7440-57-5		0.039433	mg			1,159.8
					Encapsulation	18.37	mg			Supplier	Moulding Compound			Epoxy Resin	na		1.37775	mg			40,522
														Phenol Resin	na		0.9185	mg			27,014
														Silicon Dioxide	60676-86-0		15.90842	mg			467,89
														Carbon-black	1333-86-4		0.09185	mg			2,701.4
										B	Bismuth/Bismuth Com			Bismuth	7440-69-9		0.07348	mg			2,161.1
					Finishing	0.000984	mg			Supplier	connections coating			Nickel (Ni)	7440-02-0		0.000902	mg			26.549
														Palladium (Pd)	7440-05-3		0.000057	mg			1.6999

+S	-S	Gold (Au)	7440-57-5		0.00024mg			0.7095
----	----	-----------	-----------	--	-----------	--	--	--------