



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D *: Required Field

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2014-05-23
Contact Name *	Refer to "Supplier Comment" section	Contact Title	Refer to "Supplier Comment" section
Contact Phone *	Refer to "Supplier Comment" section	Contact Email *	Refer to "Supplier Comment" section
Authorized Representative *	Antonella Lanzafame	Representative Title	AMS & IPD Materials Declaration Champion
Representative Phone *	Refer to "Supplier Comment" section	Representative Email *	Refer to "Supplier Comment" section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/internet/com/support/online_tech_support.jsp		

Uncertainty Statement

While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.


Legal Statement

Supplier Acceptance *	true	Legal Declaration *	Standard
------------------------------	------	----------------------------	----------

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
	AB6Y*G38J2AR	A	BO2A	2014-05-23
Amount	UoM	Unit type	ST ECOPACK Grade	
50.00	mg	Each	ECOPACK® 2	

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
1	260	3		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
Not Applicable ; if coating is used o	Tin (Sn), matte, annealed	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
SOJ	3.75 - 4.3 - 0.98	2	J bend	
Comment	SMB Flat NEP; MD valid for CP: STTH3L06UFY			

QueryList : ROHS directive 2011/65/EU _ July 2011	
Query	Response
Product(s) meets EU RoHS requirement without any exemptions	false
Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	false
Product(s) meets EU RoHS requirements by application of the selected exemption(s)	true
Product(s) does not meet EU RoHS requirements and is not under exemptions	false
Product(s) is obsolete, no information is available	false
Product(s) is unknown, no information is available	false
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : REACH-16th December 2013				
Query				Response
The product does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration						Mfr Item Name	AB6Y*G38J2AR					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
die (s)	Other inorganic materials	1.471	mg	supplier	die	Silicon (Si)	7440-21-3		1.402	mg	953093	28040
die (s)				supplier	metallization	Aluminium (Al)	7429-90-5		0.041	mg	27872	820
die (s)				supplier	passivation	Gamma-butyrolactone	96-48-0		0.01	mg	6798	200
die (s)				supplier	passivation	Polyhydroxyamide	55295-98-2		0.004	mg	2719	80
die (s)				supplier	back side metallization	Titanium (Ti)	7440-32-6		0.001	mg	680	20
die (s)				supplier	back side metallization	Gold (Au)	7440-57-5		0.002	mg	1360	40
die (s)				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.011	mg	7478	220
Leadframe	Copper & its alloys	19.191	mg	supplier	alloy	Copper (Cu)	7440-50-8		19.166	mg	998697	383320
Leadframe				supplier	alloy	Iron (Fe)	7439-89-6		0.009	mg	469	180
Leadframe				supplier	alloy	Iron Phosphide (FeP)	26508-33-8		0.016	mg	834	320
Soft solder	Solder	0.86	mg	JIG R	solder	Lead (Pb)	7439-92-1	7a-Lead in high me	0.821	mg	954651	16420
Soft solder				supplier	solder	Silver (Ag)	7440-22-4		0.022	mg	25581	440
Soft solder				supplier	solder	Tin (Sn)	7440-31-5		0.017	mg	19767	340
Bonding wire	Other inorganic materials	0.145	mg	supplier	wire	Copper (Cu)	7440-50-8		0.145	mg	1000000	2900
encapsulation	Other Organic Materials	27.603	mg	supplier	mold compound	Silica, vitreous	60676-86-0		24.153	mg	875014	483060
encapsulation				supplier	mold compound	Epoxy Resin	85954-11-6		1.104	mg	39996	22080
encapsulation				supplier	mold compound	Epoxy resin	Proprietary		1.104	mg	39996	22080
encapsulation				supplier	mold compound	Phenol Resin	26834-02-6		1.104	mg	39996	22080
encapsulation				supplier	mold compound	Carbon black	1333-86-4		0.138	mg	4999	2760
connections coating	Solder	0.73	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		0.73	mg	1000000	14600