



Material Composition Declaration

© Copyright 2005. IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.

This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.

Adobe Reader version 7.0.5 is required to complete this declaration.

1752-2 1.1	IPC Web Site for Information on IPC-1752 Standard http://www.ipc.org/IPC-175x	Form Type * Distribute	Declaration Class * Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Informat
------------	--	---------------------------	--

Supplier Information

Company Name * STMicroelectronics	Company Unique ID	Unique ID Authority	Response Date *	Response Document ID				
Contact Name *	Title - Contact	Phone - Contact *	Email - Contact *	Duplicate Contact -> Authorized Representative				
Authorized Representative * Emilio Castelli	Title - Representative APG Material Declaration Cham	Phone - Representative *	Email - Representative *	Supplier Comments or URL for Additional Information				
Requester Item Number	Mfr Item Number	Mfr Item Name	Effective Date	Version	Manufacturing Site	Weight *	UOM	Unit Type
	L99LD01	A55V*UQ49BA6	2012-04-10	A	MU1A	185.1	mg	Each
Alternate Recommendation	LQFP 32 7x7x1.4			Alternate Item Comments	Internal ST reference: BSA: CD00290399 EcoPack2			

Manufacturing Process Information

Terminal Plating / Grid Array Material Nickel/Palladium/Gold (Ni/Pd/Au)	Terminal Base Alloy CU Alloy	J-STD-020 MSL Rating 3	Peak Process Body Temperature 260 C	Max Time at Peak Temperature 30 seconds	Number of Reflow Cycles 3
--	---------------------------------	---------------------------	--	--	------------------------------

Comments

Disclaimer: While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and

Save the fields in this form to a file

Export Data

Import fields from a file into this form

Import Data

Clear all of the fields on this form

Reset Form

Lock the fields on this form to prevent changes

Lock Supplier Fields

RoHS Material Composition Declaration

Declaration Type *

Simplified

RoHS Directive 2002/95/EC **RoHS Definition:** Quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material for Cadmium

Supplier certifies that it gathered the information it provides in this form concerning RoHS restrictive substances using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

RoHS Declaration * 1 - Item(s) does not contain RoHS restricted substances per the definition above

Supplier Acceptance * Accepted

Exemptions: If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions.

Declaration Signature

Instructions: Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.

Supplier Digital Signature

Homogeneous Material Composition Declaration for Electronic Products

SubItem Instructions: The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

Substance Instructions: [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

Line Functions: +I Inserts a New Item /SubItem +M Inserts a new Material +C Inserts a new Substance Category +S Inserts a new Substance - Deletes the element line

Item/SubItem Name		Homogeneous Material		Weight	Unit of Measure	Level		Substance Category	Substance		CAS	Exempt	Weight	Unit of Measure	Tolerance		PPM										
+I	-I	+M	-M			+C	-C		+S	-S					-	+											
+I	-I			LQFP 32 7x7x1.4	+M	-M		Integrated circuit	12.538	mg	+C	-C	Supplier	Silicon die	+S	-S	Silicon (Si)	7440-21-3			12.444	mg					992,50
								die metallization			+S	-S	Aluminium (Al)	7429-90-5							0.001	mg					80
								die metallization			+S	-S	Copper (Cu)	7440-50-8							0.002	mg					160
								die metallization			+S	-S	Titanium (Ti)	7440-32-6							0.001	mg					80
								die metallization			+S	-S	Chromium (Cr)	7440-47-3							0.001	mg					80
								die metallization			+S	-S	Gold (Au)	7440-57-5							0.002	mg					160
								die metallization			+S	-S	Nickel (Ni)	7440-02-0							0.006	mg					476
								Die coating			+S	-S	Gamma-butyrolactone	96-48-0							0.054	mg					4,307
								Die coating			+S	-S	Polyhydroxyamide	55295-98-2							0.024	mg					1,914
								Die coating			+S	-S	Alcoxysilane	na							0.002	mg					160
								Die coating			+S	-S	Aryl Silicilic Acid	na							0.001	mg					80
		+M	-M	Leadframe			+C	-C	supplier	frame alloy	+S	-S	Copper (Cu)	7440-50-8							59.746	mg					955,60
								frame alloy			+S	-S	Nickel (Ni)	7440-02-0							1.863	mg					29,798
								frame alloy			+S	-S	Silicium (Si)	7440-21-3							0.404	mg					6,462
								frame alloy			+S	-S	Magnesium (Mg)	7439-95-4							0.093	mg					1,487
								frame coating			+S	-S	Nickel (Ni)	7440-02-0							0.387	mg					6,190
								frame coating			+S	-S	Palladium (Pd)	7440-05-3							0.016	mg					255
								frame coating			+S	-S	Gold (Au)	7440-57-5							0.013	mg	0				208
		+M	-M	Die Attach			+C	-C	supplier	glue	+S	-S	Isobornyl Methacrylate	7534-94-3							0.1	mg					55,127
								glue			+S	-S	Bismaleimide resin	na							0.073	mg					40,243
								glue			+S	-S	Silver (Ag)	7440-22-4							1.641	mg					904,63
		+M	-M	Bonding wire			+C	-C	Supplier	Bonding wire	+S	-S	Gold (Au)	7440-57-5							0.83	mg					990,45
								Bonding wire			+S	-S	Copper (Cu)	7440-50-8							0.005	mg					5,967

					+C	-C		Bonding wire	+S	-S	Palladium (Pd)	7440-05-3		0.003	mg			3,580
+M	-M	Encapsulation	107.387	mg	+C	-C	supplier	Moulding Compound	+S	-S	Solid Epoxy Resin	na		8.591	mg			80,000
					+C	-C		Moulding Compound	+S	-S	Phenol Resin	na		4.295	mg			39,996
					+C	-C		Moulding Compound	+S	-S	Silica, vitreous	60676-86-0		93.534	mg			870,99
					+C	-C		Moulding Compound	+S	-S	Carbon-black	1333-86-4		0.537	mg			5,001
					+C	-C	B	Moulding Compound	+S	-S	Bismuth (Bi)	7440-69-9		0.43	mg			4,004