



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D
<i>* : Required Field</i>			

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2016-03-01
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Authorized Representative *	Rossana Bonaccorso	Representative Title	IPD MD Champion
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement


While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement			
Supplier Acceptance *	true	Legal Declaration *	Standard

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STI24N60M2	TLI7*MQ6HH62	A	SHENZHEN B/E	2016-03-01
Amount		UoM	Unit type	ST ECOPACK Grade
1500.00		mg	Each	ECOPACK2

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles	 life.augmented	
NAC	NAC	NAC		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
NAC	Tin (Sn), matte	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
SIP	4.5, 10.2, 10.55	2	THROUGH HOLE	
Comment	I2PAK			

QueryList : ROHS directive 2011/65/EU _ July 2011	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	false
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	false
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	true
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	false
5 - Product(s) is obsolete, no information is available	false
6 - Product(s) is unknown, no information is available	false
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : REACH-17th December 2015				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration						Mfr Item Name	TLI7*MQ6HH62					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	Other inorganic materials	11.478	mg	supplier	die	Silicon (Si)	7440-21-3		11.023	mg	960359	7349
				supplier	metallization	Aluminium (Al)	7429-90-5		0.219	mg	19080	146
				supplier	Passivation	Silicon Nitride	12033-89-5		0.052	mg	4530	35
				supplier	Passivation	Silicon Oxide	7631-86-9		0.077	mg	6708	51
				supplier	back side metallization	Titanium (Ti)	7440-32-6		0.005	mg	436	3
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.075	mg	6534	50
				supplier	back side metallization	Silver (Ag)	7440-22-4		0.027	mg	2352	18
Leadframe	Copper & its alloys	840.769	mg	supplier	alloy	Copper (Cu)	7440-50-8		838.515	mg	997319	559010
				supplier	alloy	Iron (Fe)	7439-89-6		0.386	mg	459	257
				supplier	alloy	Iron Phosphide (FeP)	26508-33-8		0.705	mg	839	470
				supplier	metallization	Nickel (Ni)	7440-02-0		1.156	mg	1375	771
				supplier	metallization	Phosphorus (P)	12185-10-3		0.007	mg	8	5
Soft solder	Solder	10.338	mg	JIG - R	solder	Lead (Pb)	7439-92-1	7a-Lead in high me	9.873	mg	955020	6582
				supplier	solder	Silver (Ag)	7440-22-4		0.258	mg	24956	172
				supplier	solder	Tin (Sn)	7440-31-5		0.207	mg	20023	138
Bonding wires	Other inorganic materials	0.433	mg	supplier	wire	Aluminium (Al)	7429-90-5		0.433	mg	999077	289
				supplier	wire	Magnesium (Mg)	7439-95-4		0.000	mg	923	0
				supplier	mold compound	Silica, vitreous	60676-86-0		550.777	mg	870000	367185
Encapsulation	Other Organic Materials	633.077	mg	supplier	mold compound	Epoxy resin	25068-38-6		63.308	mg	100000	42205
				supplier	mold compound	Phenol resin	29690-82-2		15.827	mg	25000	10551
				supplier	mold compound	Carbon Black	1333-86-4		3.165	mg	4999	2110
				supplier	solder alloy	Tin (Sn)	7440-31-5		3.905	mg	1000000	2603