



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D
<i>* : Required Field</i>			

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2017-01-23
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Authorized Representative *	Rossana Bonaccorso	Representative Title	ADG MD Champion
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement


While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement			
Supplier Acceptance *	true	Legal Declaration *	Standard

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STTH15RQ06GY-TR	DSD2*U66Q2A1	A	3068	2017-01-23
	Amount	UoM	Unit type	ST ECOPACK Grade
	1380.00	mg	Each	ECOPACK2

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
1	245	3		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
NA	Tin (Sn), matte	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
SIP	10.2-9.15-4.5	2	gull wing	
Comment	D2PAK			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-April 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : REACH-20th June 2016				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	DSD2*U66Q2A1					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	Other inorganic materials	4.390	mg	supplier	die	Silicon (Si)	7440-21-3		4.213	mg	959681	3053
				supplier	metallization	Aluminium (Al)	7429-90-5		0.062	mg	14123	45
				supplier	Passivation	Silicon Oxide	7631-86-9		0.020	mg	4556	14
				supplier	back side metallization	Titanium (Ti)	7440-32-6		0.002	mg	455	1
				supplier	back side metallization	Gold (Au)	7440-57-5		0.007	mg	1595	5
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.034	mg	7745	25
				supplier	polymer die coating	Probinide	proprietary		0.052	mg	11845	38
Leadframe	Copper & its alloys	778.632	mg	supplier	alloy	Copper (Cu)	7440-50-8		777.537	mg	998594	563433
				supplier	alloy	Iron (Fe)	7439-89-6		0.358	mg	460	259
				supplier	alloy	Iron Phosphide (FeP)	26508-33-8		0.654	mg	840	474
				supplier	metallization	Nickel (Ni)	7440-02-0		0.077	mg	98	56
				supplier	metallization	Phosphorus (P)	12185-10-3		0.006	mg	8	4
Soft solder	Solder	4.830	mg	JIG - R	solder	Lead (Pb)	7439-92-1	7a-Lead in high me	4.612	mg	954865	3342
				supplier	solder	Silver (Ag)	7440-22-4		0.121	mg	25052	88
				supplier	solder	Tin (Sn)	7440-31-5		0.097	mg	20083	70
Bonding wires	Other inorganic materials	2.894	mg	supplier	wire	Aluminium (Al)	7429-90-5		2.894	mg	1000000	2097
				supplier	wire	Aluminium (Al)	7429-90-5		2.894	mg	1000000	2097
Encapsulation	Other Organic Materials	586.765	mg	supplier	mold compound	Silica, vitreous	60676-86-0		513.419	mg	874999	372043
				supplier	mold compound	Tetramethyl-biphenyl-diy-bis oxymethylene-	EC 413-900-7		23.471	mg	40001	17008
				supplier	mold compound	Epoxy Resin	25068-38-6		17.603	mg	30000	12756
				supplier	mold compound	phenol resin	29690-82-2		29.338	mg	50000	21259
				supplier	mold compound	Carbon black	1333-86-4		2.934	mg	5000	2126
Connections coating	Solder	2.489	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		2.489	mg	1000000	1804