



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D
<i>* : Required Field</i>			

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2017-01-23
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Authorized Representative *	Rossana Bonaccorso	Representative Title	ADG MD Champion
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement


While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement			
Supplier Acceptance *	true	Legal Declaration *	Standard

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STTH30RQ06WY	BTLV*U65Q2AI	A	3068	2017-01-23
	Amount	UoM	Unit type	ST ECOPACK Grade
	4400.00	mg	Each	ECOPACK2

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
NA	NA	NA		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
NA	Tin (Sn), matte	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
SIP	15.75-20.15-5.15	2	Through-hole	
Comment	DO 247			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-April 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : REACH-20th June 2016				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration :						Mfr Item Name	BTLV*U65Q2AI					
note : Substance present with less 0.001mg will not be declared in this document												
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	Other inorganic materials	7.860	mg	supplier	die	Silicon (Si)	7440-21-3		7.540	mg	959288	1714
				supplier	metallization	Aluminium (Al)	7429-90-5		0.112	mg	14249	25
				supplier	Passivation	Silicon Oxide	7631-86-9		0.037	mg	4707	8
				supplier	back side metallization	Titanium (Ti)	7440-32-6		0.004	mg	509	1
				supplier	back side metallization	Gold (Au)	7440-57-5		0.013	mg	1654	3
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.061	mg	7761	14
				supplier	polymer die coating	Probinide	proprietary		0.093	mg	11832	21
Leadframe	Copper & its alloys	2700.559	mg	supplier	alloy	Copper (Cu)	7440-50-8		2696.060	mg	998334	612741
				supplier	alloy	Iron (Fe)	7439-89-6		1.242	mg	460	283
				supplier	alloy	Iron Phosphide (FeP)	26508-33-8		2.268	mg	840	515
				supplier	metallization	Nickel (Ni)	7440-02-0		0.915	mg	339	208
				supplier	metallization	Phosphorus (P)	12185-10-3		0.074	mg	27	17
Soft solder	Solder	8.420	mg	JIG - R	solder	Lead (Pb)	7439-92-1	7a-Lead in high me	8.041	mg	954988	1828
				supplier	solder	Silver (Ag)	7440-22-4		0.211	mg	25059	48
				supplier	solder	Tin (Sn)	7440-31-5		0.168	mg	19953	38
Bonding wires	Other inorganic materials	4.925	mg	supplier	wire	Aluminium (Al)	7429-90-5		4.925	mg	1000000	1119
				supplier	wire	Aluminium (Al)	7429-90-5		4.925	mg	1000000	1119
Encapsulation	Other Organic Materials	1672.039	mg	supplier	mold compound	Silica, vitreous	60676-86-0		1454.674	mg	870000	330608
				supplier	mold compound	Epoxy resin	25068-38-6		167.204	mg	100000	38001
				supplier	mold compound	Phenol resin	29690-82-2		41.801	mg	25000	9500
				supplier	mold compound	Carbon Black	1333-86-4		8.360	mg	5000	1900
Connections coating	Solder	6.197	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		6.197	mg	1000000	1408