



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D
<i>* : Required Field</i>			

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2017-01-18
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Authorized Representative *	Rossana Bonaccorso	Representative Title	ADG MD Champion
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement


While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement			
Supplier Acceptance *	true	Legal Declaration *	Standard

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
SM4T6V7AY	AHST*TYUV68C	A	64BA	2017-01-18
	Amount	UoM	Unit type	ST ECOPACK Grade
	70.00	mg	Each	ECOPACK2

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
1	260	3		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
NA	Tin (Sn), matte	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
SOJ	4.14-2.76-1.94	2	J bend	
Comment	SMA			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-April 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : REACH-20th June 2016				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	AHST*TYUV68C					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	Other inorganic materials	1.112	mg	supplier	die	Silicon (Si)	7440-21-3		1.092	mg	982014	15600
				supplier	metallization	Aluminium (Al)	7429-90-5		0.003	mg	2698	43
				supplier	Passivation	Silicon Oxide	7631-86-9		0.004	mg	3597	57
				supplier	back side metallization	Aluminium (Al)	7429-90-5		0.004	mg	3597	57
				supplier	back side metallization	Gold (Au)	7440-57-5		0.002	mg	1799	29
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.007	mg	6295	100
Leadframe	Copper & its alloys	29.806	mg	supplier	alloy	Copper (Cu)	7440-50-8		29.767	mg	998692	425243
				supplier	alloy	Iron (Fe)	7439-89-6		0.030	mg	1007	429
				supplier	alloy	Iron Phosphide (FeP)	26508-33-8		0.009	mg	301	129
Soft solder	Solder	1.137	mg	JIG - R	solder	Lead (Pb)	7439-92-1	7a-Lead in high me	1.046	mg	919965	14943
				supplier	solder	Silver (Ag)	7440-22-4		0.057	mg	50132	813
				supplier	solder	Tin (Sn)	7440-31-5		0.028	mg	24626	400
				supplier	solder	flux residue	Proprietary		0.006	mg	5277	86
Encapsulation	Other Organic Materials	25.723	mg	supplier	mold compound	Amorphous Silica	7631-86-9		18.803	mg	730980	268614
				supplier	mold compound	Epoxy Cresol Novolak	29690-82-2		4.887	mg	189986	69814
				supplier	mold compound	Phenol resin	9003-35-4		0.772	mg	30012	11029
				supplier	mold compound	Bisphenol A-bisphenol A diglycidyle ether poly	25036-25-3		0.772	mg	30012	11029
				supplier	mold compound	Carbon black	1333-86-4		0.232	mg	9019	3314
				supplier	mold compound	Triphenylphosphine	603-35-0		0.180	mg	6998	2571
Connections coating	Solder	0.741	mg	supplier	mold compound	3-Mercaptopropyl trimethoxysilane	4420-74-0		0.077	mg	2993	1100
				supplier	solder alloy	Tin (Sn)	7440-31-5		0.741	mg	1000000	10586
Clip	Copper & its alloys	11.481	mg	supplier	alloy	Copper (Cu)	7440-50-8		11.481	mg	1000000	164014