



## Materials Declaration Form

|                        |                                     |                        |                                  |
|------------------------|-------------------------------------|------------------------|----------------------------------|
| <b>IPC Form Type *</b> | <b>1752</b><br>Distribute           | <b>Version</b>         | <b>2</b>                         |
| <b>Sectionals *</b>    | Material Info<br>Manufacturing Info | <b>Subsectionals *</b> | A-D<br><i>* : Required Field</i> |

| Supplier Information               |  |                               |                                   |
|------------------------------------|--|-------------------------------|-----------------------------------|
| <b>Company Name *</b>              | <b>STMicroelectronics</b>  | <b>Response Date *</b>        | <b>2015-10-29</b>                 |
| <b>Contact Name *</b>              | Refer to Supplier Comment section  |                               | Refer to Supplier Comment section |
| <b>Authorized Representative *</b> | <b>Floriana San Biagio</b>   | <b>Representative Title</b>   | <b>AMS MD CHAMPION</b>            |
| <b>Representative Phone *</b>      | Refer to Supplier Comment section  | <b>Representative Email *</b> | Refer to Supplier Comment section |
| <b>Supplier Comment</b>            | Online Technical Support - STMicroelectronics :<br><a href="http://www.st.com/web/en/support/support.html">http://www.st.com/web/en/support/support.html</a> |                               |                                   |

**Uncertainty Statement**

While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.


**Legal Statement**

|                              |             |                            |                 |
|------------------------------|-------------|----------------------------|-----------------|
| <b>Supplier Acceptance *</b> | <b>true</b> | <b>Legal Declaration *</b> | <b>Standard</b> |
|------------------------------|-------------|----------------------------|-----------------|

**Legal Statement**

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

| Product         |               |  |                  |            |
|-----------------|---------------|--|------------------|------------|
| Mfr Item Number | Mfr Item Name | Version  | Mfr Site         | Date       |
|                 | LDK7*0124BH6  | A  | BO2A             | 2015-10-29 |
| Amount          | UoM           | Unit type  | ST ECOPACK Grade |            |
| 130.00          | mg            | Each   | ECOPACK® 3       |            |
|                 | Comment       | ECOPACK® 3 is STMicroelectronics trade name for ROHS compliant device without use of any ROHS exemption and without Halogen nor Antimony |                  |            |

| Manufacturing information |                           |                      |         |   |
|---------------------------|---------------------------|----------------------|---------|---|
| J-STD-020 MSL Rating      | Classification Temp       | Nbr of Reflow Cycles |         | <br>life.augmented |
| 1                         | 260                       | 3                    |         |   |
| bulk Solder Termination   | Terminal Plating          | Terminal Base Alloy  | Comment |   |
| NAC                       | Tin (Sn), matte, annealed | Copper Alloy         |         |   |

| Package Designator | Size  | Nbr of instances | Shape     |  |
|--------------------|---|------------------|-----------|--|
| DSO                | 8.6x3.9x1.52  | 14               | gull wing |  |
| Comment            | Package: K7 SO 14 .15 TO JEDEC MS-012; MDF valid for LM124DT-LM224D-LM224DTLM2902D-LM2902DT-LM324D-LM324DT-LM324EDT |                  |           |  |

| QueryList : ROHS directive 2011/65/EU _ July 2011  |             |
|--|-------------|
| Query  | Response    |
| 1 - Product(s) meets EU RoHS requirement without any exemptions  | true        |
| 2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply) | false       |
| 3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)  | false       |
| 4 - Product(s) does not meet EU RoHS requirements and is not under exemptions  | false       |
| Exemption Id.  | Description |
|  |             |

| QueryList : REACH-15th June 2015   |                         |                        |             |                |
|--|-------------------------|------------------------|-------------|----------------|
| Query  |                         |                        |             | Response       |
| 1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH |                         |                        |             | true           |
| CategoryLevel_Name   | CategoryLevel_Threshold | amount in product (mg) | Application | ppm in product |
|  |                         |                        |             |                |

| Material Composition Declaration |                           |        |     |          |                    | Mfr Item Name          | LDK7*0124BH6 |        |        |     |   |                                |
|----------------------------------|---------------------------|--------|-----|----------|--------------------|------------------------|--------------|--------|--------|-----|---|--------------------------------|
| Homogeneous Material             | Material Group            | Mass   | UoM | Level    | Substance Category | Substance              | CAS          | Exempt | Mass   | UoM | Concentration in homogeneous material (ppm) | Concentration in product (ppm) |
| Die                              | Other inorganic materials | 2.385  | mg  | supplier | die                | Silicon (Si)           | 7440-21-3    |        | 2.355  | mg  | 987421                                      | 18115                          |
|                                  |                           |        |     | supplier | metallization      | Aluminium (Al)         | 7429-90-5    |        | 0.011  | mg  | 4612  | 85                             |
|                                  |                           |        |     | supplier | Passivation        | Silicon Nitride        | 12033-89-5   |        | 0.005  | mg  | 2096  | 38                             |
|                                  |                           |        |     | supplier | Passivation        | Silicon Oxide          | 7631-86-9    |        | 0.007  | mg  | 2935  | 54                             |
|                                  |                           |        |     | supplier | glass coating      | Glass: Silicon Dioxide | 7631-86-9    |        | 0.007  | mg  | 2935  | 54                             |
|                                  |                           |        |     | supplier | alloy              | Copper (Cu)            | 7440-50-8    |        | 34.860 | mg  | 918142                                      | 268154                         |
| Leadframe                        | Copper & its alloys       | 37.968 | mg  | supplier | alloy              | Iron (Fe)              | 7439-89-6    |        | 0.820  | mg  | 21597                                       | 6308                           |
|                                  |                           |        |     | supplier | alloy              | Iron Phosphide (FeP)   | 26508-33-8   |        | 0.049  | mg  | 1291  | 377                            |
|                                  |                           |        |     | supplier | alloy              | Zinc (Zn)              | 7440-66-6    |        | 0.043  | mg  | 1133  | 331                            |
|                                  |                           |        |     | supplier | metallization      | Nickel (Ni)            | 7440-02-0    |        | 0.460  | mg  | 12115                                       | 3538                           |
|                                  |                           |        |     | supplier | metallization      | Palladium (Pd)         | 7440-05-3    |        | 0.029  | mg  | 764   | 223                            |
|                                  |                           |        |     | supplier | metallization      | Gold (Au)              | 7440-57-5    |        | 0.012  | mg  | 316   | 92                             |
|                                  |                           |        |     | supplier | metallization      | Silver (Ag)            | 7440-22-4    |        | 1.695  | mg  | 44643                                       | 13038                          |
|                                  |                           |        |     | supplier | glue               | Silver (Ag)            | 7440-22-4    |        | 0.450  | mg  | 905433                                      | 3462                           |
| Die attach                       | Other inorganic materials | 0.497  | mg  | supplier | glue               | acrylate               | Proprietary  |        | 0.025  | mg  | 50302                                       | 192                            |
|                                  |                           |        |     | supplier | glue               | Methacrylate           | Proprietary  |        | 0.020  | mg  | 40241                                       | 154                            |
|                                  |                           |        |     | supplier | glue               | acrylate               | Proprietary  |        | 0.001  | mg  | 2012  | 8                              |
|                                  |                           |        |     | SVHC     | glue               | NMP                    | 872-50-4     |        | 0.001  | mg  | 2012  | 8                              |
|                                  |                           |        |     | supplier | wire               | Copper (Cu)            | 7440-50-8    |        | 0.127  | mg  | 1000000                                     | 977                            |
| Bonding wires                    | Other inorganic materials | 0.127  | mg  | supplier | wire               | Copper (Cu)            | 7440-50-8    |        | 0.127  | mg  | 1000000                                     | 977                            |
|                                  |                           |        |     | supplier | mold compound      | Silica, vitreous       | 60676-86-0   |        | 77.284 | mg  | 877001                                      | 594492                         |
|                                  |                           |        |     | supplier | mold compound      | Epoxy resin            | 85954-11-6   |        | 3.525  | mg  | 40001                                       | 27115                          |
|                                  |                           |        |     | supplier | mold compound      | Epoxy                  | 29690-82-2   |        | 3.525  | mg  | 40001                                       | 27115                          |
|                                  |                           |        |     | supplier | mold compound      | phenol resin           | Proprietary  |        | 2.644  | mg  | 30004                                       | 20338                          |
| Encapsulation                    | Other Organic Materials   | 88.123 | mg  | supplier | mold compound      | additive               | Proprietary  |        | 0.881  | mg  | 9997  | 6777                           |
|                                  |                           |        |     | supplier | mold compound      | carbon black           | 1333-86-4    |        | 0.264  | mg  | 2996  | 2031                           |
|                                  |                           |        |     | supplier | solder alloy       | Tin (Sn)               | 7440-31-5    |        | 0.900  | mg  | 1000000                                     | 6923                           |
| connections coating              | Solder                    | 0.900  | mg  | supplier | solder alloy       | Tin (Sn)               | 7440-31-5    |        | 0.900  | mg  | 1000000                                     | 6923                           |