



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D
<i>* : Required Field</i>			

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2015-07-29
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Authorized Representative *	Rossana Bonaccorso	Representative Title	IPD MD Champion
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement

While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement			
Supplier Acceptance *	true	Legal Declaration *	Standard
Legal Statement	<p>Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.</p>		

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STW28N60M2	TSLW*MQ66B62	A	SHENZHEN B/E	2015-07-29
Amount		UoM	Unit type	ST ECOPACK Grade
4430.00		mg	Each	ECOPACK2

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		
NAC	NAC	NAC		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
NAC	Tin (Sn), matte	Copper Alloy		



Package Designator	Size	Nbr of instances	Shape	
SIP	15.75, 20.15, 5.15	2	THROUGH HOLE	
Comment	Package: TO 247			

QueryList : ROHS directive 2011/65/EU _ July 2011	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	false
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	false
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	true
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	false
5 - Product(s) is obsolete, no information is available	false
6 - Product(s) is unknown, no information is available	false
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : REACH-15th June 2015				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration						Mfr Item Name	TSLW*MQ66B2					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	Other inorganic materials	28.617	mg	supplier	die	Silicon (Si)	7440-21-3		27.611	mg	964847	6233
				supplier	metallization	Aluminium (Al)	7429-90-5		0.548	mg	19149	124
				supplier	Passivation	Silicon Nitride	12033-89-5		0.130	mg	4543	29
				supplier	Passivation	Silicon Oxide	7631-86-9		0.194	mg	6779	44
				supplier	back side metallization	Titanium (Ti)	7440-32-6		0.007	mg	245	2
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.094	mg	3285	21
Leadframe	Copper & its alloys	2720.611	mg	supplier	back side metallization	Silver (Ag)	7440-22-4		0.033	mg	1153	7
				supplier	alloy	Copper (Cu)	7440-50-8		2705.048	mg	994280	610620
				supplier	alloy	Iron (Fe)	7439-89-6		1.246	mg	458	281
				supplier	alloy	Iron Phosphide (FeP)	26508-33-8		2.275	mg	836	514
				supplier	metallization	Nickel (Ni)	7440-02-0		11.968	mg	4399	2702
				supplier	metallization	Phosphorus (P)	12185-10-3		0.074	mg	27	17
Soft solder	Solder	12.832	mg	JIG - R	solder	Lead (Pb)	7439-92-1	7a-Lead in high me	12.254	mg	954956	2766
				supplier	solder	Silver (Ag)	7440-22-4		0.321	mg	25016	72
				supplier	solder	Tin (Sn)	7440-31-5		0.257	mg	20028	58
Bonding wires	Other inorganic materials	1.201	mg	supplier	wire	Aluminium (Al)	7429-90-5		1.200	mg	999167	271
				supplier	wire	Magnesium (Mg)	7439-95-4		0.001	mg	833	0
				supplier	wire							
Encapsulation	Other Organic Materials	1660.542	mg	supplier	mold compound	Silica, vitreous	60676-86-0		1444.671	mg	870000	326111
				supplier	mold compound	Epoxy resin	25068-38-6		166.054	mg	100000	37484
				supplier	mold compound	Phenol resin	29690-82-2		41.514	mg	25000	9371
				supplier	mold compound	Carbon Black	1333-86-4		8.303	mg	5000	1874
Connections coating	Solder	6.197	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		6.197	mg	1000000	1399