



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D

*: Required Field

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2017-09-15
Company Unique ID			
Contact Name *	Refer to Supplier comment section	Contact Title	Refer to Supplier comment section
Contact Phone *	Refer to Supplier comment section	Contact Email *	Refer to Supplier comment section
Authorized Representative *	Giovanni Giacopello	Representative Title	ADG Material Declaration Champion
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement

While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement		
Supplier Acceptance *	true	Legal Declaration *
		Standard

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
ESDAVLC5-4BX4	LZJF*6TAP026	A	SH1A	2017-09-15
	Amount	UoM	Unit type	ST ECOPACK Grade
	0.500	mg	Each	ECOPACK® 2

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		
Not Applicable	Not Applicable	Not Applicable		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
Not Applicable	Not Applicable	Not Applicable		



Package Designator	Size	Nbr of instances	Shape	
BARE DIE	0.83 - 0.83 -0.325	2	flat	
Comment	Package: CSPS BUMPLESS			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-April 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	TRUE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	false
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	false
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	false
Exemption Id.	Description

Query : California Prop65 list, dated 27th January 2017			
Query			Response
1 - The product does not contain identified substance from California Prop 65 List, no exposure to consumers is foreseen			FALSE
2 - The product is containing below substance(s) from California Prop 65 List, no exposure to consumers is foreseen			TRUE
Substance	amount in product (mg)	Application	ppm in product
Nickel	0.004	Die	8000

QueryList : REACH- 12th January 2017				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				TRUE
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product
2 - Product(s) does not contain REACH Substances Of Very High Concern in any Homogeneous Material above the limits per the definition within REACH				TRUE
CategoryLevel_Name	CategoryLevel_Threshold	Amount in Homogeneous Material (mg)	Application - Homogeneous Material	ppm in Homogeneous Material

Material Composition Declaration						Mfr Item Name	LZJF*6TAP026					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	Other inorganic materials	0.500	mg	supplier	die	Silicon (Si)	7440-21-3		0.408	mg	816000	816000
				supplier	metallisation	Aluminium (Al)	7429-90-5		0.011	mg	22000	22000
				supplier	Passivation	Silicon Nitride (SiN)	12033-89-5		0.001	mg	2000	2000
				supplier	passivation	Silicon Oxide	7631-86-9		0.006	mg	12000	12000
				supplier	die polymer coat	silica vitreous	60676-86-0		0.032	mg	64000	64000
				supplier	die polymer coat	Epoxy resin	Proprietary		0.011	mg	22000	22000
				supplier	die polymer coat	Acrylic polymer	Proprietary		0.011	mg	22000	22000
				supplier	die polymer coat	Bis-phenol A diglycidyl ether	25036-25-3		0.004	mg	8000	8000
				supplier	die polymer coat	Iron compound	7439-89-6		0.003	mg	6000	6000
				supplier	die polymer coat	Zinc compound	7440-66-6		0.003	mg	6000	6000
				supplier	UBM	Copper (Cu)	7440-50-8		0.004	mg	8000	8000
				supplier	UBM	Titanium (Ti)	7440-32-6		0.001	mg	2000	2000
				supplier	UBM	Gold (Au)	7440-57-5		0.001	mg	2000	2000
				supplier	UBM	Nickel (Ni)	7440-02-0		0.004	mg	8000	8000