



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D <i>* : Required Field</i>

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2018-09-21
Company Unique ID	NL 008751171801		
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Contact Phone *	Refer to Supplier Comment section	Contact Email *	Refer to Supplier Comment section
Authorized Representative *	Giovanni Giacobello	Representative Title	ADG MD Champion
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement

While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.


Legal Statement

Supplier Acceptance *	true	Legal Declaration *	Standard
------------------------------	------	----------------------------	----------

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STF25N60M2-EP	TSFP*EQ6HR62	A	3068	2018-09-21
	Amount	UoM	Unit type	ST ECOPACK Grade
	1900.00	mg	Each	ECOPACK2
	Comment	ECOPACK® 2 is STMicroelectronics trade name for ROHS compliant device without Brominated and Chlorinated compound (900ppm) and without Antimony oxide flame retardant (in each organic material)		

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
NA	NA	NA		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
NA	Tin (Sn), matte	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
SIP	10.2-16.15-4.5	3	Through-hole	
Comment	TO 220 ISO FULL PACK IN LINE			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-March 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : ELV directive : 2000/53/EC amended 2017/2096 _November 2017	
Query	Response
1 - Product(s) meets EU ELV requirements without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
Exemption Id.	Description
8e	Lead in high melting temperature type solders (i.e. lead-based alloys containing 85 % by weight or more lead)

QueryList : California Prop65 list, dated 25th May 2018			
Query			Response
1 - The product does not contain identified substance from California Prop 65 List, no exposure to consumers is foreseen			FALSE
2 - The product is containing below substance(s) from California Prop 65 List, no exposure to consumers is foreseen			TRUE
Substance	amount in product (mg)	Application	ppm in product
Nickel	0.75	Die - Leadframe	394
Lead	9.70	Soft solder	5104

QueryList : REACH-27th June 2018				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				FALSE
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product
Lead	1000 ppm	9.70	Soft solder	5104
2 - Product(s) does not contain REACH Substances Of Very High Concern in any Embedded article nor Homogeneous Material above the limits per the definition within REACH				FALSE
CategoryLevel_Name	CategoryLevel_Threshold	Amount in Embedded Article / Homogeneous Material (mg)	Application - Article / Homogeneous Material	ppm in Article /Homogeneous Material
Lead	1000 ppm	9.70	Soft solder	954993

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	TSPF*EQ6HR62					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	M-011 Other inorganic materials	8.330	mg	supplier	die	Silicon (Si)	7440-21-3		7.874	mg	945258	4144
				supplier	metallization	Aluminium (Al)	7429-90-5		0.219	mg	26291	115
				supplier	Passivation	Silicon Nitride	12033-89-5		0.052	mg	6242	27
				supplier	Passivation	Silicon Oxide	7631-86-9		0.078	mg	9364	41
				supplier	back side metallization	Titanium (Ti)	7440-32-6		0.005	mg	600	3
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.075	mg	9004	39
				supplier	back side metallization	Silver (Ag)	7440-22-4		0.027	mg	3241	14
Leadframe	M-004 Copper and its alloys	605.985	mg	supplier	alloy	Copper (Cu)	7440-50-8		604.469	mg	997498	318142
				supplier	alloy	Iron (Fe)	7439-89-6		0.605	mg	998	318
				supplier	alloy	Iron Phosphide (FeP)	26508-33-8		0.182	mg	300	96
				supplier	metallization	Nickel (Ni)	7440-02-0		0.674	mg	1112	355
				supplier	metallization	Phosphorus (P)	7723-14-0		0.055	mg	92	29
				supplier								
Soft solder	Solder	10.154	mg	JIG - R	solder	Lead (Pb)	7439-92-1	7a-Lead in high mel	9.697	mg	954993	5104
				supplier	solder	Silver (Ag)	7440-22-4		0.254	mg	25015	134
				supplier	solder	Tin (Sn)	7440-31-5		0.203	mg	19992	107
Bonding wires	M-011 Other inorganic materials	0.932		supplier	wire	Aluminium (Al)	7429-90-5		0.928	mg	995708	488
				supplier	wire	Magnesium (Mg)	7439-95-4		0.004	mg	4292	2
				supplier								
Encapsulation	M-011 Other inorganic materials	1268.733	mg	supplier	mold compound	Quartz	14808-60-7		888.113	mg	700000	467428
				supplier	mold compound	Silica, vitreous	60676-86-0		95.155	mg	75000	50082
				supplier	mold compound	Epoxy resin	25068-38-6		177.623	mg	140000	93486
				supplier	mold compound	phenol resin	29690-82-2		88.811	mg	70000	46743
				supplier	mold compound	metal hydroxide	Proprietary		12.687	mg	10000	6677
				supplier	mold compound	carbon black	1333-86-4		6.344	mg	5000	3339
Connections coating	Solder	5.866	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		5.866	mg	1000000	3087