



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D <i>* : Required Field</i>

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2016-02-16
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Authorized Representative *	Floriana San Biagio	Representative Title	AMG MD CHAMPION
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement

While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement


Supplier Acceptance *	true	Legal Declaration *	Standard
------------------------------	-------------	----------------------------	-----------------

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
	LDK7*0074AD6	A	BO2A	2016-02-16
Amount	UoM	Unit type	ST ECOPACK Grade	
130.00	mg	Each	ECOPACK® 3	
	Comment	ECOPACK® 3 is STMicroelectronics trade name for ROHS compliant device without use of any ROHS exemption and without Halogen nor Antimony		

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		
1	260	3		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
NAC	Tin (Sn), matte, annealed	Copper Alloy		



Package Designator	Size	Nbr of instances	Shape	
DSO	8.6x3.9x1.52	14	gull wing	
Comment	Package: K7 SO 14 .15 TO JEDEC MS-012; MDF valid for TL074ACDT-TL074BCDT-TL074CD-TL074CDT-TL074ID-TL074IDT			

QueryList : ROHS directive 2011/65/EU _ July 2011	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	true
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	false
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	false
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	false
Exemption Id.	Description

QueryList : REACH-17th December 2015				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration						Mfr Item Name	LDK7*0074AD6					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	Other inorganic materials	4.221	mg	supplier	die	Silicon (Si)	7440-21-3		4.151	mg	983416	31931
				supplier	metallization	Aluminium (Al)	7429-90-5		0.025	mg	5923	192
				supplier	Passivation	Silicon Nitride	12033-89-5		0.013	mg	3080	100
				supplier	Passivation	Silicon Oxide	7631-86-9		0.016	mg	3791	123
				supplier	glass coating	Glass: Silicon Dioxide	7631-86-9		0.016	mg	3791	123
Leadframe	Copper & its alloys	37.969	mg	supplier	alloy	Copper (Cu)	7440-50-8		34.861	mg	918144	268162
				supplier	alloy	Iron (Fe)	7439-89-6		0.820	mg	21597	6308
				supplier	alloy	Iron Phosphide (FeP)	26508-33-8		0.049	mg	1291	377
				supplier	alloy	Zinc (Zn)	7440-66-6		0.043	mg	1133	331
				supplier	metallization	Nickel (Ni)	7440-02-0		0.460	mg	12115	3538
				supplier	metallization	Palladium (Pd)	7440-05-3		0.029	mg	764	223
				supplier	metallization	Gold (Au)	7440-57-5		0.012	mg	316	92
				supplier	metallization	Silver (Ag)	7440-22-4		1.695	mg	44642	13038
				supplier	glue	Silver (Ag)	7440-22-4		1.010	mg	908273	7769
				SVHC	glue	NMP	872-50-4		0.001	mg	899	8
Die attach	Other inorganic materials	1.112	mg	supplier	glue	acrylate	Proprietary		0.056	mg	50360	431
				supplier	glue	Methacrylate	Proprietary		0.044	mg	39568	338
				supplier	glue	acrylate	Proprietary		0.001	mg	899	8
				supplier	glue	NMP	872-50-4		0.001	mg	899	8
Bonding wires	Other inorganic materials	0.127	mg	supplier	wire	Copper (Cu)	7440-50-8		0.127	mg	1000000	977
				supplier	wire	Copper (Cu)	7440-50-8		0.127	mg	1000000	977
Encapsulation	Other Organic Materials	85.671	mg	supplier	mold compound	Silica, vitreous	60676-86-0		75.133	mg	876995	577946
				supplier	mold compound	Epoxy resin	85954-11-6		3.427	mg	40002	26362
				supplier	mold compound	Epoxy	29690-82-2		3.427	mg	40002	26362
				supplier	mold compound	phenol resin	Proprietary		2.570	mg	29998	19769
				supplier	mold compound	additive	Proprietary		0.857	mg	10003	6592
connections coating	Solder	0.900	mg	supplier	mold compound	carbon black	1333-86-4		0.257	mg	3000	1977
				supplier	solder alloy	Tin (Sn)	7440-31-5		0.900	mg	1000000	6923