



Material Composition Declaration

© Copyright 2005. IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.

This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.

Adobe Reader version 7.0.5 is required to complete this declaration.

1752-2 1.1	IPC Web Site for Information on IPC-1752 Standard http://www.ipc.org/IPC-175x	Form Type * Distribute	Declaration Class * Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Informat
------------	--	---------------------------	--

Supplier Information

Company Name * STMicroelectronics	Company Unique ID	Unique ID Authority	Response Date *	Response Document ID				
Contact Name *	Title - Contact	Phone - Contact *	Email - Contact *	<input type="button" value="Duplicate Contact -> Authorized Representative"/>				
Authorized Representative * Emilio Castelli	Title - Representative APG Material Declaration Cham	Phone - Representative *	Email - Representative *	Supplier Comments or URL for Additional Information				
Requester Item Number	Mfr Item Number	Mfr Item Name	Effective Date	Version	Manufacturing Site	Weight *	UOM	Unit Type
	L5957	J8V2*UH37AC1	2010-11-05	A	64BA	5,535	mg	Each
Alternate Recommendation	MultiWatt 15L Split Vert.			Alternate Item Comments	Internal ST reference: BSA: CD00226421 EcoPack1			

Manufacturing Process Information

Terminal Plating / Grid Array Material	Terminal Base Alloy	J-STD-020 MSL Rating	Peak Process Body Temperature	Max Time at Peak Temperature	Number of Reflow Cycles
Tin (Sn)	CU Alloy	3	C	30 seconds	3

Comments

Disclaimer: While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and

Save the fields in this form to a file

Export Data

Import fields from a file into this form

Import Data

Clear all of the fields on this form

Reset Form

Lock the fields on this form to prevent changes

Lock Supplier Fields

RoHS Material Composition Declaration

Declaration Type *

Simplified

RoHS Directive
2002/95/EC

RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material for Cadmium

Supplier certifies that it gathered the information it provides in this form concerning RoHS restrictive substances using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

RoHS Declaration *

3 - Item(s) does not contain RoHS restricted substances per the definition above except for lead in solders and selected exemptions, if any

Supplier Acceptance *

Accepted

Exemptions: If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions.

Exemption List Version

EL-2006/690/EC

+

-

7a. Lead in high melting temperature type solders (i.e. lead based solder alloys containing 85% by weight or more lead).

Declaration Signature

Instructions: Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.

Supplier Digital Signature

Homogeneous Material Composition Declaration for Electronic Products

SubItem Instructions: The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

Substance Instructions: [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

Line Functions: +I Inserts a New Item /SubItem +M Inserts a new Material +C Inserts a new Substance Category +S Inserts a new Substance - Deletes the element line

		Item/SubItem Name	Homogeneous Material		Weight	Unit of Measure	Level		Substance Category	Substance		CAS	Exempt	Weight	Unit of Measure	Tolerance		PPM
+I	-I		+M	-M			+C	-C		+S	-S					-	+	
		MultiWatt 15L Splt			10.948	mg			Supplier	Silicon die	Silicon (Si)	7440-21-3		10.858	mg			991,77
									die metallization	Aluminium (Al)	7429-90-5			0.002	mg			183
									die metallization	Copper (Cu)	7440-50-8			0.006	mg			548
									die metallization	Titanium (Ti)	7440-32-6			0.003	mg			274
									die metallization	Chromium (Cr)	7440-47-3			0.001	mg			91
									die metallization	Gold (Au)	7440-57-5			0.002	mg			183
									die metallization	Nickel (Ni)	7440-02-0			0.006	mg			548
									Die coating	Gamma-butyrolactone	96-48-0			0.047	mg			4,293
									Die coating	Polyhydroxyamide	55295-98-2			0.021	mg			1,918
									Die coating	Alcoxysilane	na			0.001	mg			91
									Die coating	Aryl Silicilic Acid	na			0.001	mg			91
									Leadframe	frame alloy	Copper (Cu)	7440-50-8		4,417.698	mg			997,72
									frame alloy	Iron (Fe)	7439-89-6			2.035	mg			460
									frame alloy	Iron Phosphide (FeP)	26508-33-8			3.716	mg			839
									frame coating	Silver (Ag)	7440-22-4			4.339	mg			980
									Die Attach	soft solder	Lead (Pb)	7439-92-1	7a. Lead	4.434	mg			975,14
									soft solder	Silver (Ag)	7440-22-4			0.068	mg			14,955
									soft solder	Tin (Sn)	7440-31-5			0.045	mg			9,897
									Bonding wire	Bonding wire	Copper (Cu)	7440-50-8		1.084	mg			1,000,0
									Encapsulation	Moulding Compound	Silica, vitreous	60676-86-0		754.989	mg			720,00
									Moulding Compound	Epoxy Cresol Novolak	29690-82-2			178.261	mg			170,00
									Moulding Compound	Phenol resin	9003-35-4			75.499	mg			72,000
									Moulding Compound	Brominated epoxy resin	40039-93-8			15.729	mg			15,000

						+C	-C	supplier	Moulding Compound	+S	-S	Carbon black	1333-86-4		3.146	mg			3,000
						+C	-C	B	Moulding Compound	+S	-S	Antimony Trioxide	1309-64-4		20.972	mg			20,000
+M	-M	Finishing	42.037	mg		+C	-C	supplier	connection coating	+S	-S	Tin (Sn)	7440-31-5		42.037	mg			1,000,0