



## Materials Declaration Form

<b>IPC Form Type *</b>	1752 Distribute	<b>Version</b>	2
<b>Sectionals *</b>	Material Info Manufacturing Info	<b>Subsectionals *</b>	A-D  <i>* : Required Field</i>

Supplier Information			
<b>Company Name *</b>	STMicroelectronics	<b>Response Date *</b>	2018-05-18
<b>Company Unique ID</b>	NL 008751171B01		
<b>Contact Name *</b>	Refer to Supplier Comment section		Refer to Supplier Comment section
<b>Contact Phone *</b>	Refer to Supplier Comment section	<b>Contact Email *</b>	Refer to Supplier Comment section
<b>Authorized Representative *</b>	Giovanni Giacopello	<b>Representative Title</b>	ADG MD Champion
<b>Representative Phone *</b>	Refer to Supplier Comment section	<b>Representative Email *</b>	Refer to Supplier Comment section
<b>Supplier Comment</b>	Online Technical Support - STMicroelectronics : <a href="http://www.st.com/web/en/support/support.html">http://www.st.com/web/en/support/support.html</a>		

**Uncertainty Statement**


While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement		
<b>Supplier Acceptance *</b>	true	<b>Legal Declaration *</b>
		Standard

**Legal Statement**

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STW8N120K5	TSLW*VJN4B52	A	3068	2018-05-18
Amount	UoM	Unit type	ST ECOPACK Grade	
4430	mg	Each	ECOPACK2	
	Comment	ECOPACK® 2 is STMicroelectronics trade name for ROHS compliant device without Brominated and Chlorinated compound (900ppm) and without Antimony oxide flame retardant ( in each organic material)		

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
NA	NA	NA		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
NA	Tin (Sn), matte	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
QFN	15.75-20.15-5.15	3	Through-hole	
Comment	TO 247			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-April 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : California Prop65 list, dated 15th December 2017			
Query			Response
1 - The product does not contain identified substance from California Prop 65 List, no exposure to consumers is foreseen			FALSE
2 - The product is containing below substance(s) from California Prop 65 List, no exposure to consumers is foreseen			TRUE
Substance	amount in product (mg)	Application	ppm in product
Nickel	0.98	Die - Leadframe	222
Lead	9.10	Soft solder	2053

QueryList : REACH-15th January 2018				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product
2 - Product(s) does not contain REACH Substances Of Very High Concern in any Embedded article nor Homogeneous Material above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	Amount in Embedded Article / Homogeneous Material (mg)	Application - Article / Homogeneous Material	ppm in Article /Homogeneous Material

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	TSLW*/VJN4852				6000000.0	1000000.0
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	M-011 Other inorganic materials	10.477	mg	supplier	die	Silicon (Si)	7440-21-3		10.113	mg	965257	2283
				supplier	metallization	Aluminium (Al)	7429-90-5		0.142	mg	13553	32
				supplier	Passivation	Silicon Nitride	12033-89-5		0.048	mg	4582	11
				supplier	Passivation	Silicon Oxide	7631-86-9		0.076	mg	7254	17
				supplier	back side metallization	Titanium (Ti)	7440-32-6		0.005	mg	477	1
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.069	mg	6586	16
				supplier	back side metallization	Silver (Ag)	7440-22-4		0.024	mg	2291	5
Leadframe	M-004 Copper and its alloys	2826.184	mg	supplier	alloy	Copper (Cu)	7440-50-8		2821.522	mg	998350	636912
				supplier	alloy	Iron (Fe)	7439-89-6		2.825	mg	1000	638
				supplier	alloy	Iron Phosphide (FeP)	26508-33-8		0.848	mg	300	191
				supplier	metallization	Nickel (Ni)	7440-02-0		0.915	mg	324	207
				supplier	metallization	Phosphorus (P)	7723-14-0		0.074	mg	26	17
Soft solder	Solder	9.526	mg	JIG - R	solder	Lead (Pb)	7439-92-1	7a-Lead in high mel	9.097	mg	954965	2053
				supplier	solder	Silver (Ag)	7440-22-4		0.238	mg	24984	54
				supplier	solder	Tin (Sn)	7440-31-5		0.191	mg	20051	43
Bonding wires	M-003 Aluminum and its alloys	0.804	mg	supplier	wire	Aluminium (Al)	7429-90-5		0.801	mg	996269	181
				supplier	wire	Magnesium (Mg)	7439-95-4		0.003	mg	3731	1
Encapsulation	M-011 Other inorganic materials	1573.713	mg	supplier	mold compound	Silica, vitreous	60676-86-0		1369.130	mg	870000	309059
				supplier	mold compound	Epoxy resin	25068-38-6		157.371	mg	100000	35524
				supplier	mold compound	Phenol resin	25690-82-2		39.343	mg	25000	8881
				supplier	mold compound	Carbon Black	1333-86-4		7.869	mg	5000	1776
connections coating	Solder	9.296	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		9.296	mg	1000000	2098