



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D <i>* : Required Field</i>

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2018-09-07
Company Unique ID	NL 008751171B01		
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Contact Phone *	Refer to Supplier Comment section	Contact Email *	Refer to Supplier Comment section
Authorized Representative *	Giovanni Giapello	Representative Title	ADG MD Champion
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement


While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement		
Supplier Acceptance *	true	Legal Declaration *
		Standard

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STGW25M120DF3	TDLW*KLJ7R52	A	3068	2018-09-07
Amount	UoM	Unit type	ST ECOPACK Grade	
4430.00	mg	Each	ECOPACK2	
	Comment	ECOPACK® 2 is STMicroelectronics trade name for ROHS compliant device without Brominated and Chlorinated compound (900ppm) and without Antimony oxide flame retardant (in each organic material)		

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
NA	NA	NA		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
NA	Tin (Sn), matte	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
QFN	15.75-20.15-5.15	3	Through-hole	
Comment	TO 247			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-March 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : ELV directive : 2000/53/EC amended 2017/2096 _November 2017	
Query	Response
1 - Product(s) meets EU ELV requirements without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
Exemption Id.	Description
8e	Lead in high melting temperature type solders (i.e. lead-based alloys containing 85 % by weight or more lead)

QueryList : California Prop65 list, dated 25th May 2018			
Query			Response
1 - The product does not contain identified substance from California Prop 65 List, no exposure to consumers is foreseen			FALSE
2 - The product is containing below substance(s) from California Prop 65 List, no exposure to consumers is foreseen			TRUE
Substance	amount in product (mg)	Application	ppm in product
Nickel	1.08	Die - Leadframe	244
Lead	15.72	Soft solder	3549

QueryList : REACH-27th June 2018				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				FALSE
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product
Lead	1000 ppm	15.722	Soft solder	3549
2 - Product(s) does not contain REACH Substances Of Very High Concern in any Embedded article nor Homogeneous Material above the limits per the definition within REACH				FALSE
CategoryLevel_Name	CategoryLevel_Threshold	Amount in Embedded Article / Homogeneous Material (mg)	Application - Article / Homogeneous Material	ppm in Article /Homogeneous Material
Lead	1000 ppm	15.722	Soft solder	954990

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	TDLW*KL7R52									
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)				
Die	M-011 Other inorganic materials	15.533	mg	supplier	die	Silicon (Si)	7440-21-3		14.344	mg	923471	3238				
				supplier	metallization	Aluminium (Al)	7429-90-5		0.445	mg	28649	100				
				supplier	Passivation	Silicon Nitride	12033-89-5		0.087	mg	5601	20				
				supplier	Passivation	Silicon Oxide	7631-86-9		0.162	mg	10430	37				
				supplier	back side metallization	Aluminium (Al)	7429-90-5		0.049	mg	3155	11				
				supplier	back side metallization	Titanium (Ti)	7440-32-6		0.016	mg	1030	4				
				supplier	back side metallization	Gold (Au)	7440-57-5		0.012	mg	773	3				
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.166	mg	10687	37				
				supplier	back side metallization	Vanadium (V)	7440-62-2		0.008	mg	515	2				
				supplier	back side metallization	Silver (Ag)	7440-22-4		0.035	mg	2253	8				
				supplier	polymer die coating	Durimide	Proprietary		0.209	mg	13436	47				
				Leadframe	M-004 Copper and its alloys	2826.183	mg	supplier	alloy	Copper (Cu)	7440-50-8		2821.521	mg	998350	636912
								supplier	alloy	Iron (Fe)	7439-89-6		2.825	mg	1000	636
								supplier	alloy	Iron Phosphide (FeP)	26508-33-8		0.848	mg	300	191
supplier	metallization	Nickel (Ni)	7440-02-0						0.915	mg	324	207				
supplier	metallization	Phosphorus (P)	7723-14-0						0.074	mg	26	17				
supplier	JIG - R	solder	Lead (Pb)					7439-92-1	7a-Lead in High mel	15.722	mg	954990	3549			
Soft solder	Solder	16.463	mg	supplier	solder	Silver (Ag)	7440-22-4		0.412	mg	25026	93				
				supplier	solder	Tin (Sn)	7440-31-5		0.329	mg	19984	74				
				supplier	wire	Aluminium (Al)	7429-90-5		1.762	mg	996043	398				
Bonding wires	M-003 Aluminum and its alloys	1.769	mg	supplier	wire	Magnesium (Mg)	7439-95-4		0.007	mg	3957	2				
				supplier	mold compound	Silica, vitreous	60676-86-0		1357.857	mg	870000	306514				
				supplier	mold compound	Epoxy resin	25068-38-6		156.076	mg	100000	3532				
				supplier	mold compound	Phenol resin	29690-82-2		39.019	mg	25000	8808				
				supplier	mold compound	Carbon Black	1333-86-4		7.804	mg	5000	1762				
connections coating	Solder	9.296	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		9.296	mg	1000000	2098				