



## Materials Declaration Form

<b>IPC Form Type *</b>	<b>1752 Distribute</b>	<b>Version</b>	<b>2</b>
<b>Sectionals *</b>	<b>Material Info Manufacturing Info</b>	<b>Subsectionals *</b>	<b>A-D</b>

\* : Required Field

Supplier Information			
<b>Company Name *</b>	<b>STMicroelectronics</b>	<b>Response Date *</b>	<b>2017-11-22</b>
<b>Contact Name *</b>	Refer to Supplier Comment section		Refer to Supplier Comment section
<b>Authorized Representative *</b>	<b>Giuseppe Vitali Palma</b>	<b>Representative Title</b>	<b>ADG MD Champion</b>
<b>Representative Phone *</b>	Refer to Supplier Comment section	<b>Representative Email *</b>	Refer to Supplier Comment section
<b>Supplier Comment</b>	Online Technical Support - STMicroelectronics : <a href="http://www.st.com/web/en/support/support.html">http://www.st.com/web/en/support/support.html</a>		

### Uncertainty Statement

While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.


### Legal Statement

<b>Supplier Acceptance *</b>	<b>true</b>	<b>Legal Declaration *</b>	<b>Standard</b>
------------------------------	-------------	----------------------------	-----------------

### Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STPSC6H065D	HSDK*3D101T6	A	3068	2017-11-22
Amount	UoM	Unit type	ST ECOPACK Grade	
1870.00	mg	Each	ECOPACK2	

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles	 life.augmented	
NA	NA	NA		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
NA	Tin (Sn), matte	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
SIP	10.2-16.25-4.5	2	Through-hole	
Comment	DO 220			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-April 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

Query : California Prop65 list, dated 27th January 2017			
Query			Response
1 - The product does not contain identified substance from California Prop 65 List, no exposure to consumers is foreseen			FALSE
2 - The product is containing below substance(s) from California Prop 65 List, no exposure to consumers is foreseen			TRUE
Substance	amount in product (mg)	Application	ppm in product
Nickel	0.10	Die back side metal - Leadframe metal	55
Lead	1.68	Soft solder	897

QueryList : REACH-12th January 2017				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	HSDK*3D101T6					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	Other Inorganic Materials	2.801	mg	supplier	die	Silicium carbide	409-21-2		2.734	mg	976080	1462
				supplier	metallization	Aluminium (Al)	7429-90-5		0.016	mg	5712	9
				supplier	metallization	Gold (Au)	7440-57-5		0.002	mg	714	1
				supplier	metallization	Silver (Ag)	7440-22-4		0.027	mg	9639	14
				supplier	metallization	Titanium (Ti)	7440-32-6		0.001	mg	357	1
				supplier	back side metallization	Titanium (Ti)	7440-32-6		0.001	mg	357	1
				supplier	back side metallization	Gold (Au)	7440-57-5		0.002	mg	714	1
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.011	mg	3927	6
				supplier	polymer die coating	PIX1 Gamma-butyrolactone	96-48-0		0.007	mg	2499	4
				supplier	alloy	Copper (Cu)	7440-50-8		1182.771	mg	998617	632498
Leadframe	Copper & its alloys	1184.409	mg	supplier	alloy	Iron (Fe)	7439-89-6		1.184	mg	1000	633
				supplier	alloy	Iron Phosphide (FeP)	26508-33-8		0.355	mg	300	190
				supplier	metallization	Nickel (Ni)	7440-02-0		0.092	mg	78	49
				supplier	metallization	Phosphorus (P)	12185-10-3		0.007	mg	6	4
				supplier	solder	Lead (Pb)	7439-92-1	7a-Lead in high met	1.677	mg	955011	897
				supplier	solder	Silver (Ag)	7440-22-4		0.044	mg	25057	24
Soft solder	Solder	1.756	mg	supplier	solder	Tin (Sn)	7440-31-5		0.035	mg	19932	19
				supplier	wire	Aluminium (Al)	7429-90-5		1.385	mg	1000000	741
				supplier	metallization	Silica, vitreous	60676-86-0		587.605	mg	870000	314227
Bonding wires	Other Inorganic Materials	1.385	mg	supplier	mold compound	Epoxy resin	25068-38-6		67.541	mg	100000	36116
				supplier	mold compound	Phenol resin	29690-82-2		16.885	mg	25000	9029
				supplier	mold compound	Carbon Black	1333-86-4		3.377	mg	5000	1806
Encapsulation	Other Organic Materials	675.408	mg	supplier	mold compound	Epoxy resin	25068-38-6		67.541	mg	100000	36116
				supplier	mold compound	Phenol resin	29690-82-2		16.885	mg	25000	9029
Connections coating	Solder	4.241	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		4.241	mg	1000000	2268
				supplier	solder alloy	Tin (Sn)	7440-31-5		4.241	mg	1000000	2268