



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D
<i>* : Required Field</i>			

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2015-12-01
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Authorized Representative *	Rossana Bonaccorso	Representative Title	IPD MD Champion
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement

While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement			
Supplier Acceptance *	true	Legal Declaration *	Standard
Legal Statement	<p>Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.</p>		

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STD16NF25	TLDP*MMBEB62	A	SHENZHEN B/E	2015-12-01
Amount		UoM	Unit type	ST ECOPACK Grade
331.00		mg	Each	ECOPACK2

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		
1	260	3		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
NAC	Tin (Sn), matte	Copper Alloy		



Package Designator	Size	Nbr of instances	Shape	
SIP	6.5, 6.1, 2.3	3	GULL WING	
Comment	TO 252 DPAK			

QueryList : ROHS directive 2011/65/EU _ July 2011	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	false
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	false
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	true
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	false
5 - Product(s) is obsolete, no information is available	false
6 - Product(s) is unknown, no information is available	false
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : REACH-15th June 2015				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration						Mfr Item Name	TLPD*MMBE62					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	Other inorganic materials	5.825	mg	supplier	die	Silicon (Si)	7440-21-3		5.634	mg	967210	17021
				supplier	metallization	Aluminium (Al)	7429-90-5		0.022	mg	3777	66
				supplier	Passivation	Silicon Nitride	12033-89-5		0.015	mg	2575	45
				supplier	Passivation	Silicon Oxide	7631-86-9		0.105	mg	18026	317
				supplier	back side metallization	Titanium (Ti)	7440-32-6		0.003	mg	515	9
				supplier	back side metallization	Gold (Au)	7440-57-5		0.008	mg	1373	24
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.038	mg	6524	115
Leadframe	Copper & its alloys	166.150	mg	supplier	alloy	Copper (Cu)	7440-50-8		164.152	mg	987975	495927
				supplier	alloy	CopperPhosphorous (CuP)	12517-41-8		0.330	mg	1986	997
				supplier	alloy	Cobalt (Co)	7440-48-4		0.462	mg	2781	1396
				supplier	metallization	Nickel (Ni)	7440-02-0		1.199	mg	7216	3622
				supplier	metallization	Phosphorus (P)	12185-10-3		0.007	mg	42	21
Soft solder	Solder	5.468	mg	JIG - R	solder	Lead (Pb)	7439-92-1	7a-Lead in high me	5.222	mg	955011	15776
				supplier	solder	Silver (Ag)	7440-22-4		0.137	mg	25055	414
				supplier	solder	Tin (Sn)	7440-31-5		0.109	mg	19934	329
Bonding wires	Other inorganic materials	0.449	mg	supplier	wire	Aluminium (Al)	7429-90-5		0.448	mg	998885	1353
				supplier	wire	Magnesium (Mg)	7439-95-4		0.001	mg	1115	2
Encapsulation	Other Organic Materials	152.063	mg	supplier	mold compound	Silica, vitreous	60676-86-0		133.055	mg	874999	401979
				supplier	mold compound	Tetramethyl-biphenyl-diyl-bis oxymethylene-b	EC 413-900-7		6.083	mg	40003	18378
				supplier	mold compound	Epoxy Resin	25068-38-6		4.562	mg	30001	13782
				supplier	mold compound	phenol resin	29690-82-2		7.603	mg	49999	22970
				supplier	mold compound	Carbon black	1333-86-4		0.760	mg	4998	2296
Connections coating	Solder	1.045	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		1.045	mg	1000000	3157