



## Materials Declaration Form

<b>IPC Form Type *</b>	1752 Distribute	<b>Version</b>	2
<b>Sectionals *</b>	Material Info Manufacturing Info	<b>Subsectionals *</b>	A-D  <i>* : Required Field</i>

Supplier Information			
<b>Company Name *</b>	STMicroelectronics	<b>Response Date *</b>	27-07-2017
<b>Company Unique ID</b>	NL 008751171801		
<b>Contact Name *</b>	Refer to Supplier Comment section		Refer to Supplier Comment section
<b>Contact Phone *</b>	Refer to Supplier Comment section	<b>Contact Email *</b>	Refer to Supplier Comment section
<b>Authorized Representative *</b>	MDG MD CHAMPION	<b>Representative Title</b>	MDG MD CHAMPION
<b>Representative Phone *</b>	Refer to Supplier Comment section	<b>Representative Email *</b>	Refer to Supplier Comment section
<b>Supplier Comment</b>	Online Technical Support - STMicroelectronics : <a href="http://www.st.com/web/en/support/support.html">http://www.st.com/web/en/support/support.html</a>		

**Uncertainty Statement**

While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

**Legal Statement**

<b>Supplier Acceptance *</b>	true	<b>Legal Declaration *</b>	Standard
------------------------------	------	----------------------------	----------

**Legal Statement**

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STM8S207K6T6C STM8S207K6T6CTR	S25V*765XXXV	A	998Z	27-07-2017
Amount	UoM	Unit type	ST ECOPACK Grade	
196,60	mg	Each	ECOPACK® 2	
.	Comment	ECOPACK® 2 is STMicroelectronics trade name for ROHS compliant device without Brominated and Chlorinated compound (900ppm) and without Antimony oxide flame retardant ( in each organic material)		

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		
3	260	3		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
Not Applicable; if coating is used or other bulk termination	Tin (Sn), matte	Copper Alloy		


  
 life.augmented

Package Designator	Size	Nbr of instances	Shape	
QFP	7x7X1.4	32	L Bend	
Comment	Package : 5V LQFP 32 7x7x1.4 1 0060661			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-April 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	TRUE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	FALSE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description

QueryList : REACH-12th January 2017				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				TRUE
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	S25V*765XXXV				5999999.0	0.0
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die or dies	M-011 Other inorganic materials	6,671	mg	supplier	die	Silicon (Si)	7440-21-3		6,465	mg	969120	32884
				supplier	metallization	Aluminium (Al)	7429-90-5		0,018	mg	2698	92
				supplier	metallization	Copper (Cu)	7440-50-8		0,060	mg	8994	305
				supplier	metallization	Tantalum (Ta)	7440-25-7		0,007	mg	1049	36
				supplier	metallization	Titanium (Ti)	7440-32-6		0,009	mg	1349	46
				supplier	Passivation	Silicon Nitride	12033-89-5		0,016	mg	2398	81
				supplier	Passivation	Silicon Oxide	7631-86-9		0,096	mg	14391	488
				supplier	Metals	Silver	7440-22-4		0,473	mg	901000	2407
Die Attach Epoxy_ABLEBOND 3230_H	M-011 Other inorganic materials	0,525	mg	Supplier	Plastics/polymers	Highly cross-linked polymer	Proprietary		0,052	mg	99000	264
				Supplier	Plastics/polymers	Epoxy Resin A	Proprietary		2,655	mg	22000	13502
Mold Compound_EME-G631SHQ_Sum	M-011 Other inorganic materials	118,354	mg	Supplier	Plastics/polymers	Epoxy Resin B	Proprietary		2,655	mg	22000	13502
				Supplier	Plastics/polymers	Phenol Resin	Proprietary		6,757	mg	56000	34369
				Supplier	Glass	Silica(Amorphous)A	60676-86-0		91,863	mg	780450	-532748
				Supplier	Glass	Silica(Amorphous)B	7631-86-9		13,673	mg	113320	69548
				Supplier	Non-metals	Carbon Black	1333-86-4		0,752	mg	6230	3824
Wire_AG Si TYPE_MKE	Bonding Wire	0,303	mg	Supplier	Metals	Silver	7440-22-4		0,291	mg	960000	1479
				Supplier	Metals	Others	Proprietary		0,012	mg	40000	62
				Supplier	Metals	Tin	7440-31-5		1,209	mg	1000000	6150
Plating anode_Pure Tin_Nuo Nengda	M-011 Other inorganic materials	1,209	mg	Supplier	Metals	Tin	7440-31-5		1,209	mg	1000000	6150
Leadframe_C7+AG_HDS	Copper & its alloys	69,540	mg	Supplier	Metals	Nickel	7440-02-0		2,042	mg	29365	10387
				Supplier	Glass	Silicon	7440-21-3		0,452	mg	6500	2299
				Supplier	Metals	Magnesium	7439-95-4		0,109	mg	1565	554
				Supplier	Metals	Silver	7440-22-4		4,381	mg	63000	22284
				Supplier	Metals	Copper	7440-50-8		62,556	mg	899570	318187