



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D <i>* : Required Field</i>

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	27-07-2017
Company Unique ID	NL 008751171801		
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Contact Phone *	Refer to Supplier Comment section	Contact Email *	Refer to Supplier Comment section
Authorized Representative *	MDG MD CHAMPION	Representative Title	MDG MD CHAMPION
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement

While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement


Supplier Acceptance *	true	Legal Declaration *	Standard
------------------------------	------	----------------------------	----------

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STM32F103C8T7 STM32F103C8T7TR	SE5B*410XXXX	A	998Z	27-07-2017
Amount	UoM	Unit type	ST ECOPACK Grade	
195,22	mg	Each	ECOPACK® 2	
.	Comment	ECOPACK® 2 is STMicroelectronics trade name for ROHS compliant device without Brominated and Chlorinated compound (900ppm) and without Antimony oxide flame retardant (in each organic material)		

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		
3	260	3		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
Not Applicable; if coating is used or other bulk termination	Tin (Sn), matte	Copper Alloy		



 life.augmented

Package Designator	Size	Nbr of instances	Shape	
QFP	7x7X1.4	48	L Bend	
Comment	Package : 5B LQFP 48 7x7x1.4 1 0110596			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-April 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	TRUE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	FALSE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description

QueryList : REACH-12th January 2017				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				TRUE
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	SE5B*410XXXX				6000000.0	0.0				
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)				
Die or dies	M-011 Other inorganic materials	10,285	mg	supplier	die	Silicon (Si)	7440-21-3		9,858	mg	958483	50498				
				supplier	metallization	Aluminium (Al)	7429-90-5		0,029	mg	2820	149				
				supplier	metallization	Copper (Cu)	7440-50-8		0,145	mg	14098	743				
				supplier	metallization	Cobalt (Co)	7440-48-4		0,027	mg	2625	138				
				supplier	metallization	Titanium (Ti)	7440-32-6		0,008	mg	778	41				
				supplier	metallization	Tungsten (W)	7440-33-7		0,016	mg	1556	82				
				supplier	Passivation	Silicon Nitride	12033-89-5		0,019	mg	1847	97				
				supplier	Passivation	Silicon Oxide	7631-86-9		0,183	mg	17793	937				
				Die Attach Epoxy_ABLEBOND 3230_H	M-011 Other inorganic materials	0,610	mg	Supplier	Metals	Silver	7440-22-4		0,550	mg	901000	2815
								Supplier	Plastics/polymers	Highly cross-linked polymer	Proprietary		0,060	mg	99000	309
Mold Compound_EME-G631SHQ_Sun	M-011 Other inorganic materials	114,791	mg	Supplier	Plastics/polymers	Epoxy Resin A	Proprietary		2,638	mg	22000	13515				
				Supplier	Plastics/polymers	Epoxy Resin B	Proprietary		2,638	mg	22000	13515				
				Supplier	Plastics/polymers	Phenol Resin	Proprietary		6,716	mg	56000	34402				
				Supplier	Glass	Silica(Amorphous)A	60676-86-0		88,461	mg	780450	-546858				
				Supplier	Glass	Silica(Amorphous)B	7631-86-9		13,590	mg	113320	69615				
Wire_AG SI TYPE_MKE	Bonding Wire	0,376	mg	Supplier	Non-metals	Carbon Black	1333-86-4		0,747	mg	6230	3827				
				Supplier	Metals	Silver	7440-22-4		0,361	mg	960000	1847				
				Supplier	Metals	Others	Proprietary		0,015	mg	40000	77				
Plating anode_Pure Tin_Nuo Nengda	M-011 Other inorganic materials	1,078	mg	Supplier	Metals	Tin	7440-31-5		1,078	mg	1000000	5524				
Leadframe_C9+Ag_HDS	Copper & its alloys	68,077	mg	Supplier	Metals	Iron	7439-89-6		1,489	mg	21865	7625				
				Supplier	Non-metals	Phosphorus	7723-14-0		0,050	mg	730	255				
				Supplier	Metals	Zinc	7440-66-6		0,077	mg	1125	392				
				Supplier	Metals	Copper	7440-50-8		62,170	mg	913235	318468				
				Supplier	Metals	Silver	7440-22-4		4,289	mg	63000	21970				
				JIG-R	Metals	Lead	7439-92-1		0,003	mg	45	16				