

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STM32L151R8T6A STM32L151R8T6ATR	S55W*429XXXY	A	998Z	2018-09-04
Amount	UoM	Unit type	ST ECOPACK Grade	
355.39	mg	Each	ECOPACK® 2	
	Comment	ECOPACK® 2 is STMicroelectronics trade name for ROHS compliant device without Brominated and Chlorinated compound (900ppm) and without Antimony oxide flame retardant (in each organic material)		

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
3	260	3		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
able; if coating is used or other bulk	Tin (Sn), matte	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
QFP	10X10X1.4	64	L Bend	
Comment	Package : 5W LQFP 64 10x10x1.4 1 0051434			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-April 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	TRUE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	FALSE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description

QueryList : REACH-12th January 2017				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				TRUE
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	S55W*429XXXY				5999999.0	0.0
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die or dies	M-011 Other inorganic materials	9.883	mg	supplier	die	Silicon (Si)	7440-21-3		9.578	mg	969139	26951
				supplier	metallization	Aluminium (Al)	7429-90-5		0.027	mg	2732	76
				supplier	metallization	Copper (Cu)	7440-50-8		0.088	mg	8904	248
				supplier	metallization	Tantalum (Ta)	7440-25-7		0.010	mg	1012	28
				supplier	metallization	Titanium (Ti)	7440-32-6		0.013	mg	1315	37
				supplier	metallization	Tungsten (W)	7440-33-7		0.001	mg	101	3
				supplier	Passivation	Silicon Nitride	12033-89-5		0.024	mg	2428	68
				supplier	Passivation	Silicon Oxide	7631-86-9		0.142	mg	14368	400
Die Attach Epoxy_ABLEBOND 3230_H	M-011 Other inorganic materials	0.908	mg	Supplier	Metals	Silver	7440-22-4		0.818	mg	901000	2302
				Supplier	Plastics/polymers	Highly cross-linked polymer	Proprietary		0.090	mg	99000	253
Mold Compound_EME-G631SHQ_Sur	M-011 Other inorganic materials	245.046	mg	Supplier	Plastics/polymers	Epoxy Resin A	Proprietary		5.213	mg	21000	14669
				Supplier	Plastics/polymers	Epoxy Resin B	Proprietary		5.213	mg	21000	14669
				Supplier	Plastics/polymers	Phenol Resin	Proprietary		13.902	mg	56000	39119
				Supplier	Glass	Silica(Amorphous)A	60676-86-0		190.541	mg	780450	-463852
				Supplier	Glass	Silica(Amorphous)B	7631-86-9		28.629	mg	115320	80556
Wire_AG Si TYPE_MKE	Bonding Wire	0.614	mg	Supplier	Non-metals	Carbon Black	1333-86-4		1.547	mg	6230	4352
				Supplier	Metals	Silver	7440-22-4		0.589	mg	960000	1658
Plating anode_Pure Tin_Nuo Nengda	M-011 Other inorganic materials	1.438	mg	Supplier	Metals	Others	Proprietary		0.025	mg	40000	69
				Supplier	Metals	Tin	7440-31-5		1.438	mg	1000000	4046
Leadframe_C194+Ag_HDS	Copper & its alloys	97.500	mg	Supplier	Metals	Iron	7439-89-6		2.132	mg	21865	5999
				Supplier	Non-metals	Phosphorus	7723-14-0		0.071	mg	730	200
				Supplier	Metals	Zinc	7440-66-6		0.110	mg	1125	309
				Supplier	Metals	Copper	7440-50-8		89.040	mg	913235	250544
				Supplier	Metals	Silver	7440-22-4		6.143	mg	63000	17284
				JIG-R	Metals	Lead	7439-92-1		0.004	mg	45	12