

Serial EEPROM

Boost your flexibility with the world's n°1 EEPROM supplier



More robust than ever: now offering 4 million erase/write cycles per byte and 200 years data retention

ST's EEPROMs perfectly meet the major market requirement of flexibility, with a complete portfolio of densities in standard packages, accommodating power supplies from 1.6 to 5.5 V. All this is achieved with the highest robustness in terms of cycling performance and data retention. This makes ST's EEPROMs the first choice for standard applications as well as for automotive applications.

KEY FEATURES

- 4 million E/W cycles per byte, 100 million cycles per device, 200 years data retention
- Bus type: I²C, SPI, Microwire
- Complete range of densities in a single package form
 - SO8: 1 Kbit to 2 Mbits
 - TSSOP8: 1 Kbit to 1 Mbit
 - UDFPN8: 2 Kbits to 512 Kbits
- Wide voltage range: 5.5 V down to 1.6 V
- High frequency
 - 1 MHz even at 1.6 V
 - 10 MHz at 2.5 V for SPI
- 64-Kbit EEPROM in 1.1 mm² with wafer level chip scale package (WLCSP)
- Additional write-lockable page option
- Automotive grade up to 150°C, AEC-Q100 and PPAP compliant

KEY BENEFITS

- The most reliable choice for heavy cycling even at high temperatures, and data retention forever
- The cheapest non-volatile memory solution and most flexible for parameter storage
 - No dedicated software development required
 - Choice of the memory density once project completed, just pay for the bytes you need
 - Ideal for low V_{CC}, low-energy applications (battery powered)
- Reduced board space with WLCSP package
- Store the manufacturing settings safely
- Fully qualified devices for the most challenging automotive applications

PRODUCT SELECTOR




Generic part number	Serial interface	Storage capacity (Kbit)	Suffix for commercial products			
			S08N package	TSSOP8 package	UFDFPN8 (2x3) package	WLCSP package
M24M02	I ² C	2048	-DRMN6TP			-DRCS6TP/K ¹
M24M01	I ² C	1024	-RMN6TP	-RDW6TP		-DFCS6TP/K
M24512	I ² C	512	-RMN6TP	-RDW6TP	-DFMC6TG	-DFCS6TP/K
M24256	I ² C	256	-BRMN6TP	-BRDW6TP	-BFMC6TG	-DFCS6TP/K
M24128	I ² C	128	-BRMN6TP	-BRDW6TP	-BFMC6TG	-DFCS6TP/K ¹
M24C64	I ² C	64	-RMN6TP	-RDW6TP	-FMC6TG	-FCS6TP/K ²
M24C32	I ² C	32	-RMN6TP	-RDW6TP	-FMC6TG	
M24C16	I ² C	16	-RMN6TP	-RDW6TP	-RMC6TG	-FCS5TP/S
M24C08	I ² C	8	-RMN6TP	-RDW6TP	-RMC6TG	-FCS5TP/S
M24C04	I ² C	4	-RMN6TP	-RDW6TP	-RMC6TG	
M24C02	I ² C	2	-RMN6TP	-RDW6TP	-RMC6TG	
M24C01	I ² C	1	-RMN6TP	-RDW6TP		
M95M02	SPI	2048	-DRMN6TP			-DRCS6TP/K ¹
M95M01	SPI	1024	-RMN6TP	-RDW6TP		-DFCS6TP/K
M95512	SPI	512	-RMN6TP	-RDW6TP	-DFMC6TG	-DFCS6TP/K
M95256	SPI	256	-RMN6TP	-RDW6TP	-RMC6TG	-DFCS6TP/K ¹
M95128	SPI	128	-RMN6TP	-RDW6TP	-RMC6TG	-DFCS6TP/K ¹
M95640	SPI	64	-RMN6TP	-RDW6TP	-RMC6TG	-DFCT6TP/K ¹
M95320	SPI	32	-RMN6TP	-RDW6TP	-RMC6TG	
M95160	SPI	16	-RMN6TP	-RDW6TP	-RMC6TG	-RCS6TP/S
M95080	SPI	8	-RMN6TP	-RDW6TP	-RMC6TG	
M95040	SPI	4	-RMN6TP	-RDW6TP	-RMC6TG	
M95020	SPI	2	-RMN6TP	-RDW6TP		
M95010	SPI	1	-RMN6TP	-RDW6TP		
M93C86	Microwire	16	-WMN6TP	-WDW6TP		
M93C76	Microwire	8	-WMN6TP	-WDW6TP		
M93C66	Microwire	4	-WMN6TP	-WDW6TP	-RMC6TG	
M93S66	Microwire	4	-WMN6TP			
M93C56	Microwire	2	-WMN6TP	-WDW6TP		
M93S56	Microwire	2	-WMN6TP			
M93C46	Microwire	1	-WMN6TP	-WDW6TP		
M93S46	Microwire	1	-WMN6TP			
M34E02	I ² C / DDR3	2		-FDW6TP	-FMC6TG	

Note ¹ = available in Q1/2013

Note ² = also available in thin package (0.33 mm)

Ordering information scheme



© STMicroelectronics - December 2012 - Printed in United Kingdom - All rights reserved
The STMicroelectronics corporate logo is a registered trademark of the STMicroelectronics group of companies
All other names are the property of their respective owners

