



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Sectionals *	A-D <i>* : Required Field</i>

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2017-11-22
Company Unique ID	NL 008751171801		
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Contact Phone *	Refer to Supplier Comment section	Contact Email *	Refer to Supplier Comment section
Authorized Representative *	Giovanni Giacobello	Representative Title	ADG MD CHAMPION
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement

While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.


Legal Statement

Supplier Acceptance *	true	Legal Declaration *	Standard
------------------------------	------	----------------------------	----------

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STPSC6TH13TI	HSVZ*3K101T6	A	SH1A	2017-11-22
Amount	UoM	Unit type	ST ECOPACK Grade	
1900	mg	Each	ECOPACK® 2	
	Comment	ECOPACK® 2 is STMicroelectronics trade name for ROHS compliant device without Brominated and Chlorinated compound (900ppm) and without Antimony oxide flame retardant (in each organic material)		

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
Not Applicable	Not Applicable	Not Applicable		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
Not Applicable	Tin (Sn), matte, annealed	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
SIP	10 - 15.5 - 4.5	3	Through-hole	
Comment	Package: TO 220 (CB415) ISOL.			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-April 2015			
Query			Response
1 - Product(s) meets EU RoHS requirement without any exemptions			FALSE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)			FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)			TRUE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions			FALSE
Exemption Id.	Description		
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)		

QueryList : California Prop65 list, dated 7th July 2017			
Query			Response
1 - The product does not contain identified substance from California Prop 65 List, no exposure to consumers is foreseen			FALSE
2 - The product is containing below substance(s) from California Prop 65 List, no exposure to consumers is foreseen			TRUE
Substance	amount in product (mg)	Application	ppm in product
Nickel	1.09	Die	576
Lead	2.99	Soft solder	1576

QueryList : REACH-7th July 2017				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	HSV2*3K10116					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	M-011 Other inorganic materials	3.806	mg	supplier	die	Silicium carbide	409-21-2		2.434	mg	968178	1281
				supplier	metallization	Aluminium (Al)	7429-90-5		0.016	mg	6364	8
				supplier	metallization	Gold (Au)	7440-57-5		0.002	mg	796	1
				supplier	passivation	Nickel (Ni)	7440-02-0		0.013	mg	5171	7
				supplier	metallization	Silver (Ag)	7440-22-4		0.027	mg	10740	14
				supplier	metallization	Titanium (Ti)	7440-32-6		0.001	mg	398	1
				supplier	back side metallization	Titanium (Ti)	7440-32-6		0.001	mg	398	1
				supplier	back side metallization	Gold (Au)	7440-57-5		0.002	mg	796	1
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.011	mg	4375	6
				supplier	polymer die coating	PIX1 Gamma-butyrolactone	96-48-0		0.007	mg	2784	4
Leadframe	M-004 Copper and its alloys	1617.132	mg	supplier	alloy	Copper (Cu)	7440-50-8		1616.387	mg	999539	850730
				supplier	alloy	Iron (Fe)	7439-89-6		0.745	mg	461	392
				supplier	solder	Lead (Pb)	7439-92-1	7a-Lead in high me	1.613	mg	935072	849
Soft solder	Solder	1.725	mg	JIG - R	solder	Lead (Pb)	7439-92-1	7a-Lead in high me	1.613	mg	935072	849
				supplier	solder	Tin (Sn)	7440-31-5		0.086	mg	49855	45
				supplier	solder	Silver (Ag)	7440-22-4		0.026	mg	15073	13
Soft solder 2	Solder	1.624	mg	JIG - R	solder	Lead (Pb)	7439-92-1	7a-Lead in high me	1.381	mg	850369	727
				supplier	solder	Antimony (Sb)	7440-36-0		0.162	mg	99754	85
				supplier	solder	Tin (Sn)	7440-31-5		0.081	mg	49877	43
Encapsulation	M-011 Other inorganic materials	177.859	mg	supplier	wire	Aluminium (Al)	7429-90-5		3.632	mg	1000000	1912
				supplier	mold compound	Silica, vitreous	60676-86-0		135.172	mg	759995	71143
				supplier	mold compound	Epoxy Cresol Novolak	29690-82-2		18.142	mg	102002	9548
				supplier	mold compound	Phenol resin	9003-35-4		10.672	mg	60003	5617
				supplier	mold compound	Others	Proprietary		8.893	mg	50000	4681
				supplier	mold compound	Metal hydroxide	Proprietary		3.557	mg	19999	1872
connections coating	Solder	6.314	mg	supplier	mold compound	Carbon black	1333-86-4		1.423	mg	8001	749
				supplier	solder alloy	Tin (Sn)	7440-31-5		6.314	mg	1000000	3323
subelement	M-011 Other inorganic materials	89.200	mg	supplier	ceramic	Alumina (Al2O3)	1344-28-1		79.745	mg	894002	41971
				supplier	ceramic	Molybdenum oxide	1313-27-5		4.460	mg	50000	2347
				supplier	metallization	Nickel (Ni)	7440-02-0		1.070	mg	11996	563
				supplier	metallization	Phosphorus (P)	12185-10-3		0.080	mg	897	42
				supplier	metallization	Manganese (Mn)	1344-28-1		3.479	mg	39002	1831
				supplier	0	Titanium (Ti)	7440-32-6		0.366	mg	4103	193